

851-010 90° lug

GENERAL-DUTY • ALUMINUM CORE

MATERIAL SPECIFICATIONS

Lug material: High-conductivity copper alloy
Finish: Nickel plate per AMS2403, AMS 2404, or AMS2424

AUTOSHRINK DASH NO.


Code	Color
-0	Black
-1	Brown
-2	Red
-3	Orange
-4	Yellow
-5	Green
-6	Blue
-7	Violet
-8	Gray
-9	White

AUTOSHRINK BASE PART NUMBER

Terminal Base	Base P/N (Ref.)
12-10	12 777-035-0080-1
	10 777-035-0125-1
8	777-035-0156-1.5
6	777-035-0156-1.5
4	777-035-0250-2
2	777-035-0250-2
0	777-004-02-2
00	777-004-02-2
000	777-004-02-3
0000	777-004-02-3

HOW TO ORDER

Sample Part Number	851-010 C 164 -1
Basic Part Number	Crimp Terminal Lugs for TurboFlex cable
AWG Code / Size	See Size Code table
Nominal Stud Size Dash No.	See Dimensions table
Autoshrink Option	Add dash no. to include Autoshrink (See Tables). Omit for lug only.



COPPER TERMINAL CRIMP TOOL AND DIE SET

Lug Size	AS5259/1 Crimping Head* Die Set	AS5259/4 Crimping Head* Die Set	AS5259/3 Crimping Tool Die Set	AS5259/5 Crimping Tool Die Set
12-10	See note below**			
8	MS90485-8	M5259/7-001	MS90485-8	M5259/7-001
6	MS90485-6	M5259/7-002	MS90485-6	M5259/7-002
4	MS90485-4	M5259/7-003	MS90485-4	M5259/7-003
2	MS90485-2	M5259/7-004	MS90485-2	M5259/7-004
0	MS90485-01	M5259/7-006	MS90485-01	M5259/7-006
00	MS90485-02	M5259/7-007	MS90485-02	M5259/7-007
000	MS90485-03	N/A	N/A	N/A
0000	MS90485-04	N/A	N/A	N/A

*Requires Pump per AS5259/2.

Removal or cutting off of flash after crimping will result in exposed base metal. Glenair Autoshrink may be applied over the crimp barrel and wire, to environmentally protect exposed area. (see How to Order for Autoshrink option)

**Crimp size 12-10 lugs using tool M22520/38-01, cavity c, yellow (12 or 10awg wire).

SIZE CODE

Terminal Size	12-10	8	6	4	2	0	00	000	0000
AWG Code	B	C	D	E	F	G	H	I	J

WIRE STRIP LENGTH

Terminal Size	12-10	8	6	4	2	0	00	000	0000
Strip Length	.51 (12.95)	.70 (17.78)	.75 (19.05)	.87 (22.10)	1.03 (26.16)	1.09 (27.69)	1.21 (30.73)	1.42 (36.07)	1.62 (41.15)

AIRCRAFT POWER INTERCONNECT TECHNOLOGY

Crimp Terminal Lugs for TurboFlex®



851-010 90° lug

DIMENSIONS															
Stud Size Dash No.	Wire Size	Stud Size	A Max	B Min	C Min Rad	D		Ø E.O.D.	Ø F.I.D.	G		W & H*		(K)	J
						Max	Min			Max	Min	Max	Min		
164	8	8 (.164)	1.187 (30.15)	.633 (16.08)	.234 (5.94)	.084 (2.13)	.064 (1.63)	.285 (7.24)	.183 (4.65); .173 (4.39)	.178 (4.52)	.168 (4.27)	.429 (10.90)	.386 (9.80)	(.72)	.618 (15.70)
190	8	10 (.190)	1.187 (30.15)	.633 (16.08)	.234 (5.94)	.084 (2.13)	.064 (1.63)	.285 (7.24)	.183 (4.65); .173 (4.39)	.203 (5.16)	.193 (4.90)	.429 (10.90)	.386 (9.80)	(.72)	.618 (15.70)
250	8	1/4 (.250)	1.189 (30.20)	.633 (16.08)	.265 (6.73)	.084 (2.13)	.064 (1.63)	.285 (7.24)	.183 (4.65); .173 (4.39)	.275 (6.99)	.260 (6.60)	.478 (12.14)	.435 (11.05)	(.72)	.673 (17.09)
375	8	3/8 (.375)	1.189 (30.20)	.633 (16.08)	.328 (8.33)	.084 (2.13)	.064 (1.63)	.285 (7.24)	.183 (4.65); .173 (4.39)	.400 (10.16)	.385 (9.78)	.590 (14.99)	.547 (13.89)	(.72)	.793 (20.14)
250	6	1/4 (.250)	1.329 (33.76)	.680 (17.27)	.265 (6.73)	.084 (2.13)	.064 (1.63)	.334 (8.48)	.225 (5.72); .215 (5.46)	.275 (6.99)	.260 (6.60)	.503 (12.78)	.460 (11.68)	(.80)	.686 (17.42)
375	6	3/8 (.375)	1.338 (33.99)	.680 (17.27)	.328 (8.33)	.084 (2.13)	.064 (1.63)	.334 (8.48)	.225 (5.72); .215 (5.46)	.400 (10.16)	.385 (9.78)	.623 (15.82)	.580 (14.73)	(.80)	.809 (20.55)
190	4	10 (.190)	1.493 (37.92)	.800 (20.32)	.276 (7.01)	.096 (2.44)	.076 (1.93)	.395 (10.03)	.297 (7.54); .287 (7.29)	.203 (5.16)	.193 (4.90)	.628 (15.95)	.580 (14.73)	(.95)	.759 (19.28)
250	4	1/4 (.250)	1.493 (37.92)	.800 (20.32)	.276 (7.01)	.096 (2.44)	.076 (1.93)	.395 (10.03)	.297 (7.54); .287 (7.29)	.275 (6.99)	.260 (6.60)	.628 (15.95)	.580 (14.73)	(.95)	.759 (19.28)
312	4	5/16 (.312)	1.493 (37.92)	.800 (20.32)	.308 (7.82)	.096 (2.44)	.076 (1.93)	.395 (10.03)	.297 (7.54); .287 (7.29)	.338 (8.59)	.323 (8.20)	.648 (16.46)	.605 (15.37)	(.95)	.803 (20.40)
375	4	3/8 (.375)	1.493 (37.92)	.800 (20.32)	.328 (8.33)	.096 (2.44)	.076 (1.93)	.395 (10.03)	.297 (7.54); .287 (7.29)	.400 (10.16)	.385 (9.78)	.648 (16.46)	.605 (15.37)	(.95)	.823 (20.90)
312	2	5/16 (.312)	1.783 (45.29)	.960 (24.38)	.343 (8.71)	.109 (2.77)	.089 (2.26)	.489 (12.42)	.371 (9.42); .361 (9.17)	.338 (8.59)	.323 (8.20)	.711 (18.06)	.668 (16.97)	(1.13)	.970 (24.64)
375	2	3/8 (.375)	1.783 (45.29)	.960 (24.38)	.343 (8.71)	.109 (2.77)	.089 (2.26)	.489 (12.42)	.371 (9.42); .361 (9.17)	.400 (10.16)	.385 (9.78)	.711 (18.06)	.668 (16.97)	(1.13)	.970 (24.64)
437	2	7/16 (.437)	1.783 (45.29)	.960 (24.38)	.453 (11.51)	.109 (2.77)	.089 (2.26)	.489 (12.42)	.371 (9.42); .361 (9.17)	.463 (11.76)	.448 (11.38)	.804 (20.42)	.740 (18.80)	(1.13)	1.120 (28.45)
375	0	3/8 (.375)	1.858 (47.19)	1.018 (25.86)	.418 (10.62)	.125 (3.18)	.105 (2.67)	.595 (15.11)	.466 (11.84); .456 (11.58)	.400 (10.16)	.385 (9.78)	.853 (21.67)	.810 (20.57)	(1.19)	1.115 (28.32)
437	0	7/16 (.437)	1.858 (47.19)	1.018 (25.86)	.453 (11.51)	.125 (3.18)	.105 (2.67)	.595 (15.11)	.466 (11.84); .456 (11.58)	.463 (11.76)	.448 (11.38)	.903 (22.94)	.860 (21.84)	(1.19)	1.175 (29.85)
500	0	1/2 (.500)	1.858 (47.19)	1.018 (25.86)	.453 (11.51)	.125 (3.18)	.105 (2.67)	.595 (15.11)	.466 (11.84); .456 (11.58)	.525 (13.34)	.510 (12.95)	.903 (22.94)	.860 (21.84)	(1.19)	1.175 (29.85)
375	00	3/8 (.375)	1.985 (50.42)	1.141 (28.98)	.473 (12.01)	.129 (3.28)	.109 (2.77)	.647 (16.43)	.523 (13.28); .513 (13.03)	.400 (10.16)	.385 (9.78)	.956 (24.28)	.913 (23.19)	(1.31)	1.221 (31.01)
437	00	7/16 (.437)	1.985 (50.42)	1.141 (28.98)	.473 (12.01)	.129 (3.28)	.109 (2.77)	.647 (16.43)	.523 (13.28); .513 (13.03)	.463 (11.76)	.448 (11.38)	.956 (24.28)	.913 (23.19)	(1.31)	1.221 (31.01)
500	00	1/2 (.500)	1.985 (50.42)	1.141 (28.98)	.473 (12.01)	.129 (3.28)	.109 (2.77)	.647 (16.43)	.523 (13.28); .513 (13.03)	.525 (13.34)	.510 (12.95)	.956 (24.28)	.913 (23.19)	(1.31)	1.221 (31.01)
375	000	3/8 (.375)	2.223 (56.46)	1.348 (34.24)	.513 (13.03)	.140 (3.56)	.120 (3.05)	.721 (18.31)	.588 (14.94); .578 (14.68)	.400 (10.16)	.385 (9.78)	1.053 (26.75)	1.010 (25.65)	(1.54)	1.312 (33.32)
437	000	7/16 (.437)	2.223 (56.46)	1.348 (34.24)	.513 (13.03)	.140 (3.56)	.120 (3.05)	.721 (18.31)	.588 (14.94); .578 (14.68)	.463 (11.76)	.448 (11.38)	1.053 (26.75)	1.010 (25.65)	(1.54)	1.312 (33.32)
500	000	1/2 (.500)	2.223 (56.46)	1.348 (34.24)	.513 (13.03)	.140 (3.56)	.120 (3.05)	.721 (18.31)	.588 (14.94); .578 (14.68)	.525 (13.34)	.510 (12.95)	1.053 (26.75)	1.010 (25.65)	(1.54)	1.312 (33.32)
375	0000	3/8 (.375)	2.442 (62.03)	1.547 (39.29)	.560 (14.22)	.150 (3.81)	.130 (3.30)	.791 (20.09)	.656 (16.66); .646 (16.41)	.400 (10.16)	.385 (9.78)	1.148 (29.16)	1.095 (27.81)	(1.75)	1.401 (35.59)
437	0000	7/16 (.437)	2.442 (62.03)	1.547 (39.29)	.560 (14.22)	.150 (3.81)	.130 (3.30)	.791 (20.09)	.656 (16.66); .646 (16.41)	.463 (11.76)	.448 (11.38)	1.148 (29.16)	1.095 (27.81)	(1.75)	1.401 (35.59)
500	0000	1/2 (.500)	2.442 (62.03)	1.547 (39.29)	.560 (14.22)	.150 (3.81)	.130 (3.30)	.791 (20.09)	.656 (16.66); .646 (16.41)	.525 (13.34)	.510 (12.95)	1.148 (29.16)	1.095 (27.81)	(1.75)	1.401 (35.59)

*H Max and Min dimensions shall be one half of the W Max and Min dimensions, respectively.