

SPECIALTY WIRE AND CABLE

SGEMP-Resistant Wire

968-057

SGEMP-Resistant Cable

MATERIALS

- Wires: GS22759-32 thru -46 per part number
- Tape: Aluminum Mylar, foil side out
- Shield: See part number development. 90% Minimum shield coverage
- Jacket: White crosslinked modified ETFE

NOTES

- Wire is solid white with colored stripes. Stripe color coding per ANSI/NEMA WC 27500 preferred identification method.
- Jacket wall thickness per ANSI/NEMA WC 27500.

HOW TO ORDER					
Sample Part Number	968-057	-45	-20	-2	-T
Basic Part Number	968-057				
Wire Type	See Table I				
Wire Size	20 to 30 AWG				
Number of Wires	1 to 4				
Shield Type	T = Tin-Coated Copper, Round S = Silver-Coated Copper, Round N = Nickel-Coated Copper, Round				




TABLE 1 - WIRE TYPE	
Code	Wire Type
32	M22759/32 or GS22759-32
33	M22759/33 or GS22759-33
34	M22759/34 or GS22759-34
35	M22759/35 or GS22759-35
41	M22759/41 or GS22759-41
42	M22759/42 or GS22759-42
43	M22759/43 or GS22759-43
44	M22759/44 or GS22759-44
45	M22759/45 or GS22759-45
46	M22759/46 or GS22759-46

SPECIALTY WIRE AND CABLE