

"ZERO-CROSSTALK" Series 794 VersaLink™ Connectors



799-225 Clamshell Strain Relief for Series 794 Connectors

SERIES 794 VERSALINK CONNECTORS



MATERIAL AND FINISH		
Sym	Mat'l	Finish Description
E	ALUM	Chem Film
J		Cadmium With Yellow Chromate
M		Electroless Nickel
MT		Nickel-Ptfe (1000 Hr Salt Spray, Rohs)
NF		Cad/O.D. Over Electroless Nickel (1000 Hr Salt Spray)
UCR		Zinc-Cobalt With Black Chromate (Rohs)
Z2		Gold
ZNU		Zinc-Nickel With Black Chromate
Z1	SST	Passivated
ZM		Electroless Nickel

MATERIALS AND FINISHES

- Backshell, saddle bars: aluminum alloy, see material/finish table
- Hardware: CRES/passivated

NOTES

1. Measurement taken with saddle bars bottomed out on the ears. Applicable to elliptical saddle bars only.

PART NUMBER DEVELOPMENT				
Sample Part Number		799-225	M	R
Series	799-225 = Strain Relief Backshell for Series 794 VersaLink Connectors			
Finish	See Material Finish Table			
Shell Size	A, B, C, D, E, F, G, H, J, K, L, P, Q, R, S, T, U			
Saddle Bar Type	F = Flat E = Elliptical			

DIMENSIONS				
SHELL	A MAX	B	C MAX	D
A	0.385 (9.78)	0.188 (4.78)	0.485 (12.32)	0.188 (4.78)
B	0.385 (9.78)	0.250 (6.35)	0.635 (16.13)	0.250 (6.35)
C	0.385 (9.78)	0.218 (5.54)	0.785 (19.94)	0.359 (9.12)
D	0.385 (9.78)	0.218 (5.54)	0.885 (22.48)	0.459 (11.66)
E	0.385 (9.78)	0.218 (5.54)	1.035 (26.29)	0.609 (15.47)
F	0.385 (9.78)	0.218 (5.54)	1.185 (30.10)	0.759 (19.28)
G	0.475 (12.07)	0.306 (7.77)	1.145 (29.08)	0.726 (18.44)
H	0.495 (12.57)	0.324 (8.23)	1.525 (38.74)	1.099 (27.91)
J	0.385 (9.78)	0.218 (5.54)	1.545 (39.24)	1.111 (28.22)
K	0.385 (9.78)	0.218 (5.54)	1.945 (49.40)	1.511 (38.38)
L	0.495 (12.57)	0.324 (8.23)	1.765 (44.83)	1.335 (33.91)
P	0.555 (14.10)	0.384 (9.75)	0.765 (19.43)	0.279 (7.09)
Q	0.555 (14.10)	0.384 (9.75)	1.140 (28.96)	0.654 (16.61)
R	0.555 (14.10)	0.384 (9.75)	1.515 (38.48)	1.029 (26.14)
S	0.555 (14.10)	0.384 (9.75)	1.890 (48.01)	1.404 (35.66)
T	0.555 (14.10)	0.384 (9.75)	2.265 (57.53)	1.779 (45.19)
U	0.935 (23.75)	TBD	2.265 (57.53)	TBD

