

ULTRA-FLEXIBLE TurboFlex Rugged Power Cable



TurboFlex® Aluminum Core, Duralectric™ D Insulation, 3000 VAC,
961-062

TURBOFLEX

FEATURES

- For weight savings: all the benefits of TurboFlex wire and Duralectric D insulation with lightweight aluminum core conductor

HOW TO ORDER TURBOFLEX®

HOW TO ORDER TURBOFLEX®					
Sample Part Number	961	-062	-A	-H	-2
Basic No.	TurboFlex with Duralectric D Insulation				
Wall Thickness	-062 = .062"				
Conductor Material	-A = Aluminum (-65 – 200°C)				
Wire Size (See Table I)	R, S, A, B, C, D, E, F, G, H, I, J				
Duralectric D Insulation Color	See Table II				



Table I: TurboFlex Wire Size, Dimensions, DC Resistance and Ampacity Ratings

AWG Code	AWG	Strand / Count / AWG	Cir Mil (nom)	Ø B in. (mm)	DC Resistance @ 20°C (Ohms/1000 ft.)	Ampacity (Amps) 40°C Ambient
R	16	7 X 15/36	2625	.063 (1.60)	6.85	15-20
S	14	7 X 24/36	4200	.080 (2.03)	4.26	15-30
A	12	7 X 37/36	6475	.099 (2.51)	2.80	25-40
B	10	7 X 59/36	10325	.126 (3.20)	1.69	30-50
C	8	7 X 95/36	16625	.159 (4.04)	1.07	45-80
D	6	7 X 150/36	26250	.200 (5.08)	0.67	60-110
E	4	7 X 7 X 34/36	41650	.271 (6.88)	0.42	80-150
F	2	7 X 7 X 54/36	66150	.342 (8.69)	0.26	115-205
G	1/0	7 X 7 X 86/36	105350	.431 (10.95)	0.16	150-280
H	2/0	7 X 7 X 108/36	133000	.483 (12.27)	0.13	175-325
I	3/0	19 X 7 X 51/36	169575	.547 (13.89)	0.10	205-380
J	4/0	19 X 7 X 64/36	212800	.613 (15.57)	0.08	240-450

Maximum ampacities are based on temperature rise to limits of the materials used in cable construction, based on single cable bundle in free air and at sea level pressure. Consult Glenair for more information.

Ampacity Ratings: Ambient Temperature Correction Factors

Ambient Temp (°C)	For ambient temperatures other than 40°C (104°F), multiply the allowable ampacities from the table above by the appropriate factor below
41 – 50	0.97
51 – 60	0.94
61 – 70	0.90
71 – 80	0.87
81 – 90	0.83
91 – 100	0.79
101 – 120	0.71
121 – 140	0.61
141 – 160	0.50
161 – 180	0.35
181 – 200	----
201 – 255	----

Table II: Duralectric D Insulation Color

Weatherproof, halogen free, flame resistant	
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Kelly Green
6	Blue
7	Violet
8	Gray
9	White
Consult factory for other specific colors	

Wire Weight and Outer Diameter

AWG Code	Weight lbs/1000 ft. (nom.)	Ø A in. (mm)	Insulation wall thickness in. (mm)
R	17.1	.187 (4.75)	.062 (1.57)
S	20.7	.204 (5.18)	
A	25.2	.223 (5.66)	
B	32.3	.250 (6.35)	
C	42.6	.283 (7.19)	
D	57.2	.324 (8.23)	
E	81.2	.395 (10.03)	
F	114.5	.466 (11.84)	
G	165.0	.555 (14.10)	
H	199.5	.607 (15.42)	
I	244.4	.671 (17.04)	
J	296.4	.737 (18.72)	

NOTES

- Bend radius is 3X the outer diameter
- Cable will be marked with "GLENAIR TURBOFLEX", wire gauge, part number, CAGE 06324.
- Insulation thickness tolerance is ±10%