GLENAIR • JANUARY 2019 • VOLUME 23 • NUMBER 1



Connector Reference Reference



ntercomments Professionals

High-performance MS type electrical connectors have been around since the late '30s. As military and aerospace electronics became more prevalent and sophisticated, so did the requirements for interconnection devices. Today, a broad range of circular and rectangular connector types—many specialized for land, sea, air and space applications—are used for the interconnection of electronic systems, sensors, power supplies and other equipment that depend on reliable performance and standards-body guarantees for performance and quality.

In this special update edition of *QwikConnect*—which we think you'll agree belongs in your permanent reference library—we are happy to provide you with some of the most essential information for use in identifying and specifying MS type connectors and accessories.

Table of Contents

	Торіс	Page
	Military Standard Connector Types - Circular	4
A street	Popular Military Standard Connector Series	6
	Glenair Signature Connector Series	8
	Introduction to Military Standard Cylindrical Connectors	10
	Design Elements of Military Standard Connector Series	13
	Contact Densities in Cylindrical and Rectangular Connectors	17
	Wire Gauge Size and Comparison Reference Table	18
THE SHOULD BY	Wire Bundle Diameter Calculator	19
	Scoop-Proof Contact Protection	20
	Anatomy of a Crimp-Contact Circular Connector	21
Specifying Appropriate NASA Screening I make that the entire that it consists the state of the entire that th	NASA / ESA Space-Grade Outgassing Properties and Requirements	22
	International Standards IP Protection Classification	23
%	Common Modifications to Standard MS Type Connectors	24

QwikConnect • January 2019

QwikConnect

	Table of Contents	
	Торіс	Page
	Military Standard Circular Connector Index	25
	Military Specification Comparison Tables for Circular Connectors	32
	Right Brain / Left Brain Performance Matrix	40
State	AS39029 Crimp Contact Selection Guide	44
	AS39029 Shielded Contact and El Ochito® Octaxial Contact Selection Guide	46
Steam Part Part Speciagnos Con- Standard Special Speci	Fiber Optic Contact Selection Guide	48
	High-Frequency RF and High-Speed Datalink Contacts	49
	D38999 Series III and Series 806 Mighty Mouse Mil-Aero Performance Specs	50
17 18 27 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	Series 806 Mighty Mouse Mil-Aero Contact Arrangements	53
	MIL-STD-1560 Power and Signal Contact Arrangements	54
	MIL-DTL-38999 QPL-to-Glenair Finish Code Cross-Reference	60
Name of the control o	Galvanic Corrosion and Anodic Index Reference Tables	62
<u>(ξx</u>)	Ex Hazardous Zone and Category Designations	63
	Circular Connector-to-Backshell Interface Standards and Designator Codes	66
Part Sect	Connector Manufacturers' Index for Backshell and Accessory Specifications	69
Particle Secretary Secreta	AS85049 Qualified Backshells and Connector Accessories	72
- 1000 July 1000	Recommended Backshell-to-Connector Torque Values	73
	BandMaster ATS® Performance Matrix and Sizing Information	74
Ginney of Cornector Terms and Definition	Glossary of Connector Terms and Definitions	76

QwikConnect • January 2019

MS Connector Types-Circular

Cable Plugs and In-line Receptacles

Environmental cable plugs and in-line receptacles are the ruggedized cable-mounted halves of I/O connector pairs. These "free hanging," or cable connectors, are equipped with coupling rings or other mating technologies to effect reliable and repeatable interconnections. Coupling styles include various threaded configurations as well as bayonet, breech-lock, push-pull, lanyard release, and others. In-line receptacles facilitate daisy-chaining of cables.

Box- and Panel-Mounted Receptacles

The other half of an I/O interconnect assembly is the box, flange, or wall-mounted receptacle. These connector halves are characterized by their flange or mounting style (typically jamnut mount or square-flange with fasteners) and their front or rear mount position vis-a-vis the box or panel. Crimp contact versions as well as wired pigtails are available, but the most common configuration utilizes PC tail terminations for direct attachment to a circuit board.

Bulkhead Feed-Throughs


Bulkhead Feed-Throughs eliminate the need to permanently fix cable harnesses to panels-affording increased system flexibility, superior mechanical integrity, and greater serviceability. Popular hermetic and environmental bulkhead feed-through connectors include MIL-DTL-38999 Series I, II, III and IV configurations. Hermetic versions are ideally suited for high-pressure/low-leakage applications in air, sea and space environments, meeting a leak rate of 1 X 10⁻⁷ cm³ per second. Environmental versions offer IP67 level sealing.

Sav-Con® Connector Savers

Connector Savers protect connectors subject to repeated mating and unmating cycles, preventing costly repair or replacement of deliverable connectors and cables while preserving the quality and integrity of connector performance. Connector Savers take the abuse of repeated connection cycles instead of "black box" or other equipment-mounted connectors.

PCB-Mount Connectors

Panel-mounted I/O connectors equipped with termination pins or tails for direct attachment to printed circuit boards allow electrical engineers to optimize electrical performance and save space in line replaceable modules (LRMs) and other electronic equipment enclosures. Various types of PCB terminations are available including compliant pin, through-hole, and surface mount.




QwikConnect

Fused Glass and Lightweight Encapsulant Hermetics

Hermetic connectors are a special class of Mil /Aero interconnect that incorporates glassto-metal or other highly-engineered sealing technology. Hermetic connectors are specified for applications as divergent as submarines and orbiting satellites. They are deployed to resist moisture ingress in underground applications and to withstand pressure differentials in vacuum chambers, laboratory equipment and commercial and military aircraft. While glass-to-metal sealing has traditionally been the "gold standard" of hermetic sealing, new lightweight encapsulant sealing technology from Glenair, called CODE RED, delivers mission-critical hermetic sealing with better contact electrical performance and a significant reduction in weight.

EMI/EMP Filtered Connectors

EMI/RFI filter connectors incorporate electronic circuitry (capacitors) to strip line signals of unwanted RF or HRF noise that could potentially impact electronic equipment or system performance. Filter connectors may also be equipped with transient voltage suppression diodes to clamp off a high-energy power surge, such as might occur from a lightning strike or EMP event, before the surge can damage sensitive electronic equipment. Typically supplied as receptacle configurations, filtering technology may also be incorporated in plugs, bulkhead feed-throughs, and Sav-Con® Connector Savers.



Blind-Mate Connectors

Various special applications for MS circular connectors, such as satellite payload docking and release, require the use of mating connectors without threaded couplings or some other style of fixed attachment. Blind-mate connectors typically use special keying, guide pin technolgy or other design features to ensure smooth mating and de-mating of connector interfaces that are obscured from view such as in rack-and-panel applications.

Lanyard-Release Connectors

Designed for extreme reliability in harsh environments including aerospace and defense applications, lanyard-release connectors (such as the AS81703) provide jam-free, push-on, pull-off operation. Lanyard-release connectors are commonly used for droppable stores, umbilical connect, rocket launch, and other extreme vibration and shock applications where rugged and reliable de-mating is a must. Numerous configurations exist including umbilical receptacles, go-between buffers, and mounted plugs. Insert arrangements may include hybrid signal/power and RF contact technology.



Special-Application Connectors

Any number of unique special-application connector designs, often derivatives of military standards but not exactly covered by the specifications, are common in the industry. Special high-voltage or high-current designs, deep sea pressure-resistant configurations, hazardous zone solutions, extreme temperature tolerant connectors, and so on, are employed to meet extraordinary electrical, mechanical, and environmental stress factors.



Popular MS Connector Series

All the same functional types as were presented in the previous MS Circular spread are to be found in rectangular designs—including cable plugs and receptacles, connector savers, PCB-mount receptacles, hermetics, EMI/EMP filter connectors, blind mates and so on. So rather than repeat the same discussion for rectangular connectors, let's go ahead instead with a description of each of the military standard series for both rectangular and circular connectors, largely categorized by size and contact density.

ARINC 404 (MIL-C-81659) and 600

The largest rectangular connector family, the ARINC 404 and 600, takes its name from Aeronautical Radio, Inc., an airline industry association active in specifying connectors for use in commercial aircraft. The modular ARINC connector family features aerospace-grade construction and is designed with seals against moisture for use in high-reliability applications. The original environmental resistant version, the ARINC 404 series, was geared for use by the commercial aircraft industry. The military produced its own version under specification MIL-C-81659. Later, the ARINC 600 series was developed—again for the commercial aircraft industry—as a significant upgrade to the ARINC 404. ARINC 600 offers low mating force contacts, and up to 800 size 22 contact positions in one connector. Larger power contacts are also supported as well as shielded contacts up to size #8.

MIL-DTL-24308 D-Subminiature


By far the most common of all rectangular connectors, the MIL-DTL-24308 D-Subminiature connector, with its distinctive D-shape mating interface, is well suited for its role as a general purpose power and signal interconnect—for example for the low and medium speed serial data communications required by flight computers. Adapted from military connectors first offered in the 1950s, D-subminiature pin and socket connectors are typically supplied with solder cup, crimp, or PC tail contacts. Special versions of the D-sub, for coaxial, high-voltage, and high-current contacts are available. High-performance environmental, space-grade, hermetic and filter class versions are used in airframe applications and elsewhere when standard-performance products will not serve.

MIL-DTL-83513 Micro-D


The Micro-D is a high-density, precision machined rectangular with contacts set on .050" centers, typically supplied with fixed solder cup or PC tail contacts, or pre-wired with a pigtail or flex. This small form-factor rectangular connector is typically specified for missile, satellite, or other high vibration and shock mil-aero applications that require reduced size and weight, and mission-critical interconnect performance.

MIL-DTL-32139 Nanominiature

Nanominiature connectors, with their 1 AMP contacts set on .025" centers, are the smallest and lightest mil-spec rectangular in the business. These MIL-DTL-32139 qualified connectors for mission-critical board-to-wire applications offer superior mating and unmating performance and environmental resistance. TwistPin contact-equipped Nanominiature connectors are precision machined from aluminum, titanium or stainless steel. Designed to accommodate size #30 and #32 gauge wire, both rectangular and circular versions are available in prewired pigtail or printed circuit board configurations.







QwikConnect • January 2019

QwikConnect

MIL-DTL-38999 (Aerospace)

Environmental and hermetic class MIL-DTL-38999 Series connectors are the most widely used connectors within the mil-aero industry. Developed for fast vibration-proof mating, the Series III triple-start prevents galling and cross-threading, as well as low-resistance metal-to-metal coupling. Series IV offers the industry's most positive mating with a 90° quarter-turn breech-lock mate with visual, tactile and audible engagement confirmation. Series I and II (low-profile) bayonet-couplers round out this versatile, high-density connector family.



Ideal for high-shock / high-vibration environments including military space and defense applications such as missile and payload deployment, the AS81703 provides jam-free, push-on, lanyard-activated pull-off operation. Glenair's AS81703 Series 3 type connector series is intermateable and intermountable with currently available AS81703 mil-spec and commercial connectors, and offers several enhancements to the standard design: an integrated band porch for shield termination, 360° saw teeth for rear-end accessory clocking, and a red full-mate indicator stripe.

MIL-DTL-5015 (Threaded and Reverse-Bayonet)

The MIL-DTL-5015 is a medium-density circular series with a wide range of power and signal insert arrangements. Available in both threaded and reverse-bayonet coupling, the 5015 is specified in many rugged-duty applications including military ground vehicles and industrial applications. Considered more of a "legacy" connector series, the 5015 nevertheless is a popular choice for general-duty environmental applications with mixed power and signal requirements.

MIL-DTL-83723 (General Duty)

The MIL-DTL-83723 Series III Type connector is suited for use on commercial, military, and aerospace interconnect systems that demand high-vibration resistance and reliability in a medium-density cylindrical connector. The MIL-DTL-83723 uses Mil-Standard AS39029 crimp contacts as well as solder cups and PC Tail terminations in sizes 12, 16, and 20 and is available in over 30 insert arrangements, from 2 to 61 contacts.


MIL-DTL-26482 (Series I and II)


The MIL-DTL-26482 (Glenair Series IPT) bayonet-lock connector is suited for general and environmental applications that require a medium-density military type cylindrical connector. Also referenced by the VG qualification, VG95328, the 26482 bayonet coupling mechanism provides fast and easy mating, especially when the connector is situated in an awkward or hard-to-reach location. Series II versions (Glenair IPT SE) offer crimp contacts and improved dielectrics.

MIL-DTL-28840 (Shipboard)

QwikConnect • January 2019

The standard connector and backshell series for shipboard use, MIL-DTL-28840 offers high-density insert arrangements and high-shock performance. The MIL-DTL-28840 features RFI/EMI shielding, scoop-proof shells and corrosion-resistant materials and finishes. Glenair's qualified product line is fully tooled and highly available.













Glenair Signature Connector Series

Available military standard connector series satisfy the broad range of requirements for electrical wire interconnect systems. For application requirements that are not addressed by an MS series, or go beyond the capabilities of available series designs, Glenair has developed a wide range of smaller, lighter, and advanced-performance solutions.

HiPer-D High-Performance M24308

The Glenair Series 28 HiPer-D® connector is intermateable and intermountable with standard M24308 type D-Subs, but meets the need for improved performance in rugged environments. Unlike standard M24308 connectors with stamped steel shells, the HiPer-D® is precision-machined from aluminum or stainless steel. Dielectric inserts are made with thermoset epoxy for improved chemical resistance and are capable of withstanding 200°C continuous operating temperature. Aerospace-grade fluorosilicone grommets and face seals provide watertight sealing. Integrated grounding fingers provide superior electromagnetic compatibility. The HiPer-D® is available in every standard and high-density M24308 layout as well as combo layouts integrating power and shielded contacts.

Series 79 Ultraminiature Rectangular


The Series 79 was developed for aerospace systems that require advanced levels of environmental protection, electromagnetic shielding and size/weight reduction. The Series 79 features crimp, rear-release size #23 contacts on .075" spacing, as well as size #12 and #16 power and coaxial crimp contacts in a range of hybrid layouts. Panel-mount connectors feature conductive sealing gaskets. Right-angle PCB connectors have an EMI shroud to prevent electromagnetic interference. Wire sealing grommets and interfacial seals protect circuits from moisture and contamination. Plugs are available with auxiliary EMI springs for superior EMC performance. Series 791 adds advanced shell design and polarization features for rack-and-panel applications, and Series 792 is specially designed to accommodate shielded Size #8 contacts for high-speed datalink applications.

Series 20 Super-Twin[™] Modular Composite

The Glenair series 20 Super-Twin™ lightweight modular connector is an innovative replacement for legacy cable and panel connectors that no longer meet changing performance specifications for ease of assembly, EMC, and size, weight and power optimization. Super-Twin™ can accommodate a broad range of contact sizes and types from #23 to #8 signal, Quadrax, power, and fiber. Modular inserts offer fast and flexible assembly and repair. Peripheral and grommet seals provide outstanding environmental protection. Keyed inserts and shells provide protection against mis-mating. Innovative clamshell and banding porch design brings modern connector capabilities to cable and panel applications.

Board-Level Rectangulars: HD Stacker™ / Alphalink™

The HD Stacker™ brings Glenair innovation to stacking board-to-board connectors: Ultra high-density .0625" Chevron Contact System provides 55% more contacts per connector size as compared to current industry solutions. Polarized connector bodies and polarized guide pins prevent accidental mismating. The solder-free press-fit compliant pin contacts are removable, repairable, and available in custom lengths. HD Stacker™ connectors may be ordered with pre-wired cable or flex jumper terminations. AlphaLink™ is an innovative high-performance PCB connector built on .050" spacing with spring-loaded board contacts and flex, wire, or solder cup terminations. AlphaLink may be ordered as a discrete connector or in turnkey jumper configurations paired with Glenair signature I/O connectors.



QwikConnect • January 2019

QwikConnect

Subsea: SeaKing™ and SuperG55™

SeaKing is an innovative new connector series that eliminates a broad range of mechanical design weaknesses found in many of today's high-pressure subsea connectors. From its double O-ring seals and retractable engaging nut, to its multi-keyed mating interface, the SeaKing represents a bold new approach to 10K psi open-face subsea power and signal connectivity. The SuperG55 family of dry-mate underwater connectors is a revolutionary new design of the popular industry-standard marine interconnect used in countless ROV, underwater camera, diver communications, lights, pan and tilts, and other subsea applications.

PowerTrip™ Next-Generation Power Connector

Series 970 connectors fill the need for a military grade harsh environment power connector with improved mechanical, environmental and electrical performance. PowerTrip™ also delivers reduced size and weight compared to lower-density 5015 type power connectors. Featuring triple start mating threads, crimp rear-release contacts, upgraded finish choices and improved EMI protection, the PowerTrip™ connector is ideal for power distribution units, hybrid electric drives, motors, and other high current, high-reliability applications.

SuperNine® Advanced Performance D38999

The Series 23 SuperNine® advanced performance connector series rolls up many of the technology advances Glenair has pioneered in our environmental, hermetic, and filter connectors into a comprehensive high-performance MIL-DTL-38999 Series III solution. SuperNine® combines advanced plating, sealing and other high-performance features including crimp-contact hermetics, integrated EMI shield banding porch, high-durability anti-vibration coupling and more.

Series 80 Mighty Mouse Connectors

Glenair has recognized a growing need in tactical military, aerospace and specialty industrial markets for a connector series that mimics the electrical and mechanical performance of popular mil-standard connectors, such as MIL-DTL-38999, but in a smaller and lighter package. The Series 80 Mighty Mouse Connector is perfectly suited for the wide range of power and signal applications that depend on reliable environmental and mechanical performance and electromagnetic compatibility as well as high-speed applications such as gigabit Ethernet. At just half the size and weight of D38999, the high-performance Mighty Mouse is now specified on hundreds of mission-critical interconnect applications worldwide and has become the de facto high-performance connector solution for many former users of D38999.

SuperFly® Nanominiature Circular

Glenair Series 88 SuperFly® represents a perfect storm of high-performance contacts, shells, wires, termination and mating technologies. SuperFly® is the only connector series in existence that combines the weight saving and performance advantages of nanominiature, microminiature, and AS39029 type (size #23) contacts in a hybrid package for battlefield communications, high-speed datalink computing, and other high-performance applications. Available in factory-terminated cordsets, single-ended pigtails, and PCB termination receptacles for complete flexibility in cable and box configurations.





Introduction to Military Standard Cylindrical Connectors

The purpose of a connector is easy to describe: connectors bridge gaps between individual pieces of electronic equipment to make assembly, repair and upgrades easier. Instead of struggling with a gordian knot of soldered circuits and spliced wiring, connectors enable technicians to make interconnections with ease and convenience.

Connectors bridge the gap between individual wires to provide contact between two conductive elements of an electronic system. The connection they make enables electrical current (or light waves in the case of fiber optics) to flow from one conductor to the next. Edward's Publishing's indispensable Encyclopedia of Connectors defines the connector thus: "An electromechanical device which permits two or more circuit elements to be electrically and mechanically separated and reconnected at will without disturbing any other elements of the circuit. A connector performs no circuit function and should have no effect on the electrical performance of the device to which it is attached. If the connectors of a device were eliminated and the corresponding wires joined together, the circuit would not be affected."

When connectors are used to connect one set of wires to another, they are called wire-to-wire connectors. Wire-to-board connectors connect a wire to a Printed Circuit Board (PCB). And board-to-board connectors directly interconnect PCBs.



Connector testing is designed to simulate a lifetime of use over a short period of time. Environmental, mechanical and electrical tests are conducted to measure both the reliability of the connector and the system. The number-one criterion of reliability is a change in contact resistance.

10

Connectors facilitate fabrication and assembly of electronic products by enabling designers to treat each subassembly as a unique, modular unit. Interconnection can then be accomplished at the most convenient time and place in the production process. Connectors also facilitate equipment repair by allowing technicians to quickly and easily replace suspect components. Without opening black box cabinets and without introducing contaminants like solder and flux into the system, technicians can swap out suspect equipment and have a system back on line in a matter of minutes. Connectors also permit upgrades to electronic equipment without major disruptions to the overall system. Connectors give engineers the flexibility to integrate new products and components into existing systems simply by maintaining a consistent connector specification.

While there is great variety in the makeup and design of each type of connector, as a family they generally share a common set of design elements and component parts. In fact, in order to function as a separable interconnect device, a connector must house the following elements:

- Contact Interface: a mechanical means of joining the conductive contacts together under normal force
- Contact Spring Members: a means of generating the normal force required to maintain the electrical path between conductive contact elements
- Contact Finish: a means of protecting the contacts from corrosion, and for optimizing the lubricity and durability of the contact interface
- Contact Housing: a means of holding the contacts and spring members in place and maintaining their exact position and alignment. The contact housing also shields the contacts from the operating environment.

Connectors are selected with consideration to electrical, mechanical and environmental requirements. Electrical requirements include wire type and size, contact resistance, transfer impedance and current rating. Mechanical specifications, such as thermal shock, vibration and durability indicate how well a connector will perform under critical stress factors. Environmental requirements include moisture absorption, temperature resistance, corrosion and resistance to electromagnetic interference. Environmentally resistant connectors are required for interconnect systems which are

QwikConnect

subjected to fluids in combination with vibration, shock, thermal extremes and corrosion.

While the same basic connector design may be used for both signal and/or power distribution, power connectors use contacts designed specifically for the unique requirements of power distribution. This is due to the relatively higher current/voltage requirements of power applications and the temperature rise experienced by power connectors. A disk drive in a personal computer, for example, uses both signal and power connectors. The power connector bridges the circuit that drives the unit. The signal connector carries the digital data. While the signal and power contacts may be combined into a single connector housing, each contact type is uniquely suited for its role in transmitting either signal or power electrical energy.

The Military Standard Connector

The multi-contact electrical connector used in Air Force, Navy and other high-reliability applications is a critical subassembly within the wiring system. Military connectors find many diversified applications due to severe environments, mobility, and field repairability. The key attribute of such connectors is better reliability when compared to less expensive commercial connectors. The reliability of a system is essentially a measure of the failure rate of its components. Connectors can fail due to plug dependent mechanisms, wear mechanisms or corrosion mechanisms. Total system life, power on-hours (POH) and system on/off cycles (number of times that a product powers on and off) are important factors determining system reliability. Military standard connectors (and their commercial equivalents) are chosen for their performance and reliability even in the most severe interconnect applications.

The military standard connector is made up of two separate component assemblies known as the "plug and receptacle"

which intermate to connect wires with pin and socket contacts. Connector families are defined in this high-reliability world by the military detail specifications which spell out the exact

Power connectors carry contacts from size 4/0 to #16

Miniature contacts from size #12 to #20

High-density contacts from size #20 to #22

Ultraminiature contacts size #23


Microminiature contacts size #24

Nanominiature contacts size #30

requirements for every aspect of the connector's design and performance. Connector families are distinguished by their coupling mechanisms, physical shape, contact types, environmental classes and termination methodologies.

Plug and receptacle connector pairs are available in various mounting configurations to accommodate different levels of interconnection and different application requirements. The most common configurations are in-line (wire-to-wire) applications, or various bulkhead, chassis and enclosure mountings. In general, connectors are available to accommodate any fixed mounting or in-line requirement.

Circular connectors are selected because of their compact, rugged design and their ability to effectively seal the connector from environmental hazards. Circular connectors may incorporate bayonet couplings, threaded couplings, ball detent couplings (push/pull), and/or breech lock couplings as their mechanism for locking the mated pairs together.



Circular connector coupling technology: the ubiquitous MIL-DTL-38999 Series III circular features one of the most popular connector coupling designs, the triple-start stub ACME thread. In addition to fast and reliable mating, this threaded coupling design has the advantage of a ratcheting anti-decoupling mechanism, receptacle striping indicating full mating, and metal-to-metal bottoming between the mating pairs for reduced electrical resistance.

QwikConnect • January 2019 QwikConnect • January 2019

Rectangular connectors are selected to maximize the number of contacts possible in a restricted space. However, rectangulars are not as easily sealed against fluid damage and other environmental hazards. Spring style rack/panel couplings as well as standard jackscrew fasteners are both common coupling styles in rectangular connectors.

Both circulars and rectangulars can accommodate multiple contact types including power or high-voltage contacts, signal contacts, coaxial and triaxial contacts, or fiber-optic termini. High reliability contacts are usually made from gold plated, copper alloy material. Large diameter power contacts and solder type contacts may be either gold or silver plated copper alloy.

Crimp style contacts are preferred for all aerospace and other high-reliability applications (except those requiring a hermetic seal) due to their relative ease of assembly and maintenance. Solder type contacts are usually selected when cost is the primary consideration and repairability secondary. Solder type contacts are also used in hermetic connectors.

Installation of both crimp and solder type contact connectors requires unobstructed working room behind the connector. Rear release crimp contacts require additional working room to install the extraction tool to remove the contact. Another important design feature of crimp type contact connectors is the connector insert wire sealing grommet. The grommet provides moisture sealing around each individual wire.

The shell of a military standard circular connector is a cylinder available in a range of mating thread diameters with increments of 1/16". The shell size is determined by multiplying the mating thread diameter in inches by 16. For example, a connector with a 1.5 inch diameter mating thread is designated as a shell size 24 (1.5 X 16 = 24). Standard shell sizes range from size 8 ($\frac{1}{2}$ inch mating thread) to size 40 (2 $\frac{1}{2}$ inch thread size).

Making Sense of Connector Part Numbers

Military standard connectors are organized under specification series numbers: SAE AS50151, MIL-DTL-38999 and so on. The specification series number identifies the master document which explains everything about the particular connector family. The actual part numbers of connector components are designed to call out the physical connector type and its dimensional attributes. For example, a SAE AS50151 receptacle connector designed to be mounted on a box would have a part number such as MS3402DS28-21PY. The number can be dissected as follows:

The first 4 digits after the MS (Military Standard) designate the physical connector type, like so:

3400 - Wall mounted receptacle

3401 - In line receptacle

3402 - Box mount receptacle 3404 - Jam nut recept<u>acle</u>

3406 - Straight plug

3408 - 90° plug

3409 - 45° plug

3412 - Box mount receptacle with rear threads

The single character which follows indicates the connector service class:

D - High Shock


K - Firewall

L - High Temperature

W - General Purpose

The next character, S in our example, indicates the shell material; in this case stainless steel. The next two characters, 28 in our example, identify the shell size. The following pair of numbers, 21 in our example, identifies the contact arrangement. If this pair of characters is followed by an "S," it indicates female-style (socket) contacts. If they are followed by a "P," it indicates male contacts (Pin). The final character, Y in our example, indicates the choice of polarization keying.


That's all there is to it. While there are many part number complexities and nuances throughout the various MS connector families, they all follow the same basic approach to part number development.



Design Elements: Military Standard Connector Series

The following pages recap standard circular military connector design features for some of the more common series. Application notes and illustrations describe key mechanical aspects of each series. Readers will note that many of the descriptions call out deficiencies in design, particularly for older connector series such as 5015 and 26482.

SAE AS50151 (MIL-DTL-5015) connectors, circular, MS3100 series (solder contact) Glenair designator code B (Glenair series: IT)




Design Features:

- Threaded coupling design; eight connector configurations.
- Fifteen shell sizes—Range 8 thru 48 (.500" to 3.000" diameter).
- Wide variety of power and signal contact sizes (#4/0 to #20), standard density; 1 to 100 contacts.
- Conductive finish—Cadmium/Olive drab, 96-hour corrosion protection (standard).

Application Notes:

- 1. Contacts may mate prior to connector shell mating.
- 2. Single keying may not always ensure shell polarizing.
- 3. Uncontrolled accessory interface.
- 4. Plug or receptacle may have pin or socket contacts.
- 5. Connector shell may strike pin contacts, thus power should always be on socket contacts.

SAE AS50151 connectors, circular MS3400 (front-release crimp contact) and MS3450 (rear-release crimp contact) Glenair designator code A



Design Features:


- Threaded coupling design, captive; eight connector configurations.
- Fifteen shell sizes—Range 8 thru 48 (.500" to 3.000" diameter).
- Wide variety of contact sizes (#4/0 to #20), standard density; 1 to 100 contacts.
- Cadmium/Olive drab conductive finish, 500 hour salt spray; electroless-nickel options (standard).

Application Notes:

- Same interface features as MS3100 and MS3106; intermateable.
- 2. Single keying may not always ensure shell polarizing.

QwikConnect • January 2019 QwikConnect • January 2019

MIL-DTL-26482 connectors, circular MS3110 and MS3116 Series 1 (solder contact) Glenair designator code D (Glenair series: IPT)




Design Features:

- Bayonet coupling, quick disconnect plug and receptacle
- Ten shell sizes—Range 6 through 24 (.3750" to 1.500" diameter).
- 3 to 61 standard density #12, #16, and #20 contacts.
- Conductive and non-conductive finishes; Cadmium/Olive drab and anodic.

Notes:

- 1. Contacts may mate prior to connector shell mating.
- 2. Plug may have less than three threads.

MIL-C-26482 Connectors, Circular, MS3470 Series 2 (rear-release crimp contacts) Glenair Designator Code A




Design Features:

14

- Bayonet coupling design, quick disconnect.

 Seven receptacle designs and two plug designs
 (including RFI shielded)
- Nine shell sizes—8 through 24 (.500" to 1.500" dia)
- 3 to 61 standard-density #12, #16, #20, and #22 contacts.

MIL-C-26482 Connectors, Circular, MS3120 and MS3126 Series 1 (frontrelease crimp contacts) Glenair designator code D (Glenair series IPT SE)




Design Features:

- Bayonet coupling, quick disconnect plug and receptacle.
- Eight shell sizes—Range 8 thru 24 (.500" to 1.500" dia.)
- 3 to 61 standard density #12, #16, #20, and #22 contacts.

Application Notes:

- 1. Contacts may mate prior to connector shell mating when grounding fingers not supplied.
- 2. Same limitations as MS3110/MS3116 solder connectors.
- 3. Uncontrolled wire seal grommet geometry; accessories properly mate.


MIL-DTL-28840 Connectors, Circular (front-release crimp contacts) Glenair designator code G



Design Features:

- Threaded coupling design, rapid advance, captive, scoop proof; five connector designs
- Nine shell sizes—Range 11 through 33 (.500 to 2.000 diameter).
- 7 to 155 #20 gauge high density contacts.

MIL-DTL-38999 Connectors, Series I (rear-release crimp contacts) Glenair designator code F (Glenair series 231-105) MIL-DTL-38999 Connectors, Series II (rear-release crimp contacts) Glenair designator code F (Glenair series 232-105*)




Design Features:

- Bayonet coupling design, quick disconnect.
- Nine shell sizes—Range 8 through 24 (.500" to 1.500" diameter); twelve connector styles.
- #8, #10, #12, #16, #20, and #22 standard-density; #22 high-density arrangements; 3 to 128 contacts.
- Scoop-proof shell design to prevent shell-to-contact problem.
- Controlled accessory interface per MIL-DTL-38999, figure II.
- Cork-and-bottle primary insert interface seal and shell environmental seal, fuel-resistant silicone elastomers.
- Conductive and non-conductive finishes; electroless nickel, Cadmium/Olive drab 500 hour salt spray, and anodic.

Notes:

- Long scoop-proof barrel design to prevent shell striking contacts.
- 2. Serrated accessory interlocking tooth design may prevent reliable moisture seal or EMI bond to accessories.
- 3. Bayonet coupling may not perform under severe conditions with large diameter cable and backshell.



Design Features:

- Bayonet coupling design, quick disconnect, captive.
- Nine shell sizes—Range 8 through 24 (.500" to 1.500" diameter); Fifteen connector designs.
- #16, #20, and #22 contacts, standard density and #22 high-density arrangements; 3 to 128 contacts.
- Shell ground available on MS and commercial part numbers.
- Controlled accessory interface per MIL-DTL-38999 fig. II.
- Cork-and-bottle primary interface and shell environmental seals, fluid-resistant silicone elastomers.
- Conductive and non-conductive finishes; electroless nickel, Cadmium/Olive drab, 500-hour salt spray, and anodic.
- Short barrel construction for minimum envelope.


notes:

- 1. Very short barrel, shell may strike pin contacts.
- 2. Wire seal grommet controlled to maximum condition only, over compression will cause contact splaying.
- 3. Same limitations as D38999 Series I.

* In development

MIL-DTL-38999 connectors, Series III circular, rear-release crimp contacts; Glenair code H (Mil-qualified and commercial versions available from Glenair)

MIL-DTL-38999 connectors, Series IV circular, rear-release crimp contacts; Glenair code H (Mil-qualified and commercial versions available from Glenair)





Design Features:

- Threaded coupling design, rapid advance, self-locking.
- Nine shell sizes—Range 9 through 25 (.500" to 1.500" diameter). Thirteen connector designs.
- #8, #10, #12, #16, #20, and #22 contacts, standard density and #22 high-density arrangements; 3 to 128 contacts.
- #16 fiber-optic insert arrangement.
- Scoop-proof shell design to prevent shell to contact problem.
- Controlled accessory interface with metric threads.
- Diaphragm contact seal interface and shell environmental seal, fluid resistant fluorosilicone elastomers
- Conductive and non-conductive finishes; Cadmium/Olive drab 500 hour salt spray, electroless nickel, anodic and stainless steel.
- Conductive composite shell, cadmium/olive drab over electroless nickel, and electroless nickel, 2000 hour salt spray.

Notes:

- 1. Same accessory mating interface as MIL-DTL-38999 Series I, except metric threads.
- 2. 100 percent scoop proof, positive shell mating.





ccessory

Interlock 100° Teeth Circumferentia

Shell Grounding

Design Features:

- Breech lock coupling design, rapid advance, self-locking.
- Eight shell sizes—Range 11 through 25 (.500" to 1.500" diameter).
- #12, #16, #20, and #22 contacts, standard density and #22 high density arrangements; 3 to 128 contacts.
- #16 fiber optic insert arrangements.
- Scoop-proof shell design to prevent shell-to-contact problems.
- Controlled accessory interface with metric threads.
- Ruggedized construction for shipboard service.
- Cork and bottle primary interface and shell environmental seals, fluid resistant fluorosilicone elastomers.
- Conductive and non-conductive finishes; Cadmium/Olive drab 500 hour salt spray, electroless nickel, anodic, and stainless steel.

Notes:

- 1. 100 percent scoop-proof, positive shell mating.
- 2. Same accessory interlock teeth as MIL-DTL-38999, Series III.
- 3. Same O-ring seal features as MIL-DTL-38999, Series III.

QwikConnect

Center-to-Center Contact Densities in Cylindrical and Rectangular Connectors

	Ce	enter-to-Center Co	ntact Distance	es: Ci	rcular C	onnect	ors
/	Туре	Connector Spec.	Ins. Arr. Spec.	Max Shell Size	Max # of Contacts	Contact Size	Center-to-Center
2		MIL-DTL-5015	MIL-STD-1651	48	85	16	0.241" (6.1 mm)
	Standard	MIL-DTL-22992	MIL-STD-1651	44	104	16	0.193" (4.9 mm)
	Stalluaru	VG95234	MIL-STD-1651	26	52	16	0.203" (5.2 mm)
		MIL-DTL-28840	MIL-STD-1698	33	155	20	0.114" (2.9 mm)
		MIL-DTL-26482	MIL-STD-1669	24	61	20	0.135" (3.4 mm)
י	Miniature	MIL-DTL-26500	MIL-STD-1554	24	61	20	0.131" (3.3 mm)
		MIL-DTL-83723	MIL-STD-1554	24	61	20	0.131" (3.3 mm)
U	Subminiature	MIL-DTL-38999	MIL-STD-1560	25	128	22D	0.095" (2.4 mm)
	Subminiature	MIL-DTL-38999 HD	MIL-STD-1560	25	187	23	0.080" (2.0 mm)
	Ultra-miniature	Series 80 Mighty Mouse	N/A	23	130	23	0.076" (1.9 mm)
	Nanominiature	Series 89 Nano Circular	IAW MIL-DTL-32139	4	55	30/32	0.025" (0.6 mm)

Standard	Miniature	Subminiature	Subminiature HD	Ultraminiature	Nanominiature
	0.000000000000000000000000000000000000			000000 0000000 00000000 00000000 000000	
MIL-DTL-5015 MIL-DTL-22992 VG95234 (ITS)	MIL-DTL-26482	MIL-DTL-38999	MIL-DTL-38999 High-Density	Series 80 Mighty Mouse	Series 89 Nano Circular
MIL-DTL-28840					
Arrangement shown:	Arrangement shown:	Arrangement shown:	Arrangement shown:	Arrangement shown:	Arrangement shown:
24-A55 • 55 #20 Contacts	22-55 • 55 #20 Contacts	E35 • 55 #22D Contacts	15-23 • 55 #23 Contacts	16-55 • 55 #23 Contacts	4-55 • 55 1 Amp Contacts

	\`A	A						
Center-to-Center Contact Distances: Rectangular Connectors								
Туре	Connector Spec.	Max # of Contacts	Contact Size	Center-to-Center				
D-Sub	M24308	104	20/22	0.109" (2.8 mm)				
Series 79	Series 790	102	23	0.076" (1.9mm)				
Rectangular Micro	MIL-DTL-83513	100	24/26	0.050" (1.3 mm)				
Rectangular Nano	MIL-DTL-32139	51	30/32	0.025" (0.6 mm)				



QwikConnect • January 2019

Wire Gauge Size and Composition Reference Table

Companibling Data									
		Individual Strand	Copper Wire Data Maximum		esistance (Ohms per 1	000 tt @ 20°C			
Wire Size AWG	Stranding No. /	Diameter	Diameter						
	AWG of Strands	in (mm)	in (mm)	Silver Coated	Nickel Coated	Tin Coated			
32	1/32	0.0080 (0.20)	0.009 (0.23)	169	175	178			
32	7/40	0.0031 (0.08)	0.011 (0.28)	173	185	189			
30	1.30	0.0100 (0.25)	0.011 (0.28)	108	112	116			
30	7/38	0.0040 (0.10)	0.013 (0.33)	100.7	110.7	114.1			
28	1/28	0.0126 (0.32)	0.013 (0.33)	68.0	70.0	71.6			
28	7/36	0.0050 (0.13)	0.016 (0.41)	63.8	43.8	45.3			
26	1/26	0.0159 (0.40)	0.017 (0.43)	42.7	43.8	43.4			
26	7/34	0.0063 (0.16)	0.020 (0.51)	40.5	43.1	43.4			
26	19/38	0.0040 (0.10)	0.022 (0.56)	38.4	42.2	41.3			
24	1/24	0.0201 (0.51)	0.022 (0.56)	26.8	27.4	27.8			
24	7/32	0.0080 (0.20)	0.025 (0.64)	25.2	26.5	27.0			
24	19/36	0.0050 (0.13)	0.027 (0.69)	24.3	25.9	26.2			
22	1/2-2	0.0253 (0.64)	0.026 (0.66)	17.0	18.7	17.7			
22	7/30	0.0100 (0.25)	0.031 (0.79)	15.9	16.6	17.1			
22	19/34	0.0063 (0.16)	0.033 (0.84)	15.1	16.0	16.2			
20	1/20	0.0320 (0.81)	0.033 (0.84)	10.5	10.7	10.9			
20	7/28	0.0126 (0.32)	0.039 (0.99)	10.0	10.4	10.7			
20	10/30	0.0100 (0.25)	0.040 (1.02)	11.3	11.8	12.1			
20	19/32	0.0080 (0.20)	0.041 (1.04)	9.19	9.19 9.77				
18	1/18	0.0403 (1.02)	0.041 (1.04)	6.60	6.70	6.90			
18	7/26	0.0159 (0.40)	0.050 (1.27)	6.28	6.50	6.70			
18	16/30	0.0100 (0.25)	0.051 (1.30)	6.30	6.60	6.80			
18	19/30	0.0100 (0.25)	0.052 (1.32)	5.79	6.10	6.23			
16	1/16	0.0508 (1.29)	0.052 (1.32)	4.20	4.35	4.36			
16	19/29	0.0113 (0.29)	0.059 (1.50)	4.52	4.76	4.80			
16	26/30	0.0100 (0.25)	0.062 (1.57)	4.31	4.55	4.69			
14	1/14	0.0641 (1.63)	0.065 (1.65)	2.58	2.67	2.68			
14	191/27	0.0142 (0.36)	0.073 (1.85)	2.88	3.00	3.06			
14	41/30	0.0100 (0.25)	0.081 (2.06)	2.74	2.85	2.94			
12	1/12	0.0808 (2.05)	0.082 (2.08)	1.62	1.68	1.69			
12	19/25	0.0179 (0.45)	0.093 (2.36)	1.81	1.88	1.92			
12	37/28	0.0126 (0.32)	0.091 (2.31)	1.90	1.98	2.02			
12	65/30	0.0100 (0.25)	0.099 (2.51)	1.73	1.80	1.85			
10	1.10	0.1019 (2.59)	0.103 (2.62)	1.02	1.05	1.06			
10	37/26	0.0159 (0.40)	0.115 (2.92)	1.1	1.24	1.26			
10	105/30	0.0100 (0.25)	0.130 (3.30)	1.07	1.11	1.15			
8	133/29	0.0113 (0.29)	0.173 (4.39)	0.658	0.694	0.701			

QwikConnect

Wire Bundle Diameter Calculator

Calculating Wire Bundle Diameter

When calculating wire bundle diameters, note that the gauge of the wire describes only the diameter of the metal conductor, and not the overall diameter including insulation and/or braids. Refer to the appropriate wire specification for the actual diameter of the wire for use in the following calculations.

	Steps	Calculations					
	(1a) Determine average wire diameter when all wires are the same diameter; or	Given 30 Wires @ .045 DIA Avg. Wire DIA = .045					
Đ	(1b) Determine average wire diameter when wires are different diameters.	Given 15 Wires @ .045 and 15 Wires @ .135 15 x .045 = .68 15 x .135 = <u>2.03</u> + <u>2.71</u> = .090 Avg. Wire DIA = 2.71					
	(2) Multiply average wire diameter by factor from Table I below	(1a) .045 x 6.5 = .2925 Core Wire Bundle DIA (1b) .090 x 6.5 = .585 Core Wire Bundle DIA					
	(3) Add thickness of any shielding or jacketing to core wire bundle diameter (for example, add, 0.75 for braided sleeving.	(1a) .2925 + .025 = .3175 Wire Bundle Outside DIA (1b) .585 + .025 = .61 Wire Bundle Outside DIA					

	Table I																	
No. of Wires	1	2	3	4	5	6	7	8	9	10	12	14	16	18	20	24	28	32
Factor	1.0	2.0	2.2	2.4	2.7	2.9	3.0	3.3	3.8	4.0	4.3	4.6	5.0	5.3	5.6	6.0	6.5	6.9
No. of Wires	36	40	45	50	55	60	65	70	75	80	90	100	125	150	175	200	250	300
Factor	7.4	7.7	8.1	8.5	8.9	9.3	9.7	10.1	10.5	10.9	11.6	12.2	13.7	15.0	16.1	17.2	19.3	21.0

Understanding Wire Gauge [Ga]

add .025 for braided sleeving

A traditional unit measuring the diameter (or the cross-sectional area) of a wire. Various wire gauge scales have been used in the U.S. and Britain. In traditional scales, larger gauge numbers represent thinner wires. (For very thick wires,

B

₮

repeated zeros are used instead of negative numbers, so gauges 00, 000, and 0000 represent -1, -2, and -3, respectively.) In the American Wire Gauge (AWG) scale, 0000 gauge represents a wire having a diameter of 0.46 inch and 36 gauge represents a diameter of 0.005 inch (5 mils). Diameters for the other gauges are obtained by geometric interpolation, meaning that the ratio between successive diameters is a constant, except for necessary roundoff. Thus n gauge wire has a diameter of .005-92((36-n)/39) inch. The metric wire gauge number is equal to 10 times the diameter of the wire, in millimeters; thus a metric 8 gauge wire has diameter 0.8 millimeters.

 \oplus

Scoop-Proof Contact Protection

The scoop-proof connector shell design solves problems associated with mating plugs and receptacles in less than ideal conditions, such as in the dark, from an awkward angle, or in the case of the illustrations below, in a blind-mate application. Scoop-proof connectors feature a long shell on the receptacle side which prevents mechanical damage of exposed pin contacts from the nose of the plug during mating. As Dick Holden explained it, "no matter how hard that swabbie tries, it is impossible to cock the mating plug so as to damage the pins or electrically short the contacts." This scoop-proof design feature, common to most aerospace-grade connectors such as D38999 Series III, works hand-in-hand with the interlocking keys and keyways machined into the connector mating interfaces such that even if connector halves are brought together offset or at an angle, the plug and receptacle can only ever mate in the correct orientation. The drawings below show a blind-mate connector pair (no coupling nut on the plug) that takes advantage of keying and scoop-proof design features to ensure reliable mating. The top picture shows the plug's initial engagement with the receptacle, guided home by the keys and keyways. The bottom illustration shows the utility of the scoop-proof receptacle shell in preventing pin damage.




Figure 1: Key and keyway engagement ensures polarized mating and axial alignment






Figure 2: Scoop-proof design feature prevents badly-angled plug nose from striking the pin contacts

QwikConnect

Anatomy of a Crimp-Contact Circular Connector

All modern-day crimp-contact connectors share the same basic anatomy (component parts and construction). Exploded views shown here are Glenair Series 80 Mighty Mouse connectors.





NASA / ESA SCREENING

Outgassing Properties and Requirements

Space-grade interconnect manufacturing and test capability

Outgassing and Inspection Modification Codes

Outgassing

Space flight equipment requires lowoutgassing components in order to prevent degradation to optics and other sensitive instruments. High-performance circular and rectangular connectors contain non-metallic materials such as rubber, plastic, adhesives and potting compounds which can give off condensable materials when subjected to a vacuum or high heat. Unless the connector is specially processed, the amount of condensable material outgassed can exceed allowable limits. The space industry has adopted a standardized test procedure, ASTM E595, to evaulate outgassing properties. The MIL-DTL-38999 specification Class G also details specific outgassing values. In Glenair's 186T process, connectors and connector materials are heated to 175° C at a vacuum of 5 X 10⁻⁶ Torr for 48 hours. Items under test are then weighed to calculate the Total Mass Loss (TML), which may not exceed 1.0% of the total initial mass. A collector plate is used to determine the Collected Volatile Condensable Material (CVCM), which may not exceed 0.1% of the total original specimen mass. Glenair is able to offer outgas processing which assures all materials comply with their respective standards.

Note on Connector Material and Finish Options

Some types of metals are prohibited for space flight. "Pure Tin, Cadmium, Zinc shall not be used as a final finish on EEE part (NASA EEE-INST-002 Instructions for EEE Parts Selection, Screening, Qualification, and Derating). NASA recommends electroless nickel or gold finish on connector shells and gold finish for contacts.

Specifying Appropriate NASA Screening

Choose a NASA EEE-INST-002 Table 2A screening level. This table contains three screening levels: Level 1 for missions requiring the highest reliability and lowest level of risk, Level 2 for low to moderate risk missions, and Level 3 missions where enhanced screening and inspection is not invoked.

2Choose outgassing process and/or NASA inspection requirements. 7 options are available for NASA outgassing, see Table I for details. Cross reference Table II for inspections completed by screening level as required by NASA standards.

3 Select the modification code from the table and add it to the part number. Example for a SuperNine Blind-Mate Plug, 253-016-00ME25-35PNMS-429C.

Table I: Outgassing per NASA Screening Levels and D38999, Class G

Screening Level	No Outgas Processing	48 Hour Oven Bake 175° C 100%	Thermal Vacuum* Outgassing 24 Hour 125° C 100%	Thermal Vacuum* Outgassing 48 Hour 175° C 100%	Mod Code
D38999, Class G (no screenining)				•	186T
3			•		429L
	•				429
2			•		429A
		•			429K
	•				429B
1			•		429C
		•			429J
-					

*Thermal vacuum of 10⁻⁶ Torr.

Table II: NASA EEE-INST-02, Table 2A Screening Levels

Inspection	Level 1	Level 2	Level 3
Visual	100%	100%	100%
Mechanical	2	2	
Dielectric Withstanding Voltage	2	2	
Insulation Resistance	2	2	
Contact Engagement & Separation Force	2		
Hermeticity (Sealed Receptacles Only)	100%	100%	100%
Coupling Force	2		

Note: required inspection quantity shown. Zero acceptance of failures allowed for all quantities inspected. Inspection is not performed/required for MIL-DTL-38999, Class G

QwikConnect • January 2019

QwikConnect

International Standards IP Protection Classification

International Protection Marking IEC standard 60529, or IP Code, classifies and rates the degree of ingress protection provided against foreign objects, dust, and water by mechanical casings and electrical enclosures.

	against foreign objects, dust, and water by mechanical casings and electrical enclosures.									
Fi	rst Numeral: Sc	olid Particle Prote	ection		Second Numeral: Liquid Ingress Protection					
IP		Effective Agains			IP			Effective Against		ription
0		-	No Protection		0			_	No Pro	otection
1		objects >50 mm	Protected against objec 50 mm in diameter (larg of the body such as the of hand)	e areas	1			Dripping water	drops or rain	ted against vertically falling of water, (e.g. condensation ifall), test equivalent to 1mm l/minute
2		>12.5 mm	Protected against solid over 12.5 mm in diamete (contact with fingers)		2			Dripping water when tilted at 15°	drippi tilted 1	eted against vertically ng of water, enclosure 15°. Four positions tested, alent to 3mm water/minute
3	-	>2.5 mm	Protected against solid (e.g. tools, wires) over 2. in diameter		3		:	Spraying water	from v	rted against sprays up to , 60° vertical. Tested 1 minute/sq. m ninutes.
4		>1mm	Protected against objec 1 mm in diameter (e.g. n wires, sleder screws)		4		: •	Splashing water	has no	splashing from any direction b harmful effect. 10-minute lus 5 minute test with shield red.
5		Dust protected	Protected against dust (ingress, no harmful dep		5		Ħ	Water jets	directi	ressure jets of water from all ions have no harmful effect ute test, 1 min./sq. m
6		Dust tight	Totally protected agains A vacuum must be appl test up to 8 hours based air flow.	ied,	6			Powerful water jets	water	rted against strong jets of from any direction, 100 l / or at least 3 min.
) `	Θ Θ Θ	Θ Θ		Θ	7			Immersion up to 1m		ction against ingress of water mful quantity, 1m, 30 min.
∃		9	$/$ \setminus_{Θ} \ominus \ominus	Θ	8		<u></u>	Immersion, continuous, 1m+		on and depth by agreement nanufacturer, generally 3m
(2	Θ/		Evam	nle l	P Rating		1 0 0		
lf t	he 1st IP number	r is ar	nd the 2nd IP number is	LAGIII		n the IP ra	tina is			
6		7			IP 6		<u> </u>			
	st tight		nmersion up to 1m		Tota			inst dust; protected again	st dama	age from water ingress
				Leve	s of	Sealing				
	Connecto	or Type	Seal Rating			Method		Typical Shell Material		Contact Material
	Dust Ti		3		ner a	nd/or epox	ку	Aluminum or Plastic		BeCu/Brass/others
	Environm	nental	IP 66	Elastor	ner a	nd/or epox	ку	Aluminum or Plastic		BeCu/Brass/others
	Environm	nental	IP 67	Elastor	ner a	nd/or epox	ку	Aluminum or Plastic		BeCu/Brass/others
	Environm	nental	IP 68	Elastor	ner a	nd/or epox	ку	Aluminum or Plastic		BeCu/Brass/others
	Semi-Hermetic (-4	491 Mod Code)	1 X 10 ⁻⁴ Epoxy Special			inum		Special		
	Herme	etic	1 X 10 ⁻⁴		•	t) to Metal		Aluminum		BeCu/other
	Herme	etic	1 X 10 ⁻⁶	G	lass to Metal			Cold Rolled Steel or Titanium		Alloy 52 or Kovar

CODE RED Encapsulant

Glass to Metal

Glass to Metal

Aluminum

Stainless Steel or Kovar

Inconel or Stainless Steel

1 X 10⁻¹⁰
Hermetic leak rate = CC He/Sec

1 X 10

1 X 10 -8

Hermetic

Hermetic

Hermetic

Gold-plated Copper

Alloy 52 or Kovar

Inconel or Stainless Steel

Common Modifications to Standard MS Type Connectors



Integrated Band and Boot Porch



Modular Insert Architecture for High-Speed



Space-Grade Plating and **Outgas Processing**




Solder or Weld-Mount Flange Modifications



Unique Coupling Nut Castellations and Coatings



Pure Gas Tube and Pitot Tube Contact Integration





High Density Contact Arrangements



Blind Mate / **QDC** Coupling




TBH's Panel Thickness Modifications



Interface and Sealing Modifications for High-Voltage



High-Temperature Shells and Inserts





Guide Pin Incorporation for Axial Alignment



Non-Standard MS Couplings such as Push-Pulls



Back Potting for Advanced Environmental Sealing



Auxiliary Ground Spring Integration



Flange Modifications



PC Tail Length and Diameter Modifications



Anti-mismating and Polarization Keys / Lobes



Bulkhead Penetrators



Integrated Flex **Circuit Terminations**



Gender Changers and Other Unique Connector Savers



Anti-Demate **Locking Collars**



Hybrid Power / Signal **Contact Layouts**



Integrated EMI Filtering and EMP Diodes



Anti-Vibration and Shock **PCB Standoffs**



High-Speed Datalink and RF **Contact Layouts**



RJ45 and USB 3.0 Field Connector Modifications



O-Ring Equipped Panel and Box **Mount Designs**

QwikConnect

Military Standard Circular Connector Index

The following is a listing of circular connectors defined by US Military Specifications, cross-referenced to the applicable active or inactive part number series. The symbols in the Connector Designator column are an essential element in Glenair's backshell part number developments.

PART NO.	CONN. DESIGN.	SPECIFICATION	SERIES	DESCRIPTION
MS3100	В	SAE AS50151	MS3100	Receptacle Wall Mount (Solder). Superseded by SAE-AS31001
MS3101	В	SAE AS50151	MS3100	Plug (Solder). Superseded by SAE-AS31011
MS3102	**	SAE AS50151	MS3100	Receptacle Box Mount (Solder). Superseded by SAE-AS31021
MS3103	**	SAE AS50151	MS3100	Receptacle Potting (Solder). Superseded by SAE-AS31031
MS3105	**	SAE AS50151	MS3100	Dummy Receptacle. Superseded by SAE-AS31051
MS3106	В	SAE AS50151	MS3100	Plug Straight (Solder). Superseded by SAE-AS31061
MS3107	В	SAE AS50151	MS3100	Plug Quick Disconnect (Solder). Superseded by SAE-AS31070
MS3108	В	SAE AS50151	MS3100	Plug 90° (Solder). Superseded by SAE-AS31081
MS3110	D-729	MIL-DTL-26482	1	Receptacle Wall Mount
MS3111	D	MIL-DTL-26482	1	Plug Cable Connecting
MS3112	**	MIL-DTL-26482	1	Receptacle Box Mount
MS3113	**	MIL-DTL-26482	1	Receptacle Solder Mount
MS3114	D-717	MIL-DTL-26482	1	Receptacle Jam Nut
MS3115	**	MIL-DTL-26482	1-2	Dummy Receptacle
MS3116	D	MIL-DTL-26482	1	Plug Straight
MS3119	**	MIL-DTL-26482	1	Receptacle Thru-Bulkhead
MS3120	D	MIL-DTL-26482	1	Receptacle Wall Mount (Crimp)
MS3121	D	MIL-DTL-26482	1	Plug Straight (Crimp)
MS3122	**	MIL-DTL-26482	1	Receptacle Box Mount (Crimp)
MS3124	D-717	MIL-DTL-26482	1	Receptacle Rear Mount Jam Nut (Crimp)
MS3126	D	MIL-DTL-26482	1	Plug Straight (Crimp)
MS3127	**	MIL-DTL-26482	1	Receptacle Box Mount (Crimp)
MS3128	D	MIL-DTL-26482	1	Receptacle Wall Mount (Crimp)
MS3130	*	SAE AS81703	1	Receptacle Push Pull Wall Mount Flange
MS3132	X-706	SAE AS81703	1	Receptacle Push Pull Box Mount
MS3134	X-706	SAE AS81703	1	Receptacle Push Pull Jam Nut
MS3135	**	SAE AS81703	1	Dummy Receptacle
MS3137	X-706	SAE AS81703	1	Plug Straight Push Pull
MS3138	X-706	SAE AS81703	1	Plug Lanyard Push Pull
MS3139	**	SAE AS81703	1	Receptacle Thru-Bulkhead (Wall Mount)
MS3140	X-706B	SAE AS81703	2	Receptacle Push Pull Wall Mount
MS3142	**	SAE AS50151	MS3100	Receptacle Hermetic Box Mount (Solder)
MS3143	**	SAE AS50151	MS3100	Receptacle Hermetic Solder Mount
MS3144	X-706B	SAE AS81703	2	Receptacle Push Pull Jam Nut
MS3145	**	SAE AS81703	3	Receptacle Hermetic Push Pull Box Mount
MS3146	**	SAE AS81703	3	Receptacle Push Pull Hermetic Solder Mount
MS3147	X-706B	SAE AS81703	2	Plug Push Pull (Crimp)
MS3148	X-706B	SAE AS81703	2	Plug Push Pull Lanyard (Crimp)
MS3149	**	SAE AS81703	3	Receptacle Push Pull Hermetic (Single-Hole Mount)
MS3400	Α	SAE AS50151	MS3400	Receptacle Wall Mount (Crimp)
* Consult Facto				ries ***Inactive for new design

^{*} Connector does not accommodate rear accessories

Military Standard Circular Connector Index

PART NO.	CONN. DESIGN.	SPECIFICATION	SERIES	DESCRIPTION
MS3401	А	SAE AS50151	MS3400	Receptacle Cable Connecting (Crimp)
MS3402	**	SAE AS50151	MS3400	Receptacle,Box Mount (Crimp)
MS3404	Α	SAE AS50151	MS3400	Receptacle Jam Nut (Crimp)
MS3406	Α	SAE AS50151	MS3400	Plug (Crimp)
MS3408	A	SAE AS50151	MS3400	Plug 90° (Crimp)
MS3409	Α	SAE AS50151	MS3400	Plug 45° (Crimp)
MS3412	Α	SAE AS50151	MS3400	Receptacle Wall Mount (Crimp)
MS3424	Α	SAE AS81703	3	Receptacle Push Pull Wall Mount
MS3440	**	MIL-DTL-26482	2	Receptacle Narrow Flange Mount (was M83723/9/10)
MS3442	**	MIL-DTL-26482	2	Receptacle Wide Flange Mount
MS3443	**	MIL-DTL-26482	2	Receptacle Solder Flange Mount
MS3445	*	SAE AS81703	2	Plug Push Pull Rack & Panel Mount
MS3446	Α	SAE AS81703	3	Plug Push Pull Rack & Panel Mount
MS3449	**	MIL-DTL-26482	2	Receptacle Push Pull Single Hole Mount
MS3450	Α	SAE AS50151	MS3450	Receptacle Wall Mount (was M83723/19/20) (Crimp)
MS3451	Α	SAE AS50151	MS3450	Receptc Cbl Connecting (was M83723/17/18) (Crimp)
MS3452	**	SAE AS50151	MS3450	Receptacle Box Mount (was M83723/21/22) (Crimp)
MS3454	Α	SAE AS50151	MS3450	Receptacle Jam Nut (Crimp)
MS3456	Α	SAE AS50151	MS3450	Plug Straight (was M83723/23/24) (Crimp)
MS3459	Α	SAE AS50151	MS3450	Plug Straight Self Locking (was M83723/52/53)
MS3463	**	SAE AS81703	3	Receptacle Push Pull (Hermetic)
MS3464	Α	SAE AS81703	3	Receptacle Push Pull Jam Nut
MS3466	**	SAE AS81703	3	Receptacle Push Pull Hermetic (Box Mount)
MS3467	Α	SAE AS81703	3	Plug Push Pull
MS3468	Α	SAE AS81703	3	Plug Push Pull Lanyard
MS3469	**	SAE AS81703	3	Receptacle Push Pull Hermetic Jam Nut
MS3470	Α	MIL-DTL-26482	2	Receptacle Narrow Flange Mount (was M83723/1/2)
MS3471	Α	MIL-DTL-26482	2	Receptacle Cable Connecting (was M83723/7/8)
MS3472	А	MIL-DTL-26482	2	Receptacle Wide Flange Mount (was M83723/3/4)
MS3473	**	MIL-DTL-26482	2	Receptacle Solder Mount Hermetic
MS3474	А	MIL-DTL-26482	2	Receptacle Rear Mount Jam Nut (was M83723/5/6)
MS3475	Α	MIL-DTL-26482	2	Plug RFI Shielded (was M83723/42/43)
MS3476	А	MIL-DTL-26482	2	Plug Straight (was M83723/13/14)
MS3477	**	MIL-DTL-26482	2	Receptacle Hermetic Box Mount
MS3479	**	MIL-DTL-26482	2	Receptacle Hermetic Rear Mount Jam Nut
MS17343	С	MIL-DTL-22992	R	Receptacle Wall Mount
MS17344	С	MIL-DTL-22992	R	Plug Straight
MS17345	С	MIL-DTL-22992	R	Plug Cable Connecting (Female)
MS17346	С	MIL-DTL-22992	R	Receptacle Box Mount
MS17347	С	MIL-DTL-22992	R	Receptacle Jam Nut
MS17348	**	MIL-DTL-22992	R	Receptacle Jam Nut Box Mount
MS18062	**	MIL-DTL-22992	R	Dummy Receptacle
MS20026	*	MIL-DTL-27599	I	Receptacle Wall Mount Solder***
MS20027	*	MIL-DTL-27599	I	Receptacle Line***
MS20028	*	MIL-DTL-27599	I	Plug Straight***
MS20029	**	MIL-DTL-27599	I	Receptacle Jam Nut Mount***
MS20030	*	MIL-DTL-27599		Receptacle Box Mount Hermetic
* Consult F	** 6	ata	mmodate rear access	ories ***Inactive for new design TYP 2 PL

PART NO.	CONN. DESIGN.	SPECIFICATION	SERIES	DESCRIPTION
MS20031	**	MIL-DTL-27599		Receptacle Jam Nut Hermetic***
MS20032	**	MIL-DTL-27599		Receptacle Solder Mount Hermetic***
MS20034	*	MIL-DTL-27599		Receptacle Wall Mount***
MS20035	*	MIL-DTL-27599		Receptacle Box Mount***
MS24264	Е	MIL-DTL-26500	FG&R	Receptacle Flange Mount*** Use MIL-DTL-83723
MS24265	Е	MIL-DTL-26500	FG&R	Receptacle Single Hole Mount*** Use MIL-DTL-83723
MS24266	Е	MIL-DTL-26500	FG&R	Plug Straight*** Use MIL-DTL-83723
MS25183	**	SAE AS50151	MS3100	Plug Potting Seal (Solder)
MS27034	**	MIL-DTL-26500		Receptacle Hermetic Solder Mount
MS27334	*	MIL-DTL-27599		Receptacle Wall Mount ***
MS27335	**	MIL-DTL-27599		Receptacle Box Mount ***
MS27336	*	MIL-DTL-27599		Plug Straight ***
MS27337	*	MIL-DTL-27599		Receptacle Jam Nut ***
MS27338	*	MIL-DTL-27599		Receptacle Wall Mount Hermetic
MS27339	**	MIL-DTL-27599		Receptacle Box Mount Hermetic
MS27340	**	MIL-DTL-27599		Receptacle Jam Nut Mount Hermetic
MS27341	**	MIL-DTL-27599		Receptacle Solder Mount Hermetic
MS27466	F	MIL-DTL-38999	1	Receptacle Wall Mount
MS27467	F	MIL-DTL-38999	I	Plug Straight
MS27468	F	MIL-DTL-38999	1	Receptacle Jam Nut
MS27469	**	MIL-DTL-38999	I	Receptacle Wall Mount Hermetic
MS27470	**	MIL-DTL-38999	1	Receptacle Jam Nut Hermetic
MS27471	**	MIL-DTL-38999	I	Receptacle Solder Mount Hermetic
MS27472	F	MIL-DTL-38999	II	Receptacle Wall Mount
MS27473	F	MIL-DTL-38999	II	Plug Straight
MS27474	F	MIL-DTL-38999	II	Receptacle Jam Nut
MS27475	F	MIL-DTL-38999	II	Receptacle Wall Mount
MS27476	**	MIL-DTL-38999	II	Receptacle Box Mount Hermetic
MS27477	**	MIL-DTL-38999	II	Receptacle Jam Nut Hermetic
MS27478	**	MIL-DTL-38999	II	Receptacle Solder Mount Hermetic
MS27479	F	MIL-DTL-38999	II	Inactive Use MS27472
MS27480	F	MIL-DTL-38999	II	Inactive Use MS27473
MS27481	F	MIL-DTL-38999	II	Inactive Use MS27474
MS27482	F	MIL-DTL-38999	II	Inactive Use MS27475
MS27483	**	MIL-DTL-38999	II	Inactive Use MS27474
MS27484P	**	MIL-DTL-38999	II	Plug Straight
MS27484T	F	MIL-DTL-38999	II	Plug Straight
MS27496	**	MIL-DTL-38999	T	Receptacle Box Mount
MS27497	F	MIL-DTL-38999	II	Receptacle Back Panel Wall Mount
MS27498	F	MIL-DTL-38999	1	Plug 90° (MS27467)
MS27499	**	MIL-DTL-38999	II	Receptacle Box Mount
MS27500	F	MIL-DTL-38999	II	Inactive See MS27473
MS27503	**	MIL-DTL-38999	II	Inactive See MS27478
MS27504	**	MIL-DTL-38999	II	Inactive See MS27499
MS27505	**	MIL-DTL-38999	I	Receptacle Back Panel Box Mount
MS27508	**	MIL-DTL-38999	II	Receptacle Back Panel Box Mount
MS27513	**	MIL-DTL-38999	II	Receptacle Box Mount

^{*} Consult Factory

^{**} Connector does not accommodate rear accessories

^{***}Inactive for new design

Consult Factory ** Connector does not accommodate rear accessories

⁴⁻⁴⁰ UNC 2B T

Military Standard Circular Connector Index

PART NO.	CONN. DESIGN.	SPECIFICATION	SERIES	DESCRIPTION
MS27515	F	MIL-DTL-38999	I	Inactive Use MS27656
MS27613	E-710	MIL-DTL-26500		Receptacle Panel Mount ***Use MIL-DTL-83723
MS27614	E-710	MIL-DTL-26500		Receptacle D-Hole Mount ***Use MIL-DTL-83723
MS27615	E-710	MIL-DTL-26500		Plug Straight ***Use MIL-DTL-83723
MS27652	F	MIL-DTL-38999	I	Inactive Use MS27466
MS27653	F	MIL-DTL-38999	I	Inactive Use MS27467
MS27654	F	MIL-DTL-38999	I	Inactive Use MS27656
MS27656	F	MIL-DTL-38999	I	Receptacle Back Panel Wall Mount (MS27499)
MS27661	F-752	MIL-DTL-38999	T	Plug Lanyard Release
MS27662	**	MIL-DTL-38999	I	Receptacle Thru-Bulkhead
MS27664	**	MIL-DTL-38999	II	Receptacle Back-Panel Wall Mount
MS27665	F	MIL-DTL-38999	I	Plug Rack & Panel Mount
MS27667	**	MIL-DTL-38999	II	Receptacle Thru-Bulkhead
MS90555	*	MIL-DTL-22992	L	Receptacle Wall Mount
MS90556	*	MIL-DTL-22992	L	Plug Straight
MS90557	*	MIL-DTL-22992	L	Plug Cable Connecting
MS90558	*	MIL-DTL-22992	L	Receptacle w/Coupling Ring Wall Mount
M28840/10	G	MIL-DTL-28840		Receptacle Wall Mount
M28840/11	G	MIL-DTL-28840		Receptacle Cable Connecting
M28840/12	**	MIL-DTL-28840		Receptacle Box Mount
M28840/14	G	MIL-DTL-28840		Receptacle Jam Nut
M28840/16	G	MIL-DTL-28840		Plug Straight
D38999/20	Н	MIL-DTL-38999	III	Receptacle Wall Mount
D38999/21	**	MIL-DTL-38999	III	Receptacle Hermetic (Box Mount)
D38999/23	**	MIL-DTL-38999	III	Receptacle Hermetic Jam Nut
D38999/24	Н	MIL-DTL-38999	III	Receptacle Jam Nut
D38999/25	**	MIL-DTL-38999	III	Receptacle Hermetic Solder Mount
D38999/26	Н	MIL-DTL-38999	III	Plug Straight
D38999/27	**	MIL-DTL-38999	III	Receptacle Hermetic Weld Mount
D38999/29	H-701	MIL-DTL-38999	III	Plug Lanyard Release
D38999/30	H-701	MIL-DTL-38999	III	Plug Lanyard Release
D38999/31	Н	MIL-DTL-38999	III	Plug Lanyard Release
D38999/36	Н	MIL-DTL-38999	III	Plug Lanyard Release
D38999/40	Н	MIL-DTL-38999	IV	Receptacle Wall Mount
D38999/41	**	MIL-DTL-38999	IV	Box Mount Receptacle Hermetic
D38999/42	**	MIL-DTL-38999	IV	Receptacle Box Mount
D38999/43	Н	MIL-DTL-38999	IV	Jam Nut Mount Hermetic Receptacle
D38999/44	H-715	MIL-DTL-38999	IV	Receptacle Jam Nut
D38999/45	**	MIL-DTL-38999	IV	Solder Mount Hermetic Receptacle
D38999/46	Н	MIL-DTL-38999	IV	Plug Straight EMI
D38999/47	Н	MIL-DTL-38999	IV	Plug Straight
D38999/49	Н	MIL-DTL-38999	IV	In Line Cable Receptacle
D38999/60	Н	MIL-DTL-38999	III	Tight Tolerance Fiber Optic Plug
D38999/61	Н	MIL-DTL-38999	III	Tight Tolerance Wall Mount Fiber Optic Receptacle
M81511/1	J	SAE AS81511	2	Receptacle Flange Mount
M81511/2	**	SAE AS81511	2	Receptacle Solder Flange
M81511/3	J	SAE AS81511	2	Receptacle Jam Nut
* Consult Factor		ctor does not accommo		

	PART NO.	CONN. DESIGN.	SPECIFICATION	SERIES	DESCRIPTION
	M81511/4	**	SAE AS81511	2	Receptacle Jam Nut ***
	M81511/5	J	SAE AS81511	2	Plug Cable Connecting ***
	M81511/6	J	SAE AS81511	2	Plug ***
	M81511/21	J	SAE AS81511	1	Receptacle Flange Mount ***
	M81511/22	**	SAE AS81511	1	Receptacle Solder Flange Mount ***
	M81511/23	J	SAE AS81511	1	Receptacle Jam Nut ***
	M81511/24	**	SAE AS81511	1	Receptacle Jam Nut ***
	M81511/25	J	SAE AS81511	1	Receptacle Cable Connecting ***
	M81511/26	J	SAE AS81511	1	Plug ***
	M81511/27	**	SAE AS81511	1	Receptacle Thru-Bulkhead Jam Nut ***
	M81511/28	**	SAE AS81511	2	Receptacle Thru-Bulkhead Single Hole Mount ***
	M81511/31	J	SAE AS81511	2	Receptacle Flange Mount ***
	M81511/32	J	SAE AS81511	2	Receptacle Jam Nut Mount ***
	M81511/33	J	SAE AS81511	2	Recepacle,Cable Connecting ***
	M81511/34	J	SAE AS81511	2	Plug ***
	M81511/35	J	SAE AS81511	1	Receptacle Flange Mount ***
	M81511/36	J	SAE AS81511	1	Receptacle Jam Nut ***
	M81511/37	J	SAE AS81511	1	Receptacle Cable Connecting ***
	M81511/38	J	SAE AS81511	1	Plug ***
	M81511/41	J	SAE AS81511	3	Receptacle Flange Mount ***
	M81511/42	**	SAE AS81511	3	Receptacle Solder Flange Mount ***
	M81511/44	**	SAE AS81511	3	Receptacle Jam Nut ***
	M81511/45	J	SAE AS81511	3	Receptacle Cable Connecting ***
	M81511/46	J	SAE AS81511	3	Plug ***
7	M81511/47	**	SAE AS81511	3	Receptacle Solder Flange Mount ***
	M81511/48	**	SAE AS81511	3	Receptacle Jam Nut ***
Υ .	M81511/49	J	SAE AS81511	3	Receptacle Jam Nut ***
	M81511/50	**	SAE AS81511	4	Receptacle Jam Nut ***
	M81511/51	J **	SAE AS81511	4	Receptacle Flange Mount ***
	M81511/52		SAE AS81511	4	Receptacle Solder Flange Mount ***
	M81511/53	J	SAE AS81511	4	Receptacle Jam Nut ***
	M81511/54	**	SAE AS81511	4	Receptacle Jam Nut ***
	M81511/55	J	SAE AS81511	4	Receptacle Cable Connecting ***
	M81511/56	J	SAE AS81511	4	Plug ***
	M81511/57	**	SAE AS81511	4	Receptacle Solder Flange Mount ***
0):	M81582/1	*	SAE AS81582		Receptacle Jam Nut Mount ***
-	M81582/2	*	SAE AS81582		Plug Lanyard Release ***
	M83723/1	A	MIL-DTL-83723		Superseded by MS3470
	M83723/2	A	MIL-DTL-83723	1	Superseded by MS3470
_	M83723/3	A	MIL-DTL-83723		Superseded by MS3472
	M83723/4	A	MIL-DTL-83723	<u> </u>	Superseded by MS3472
	M83723/5	A	MIL-DTL-83723	1	Superseded by MS3474
	M83723/6	A	MIL-DTL-83723	I	Superseded by MS3474
	M83723/7	A	MIL-DTL-83723	1	Superseded by MS3471
	M83723/8	A	MIL-DTL-83723	I	Superseded by MS3471
	M83723/9	**	MIL-DTL-83723		Superseded by MS3440
	M83723/10	**	MIL-DTL-83723	I	Superseded by MS3442

^{*} Consult Factory

^{**} Connector does not accommodate rear accessories

Military Standard Circular Connector Index

PART NO.	CONN. DESIGN.	SPECIFICATION	SERIES	DESCRIPTION
M83723/11	**	MIL-DTL-83723	I	Superseded by MS3443
M83723/12	**	MIL-DTL-83723	I	Superseded by MS3443
M83723/13	Α	MIL-DTL-83723	I	Superseded by MS3476
M83723/14	A	MIL-DTL-83723	I	Superseded by MS3476
M83723/17	K	MIL-DTL-83723	II	Superseded by MS3451 ***
M83723/18	K	MIL-DTL-83723	II	Superseded by MS3451 ***
M83723/19	K	MIL-DTL-83723	II	Superseded by MS3450 ***
M83723/20	K	MIL-DTL-83723	II	Superseded by MS3450 ***
M83723/21	**	MIL-DTL-83723	II	Superseded by MS3452 ***
M83723/22	**	MIL-DTL-83723	II	Superseded by MS3452 ***
M83723/23	K	MIL-DTL-83723	II	Superseded by MS3456 ***
M83723/24	K	MIL-DTL-83723	II	Superseded by MS3456 ***
M83723/25	**	MIL-DTL-83723	II	Superseded by MS3142 ***
M83723/26	**	MIL-DTL-83723	II	Superseded by MS3143 ***
M83723/36	Α	MIL-DTL-83723	I	Inactive For New Design
M83723/37	A	MIL-DTL-83723	I	Inactive For New Design
M83723/38	A	MIL-DTL-83723	I	Inactive For New Design
M83723/39	Α	MIL-DTL-83723	I	Inactive For New Design
M83723/40	Α	MIL-DTL-83723	1	Inactive For New Design
M83723/41	A	MIL-DTL-83723	I	Inactive For New Design
M83723/42	A	MIL-DTL-83723	1	Superseded by MS3475
M83723/43	A	MIL-DTL-83723	ı	Superseded by MS3475
M83723/45	**	MIL-DTL-83723	1	Superseded by MS3115
M83723/48	A	MIL-DTL-83723	I	Inactive For New Design
M83723/49	А	MIL-DTL-83723	1	Inactive For New Design
M83723/52	K	MIL-DTL-83723	II	Superseded by MS3459
M83723/53	K	MIL-DTL-83723	II	Superseded by MS3459
M83723/66	A	MIL-DTL-83723	III	Plug Push Pull (Pin Contacts)
M83723/67	А	MIL-DTL-83723	III	Plug Push Pull (Socket Contacts)
M83723/68	A	MIL-DTL-83723	III	Plug Push Pull Lanyard (Pin Contacts)
M83723/69	Α	MIL-DTL-83723	III	Plug Push Pull Lanyard (Socket Contacts)
M83723/71	A	MIL-DTL-83723	III	Receptacle Bayonet Flange Mount (Socket Contact)
M83723/72	А	MIL-DTL-83723	III	Receptacle Bayonet Flange Mount (Pin Contact)
M83723/73	A	MIL-DTL-83723	III	Receptc Bayonet Single Hole Mount (Socket Contact)
M83723/74	А	MIL-DTL-83723	III	Receptacle Bayonet Single Mount (Pin Contact)
M83723/75	Α	MIL-DTL-83723	III	Plug Bayonet (Socket Contact)
M83723/76	Α	MIL-DTL-83723	III	Plug Bayonet (Pin Contact)
M83723/77	A	MIL-DTL-83723	III	Plug Bayonet RFI (Socket Contact)
M83723/78	Α	MIL-DTL-83723	III	Plug Bayonet RFI (Pin Contact)
M83723/79	**	MIL-DTL-83723	III	Receptacle Bayonet Flange Mount Hermetic
M83723/80	**	MIL-DTL-83723	III	Receptacle Bayonet Solder Flange Mount Hermetic
M83723/81	**	MIL-DTL-83723	III	Receptacle Bayonet Single Hole Mount Hermetic
M83723/82	Α	MIL-DTL-83723	III	Receptacle Threaded Flange Mount (Socket Contact)
M83723/83	Α	MIL-DTL-83723	III	Receptacle Threaded Flange Mount (Pin Contact)
M83723/84	Α	MIL-DTL-83723	III	Receptc Threaded Single Hole Mount (Socket Contact)
M83723/85	Α	MIL-DTL-83723	III	Receptacle Threaded Single Hole Mount (Pin Contact)
M83723/86	A	MIL-DTL-83723	III	Plug Threaded (Socket Contact)
* Consult Fact		ctor does not accommo		ories ***Inactive for new design TYP 2 PI

nsult Factory	** Connector of	loes not accomr	modate rear accessories	***Inactive for r
,				

	PARTINO.		SPECIFICATION	JENIES	DESCRIF HON
	M83723/87	Α	MIL-DTL-83723	III	Plug Threaded (Pin Contact)
	M83723/88	**	MIL-DTL-83723	III	Receptacle Threaded Flange Mount (Pin Contact)
	M83723/89	**	MIL-DTL-83723	III	Receptacle Threaded Single Hole Mount Hermetic
	M83723/90	**	MIL-DTL-83723	III	Receptacle Threaded Solder Flange Mount Hermetic
	M83723/91	Α	MIL-DTL-83723	III	Plug Threaded RFI (Socket Contact)
	M83723/92	Α	MIL-DTL-83723	III	Plug Threaded RFI (Pin Contact)
	M83723/93	**	MIL-DTL-83723	III	Receptacle Bayonet Solder Flange Mount Hermetic
	M83723/94	**	MIL-DTL-83723	III	Receptacle Bayonet Single Hole Mount Hermetic
	M83723/95	Α	MIL-DTL-83723	III	Plug Threaded (Socket Contact) Self Locking
	M83723/96	Α	MIL-DTL-83723	III	Plug Threaded (Pin Contact) Self Locking
	M83723/97	Α	MIL-DTL-83723	III	Plug Threaded RFI (Socket Contact) Self Locking
	M83723/98	Α	MIL-DTL-83723	III	Plug Threaded RFI (Pin Contact) Self Locking
	NATC00	H*	SSQ21635		Receptacle Flange
	NATC06	H*	SSQ21635		Plug
	NATC07	H*	SSQ21635		Receptacle Jam Nut
	NATC09	***	SSQ21635		Receptacle Weld Mount
	NATC77	***	SSQ21635		Receptacle Jam Nut Bulkhead Feed-Thru
	NATC99	***	SSQ21635		Receptacle Weld Mount
	NBO	Α	40M39569		Receptacle Flange Mount
	NBOH	**	40M39569		Receptacle Hermetic
	NB3H	**	40M39569		Receptacle Hermetic
	NB4	Α	40M39569		Receptacle Flange Mount
	NB5H	**	40M39569		Thru-Bulkhead Hermetic
	NB6	Α	40M39569		Plug Straight
	NB6G	Α	40M39569		Plug Straight,EMI
	NB7	Α	40M39569		Receptacle Jam Nut
	NB7H	**	40M39569		Receptacle Hermetic
	NB8H	**	40M39569		Receptacle Hermetic
	NLSO	F	40M38277		Receptacle Flange Mount
	NLS3H	**	40M38277		Receptacle Hermetic
	NLS6	F	40M38277		Plug Straight
	NLS6G	F	40M38277		Plug Straight EMI
	NLS7	F	40M38277		Receptacle Jam Nut
	NLS7H	**	40M38277		Receptacle Jam Nut
	NZGL00	H**	SSQ21635		Receptacle Flange
	NZGL03	***	SSQ21635		Receptacle Lever
).1	NZGL06	H**	SSQ21635		Plug
	NZGL07	H**	SSQ21635		Receptacle Weld Mount
	NZGL09	***	SSQ21635		Receptacle Weld Mount
	NZGL66	H**	SSQ21635		Plug
	NZGL77	***	SSQ21635		Receptacle Jam Nut
	NZGL99	***	SSQ21635		Receptacle Weld Mount
	* Consult Facto	ry ** Connec	ctor does not accommod	late rear accesso	ries ***Inactive for new design

DESCRIPTION


PART NO.

CONN. DESIGN. SPECIFICATION
















		PERFORMANCE		F (12 1() 1/450 - 40320		CONTACT T	YPE			SHELL		
MILITARY	ENVIRONMENTAL AND MATERIAL		WATER		ODEDATING	SOLDER or	CRIMP			CUELL		
SPECIFICATION	CLASS	DESCRIPTION	RESISTANCE	RESILIENT MATERIAL	OPERATING TEMP	EYELET		REAR	SIZE	SHELL MATERIAL	FINISH DESCRIPTION	COUPLING TYPE
	A	Non-Environmental Solid Shell	Moisture-proof	-	125°C	•	-	-		Aluminum	96 hr. Cad O.D.	
	В	Non-Environmental Split Shell	Moisture-proof	-	125° C	•	_	-		Aluminum	96 hr. Cad O.D.	
	С	Pressurized	Moisture-proof	_	125°C	•	_	-	16	Aluminum	96 hr. Cad O.D.	
SAE AS50151	Е	Environmental Grommet Seal	Moisture-proof	Neoprene	125°C	•	-	-	12	Aluminum	96 hr. Cad O.D.	
Solder Series I	F	Environmental Grommet Seal with Clamp	Moisture-proof	Neoprene	125°C	•	_	-	8	Aluminum	96 hr. Cad O.D.	Threaded
(IT)	HS	Hermetic	Submersible	Silicone	125°C	•	-	-	4	Stainless Steel	96 hr. Cad O.D.	
(,	Р	Environmental Potting Seal	Moisture-proof	Polyamide	125°C	•	_	-	1/0	Aluminum	96 hr. Cad O.D.	
	K	Non-Environmental Firewall	Moisture-proof	-	125°C	Non	-Removable C	rimp		Carbon Steel	96 hr. Cad O.D.	
	R	Environmental Grommet Seal with 'O' Ring	Moisture-proof	Neoprene	125°C	•	_	-		Aluminum	96 hr. Cad O.D.	
	D	Environmental High Shock	Splash-proof	Silicone	175°C	-	•	-		Aluminum	500 hr. Cad O.D.	
	DJ	Environmental High Shock	Splash-proof	Silicone	175°C	-	•	-		Aluminum	500 hr. Cad O.D.	
	DJS	Environmental High Shock	Splash-proof	Silicone	175°C	-	•	-		Stainless Steel	Black Cad	
	DS	Environmental High Shock	Splash-proof	Silicone	175°C	-	•	-		Stainless Steel	Black Cad	
SAE AS50151	K	Environmental Firewall	Submersible	Silicone	175°C	-	•	-	16	Carbon Steel	Electroless Nickel	
Crimp	KS	Environmental Firewall	Submersible	Silicone	175°C	-	•	-	12	Stainless Steel	Passivated	
Front Release	KT	Environmental Firewall	Submersible	Silicone	175°C	-	•	-	8	Carbon Steel	96 hr. Cad O.D.	Threaded
Series II	L	Environmental High Temperature	Submersible	Silicone	200°C	-	•	-	1/0	Aluminum	Electroless Nickel	
	LS	Environmental High Temperature	Submersible	Silicone	200°C	-	•	-	1, 0	Stainless Steel	Passivated	
	U	Environmental High Temperature	Splash-proof	Silicone	200°C	-	•	-		Aluminum	Electroless Nickel	
	US	Environmental High Temperature	Splash-proof	Silicone	200°C	-	•	-		Stainless Steel	Passivated	
	W	Environmental General Purpose	Splash-proof	Silicone	175°C	-	•	-		Aluminum	96 hr. Cad O.D.	
	K	Environmental Firewall	Submersible	Silicone	175°C	-	_	•		Carbon Steel	Electroless Nickel	
	KS	Environmental Firewall	Submersible	Silicone	175°C	-	-	•		Stainless	Passivated	
SAE AS50151	KT	Environmental Firewall	Submersible	Silicone	175°C	-	_	•	16	Carbon Steel	96 hr. Cad O.D.	
Crimp	L	Environmental High Temperature	Submersible	Silicone	200°C	-	-	•	12	Aluminum	Electroless Nickel	
Rear Release	LS	Environmental High Temperature	Submersible	Silicone	200°C	-	_	•	8	Stainless Steel	Passivated	Threaded
Series III	U	Environmental High Temperature	Splash-proof	Silicone	200°C	-	-	•	1/0	Aluminum	Electroless Nickel	
	US	Environmental High Temperature	Splash-proof	Silicone	200°C	-	-	•	1, 0	Stainless Steel	Passivated	
	W	Environmental General Purpose	Splash-proof	Silicone	175°C	-	-	•		Aluminum	96 hr. Cad O.D.	
MIL-C-10544	ALL	Environmental Signal Corps Audio U Series	Moisture-proof	Neoprene	125°C	Solder &	Taper Pin Tern	ninations	16	Stainless Steel	Passivated	Reverse Bayonet
MIL-DTL-12520	ALL		Moisture-proof	Neoprene	125°C	•	-	-	20 16 12 8	Aluminum	Cad O.D.	Center Lock Screw
MIL-C-22249	ALL	Environmental High Pressure Bulkhead	Submersible	Silicone	73°C	•	-	-	20 16	Stainless Steel	Passivated	Threaded
MIL-C-22539	ALL	Environmental High Pressure Bulkhead	Submersible	Dially Phthalate	73°C	•	-	-	16 12	Stainless Steel	Passivated	Threaded

	ENI//DONINGENITAL	PERFORMANCE		91110 1111 2/11-40173		CONTACT T	/PE			SHELL	>>>>		
MILITARY	ENVIRONMENTAL AND MATERIAL		WATER		OPERATING	SOLDER or	CRIMP			SHELL			
SPECIFICATION	CLASS	DESCRIPTION	RESISTANCE	RESILIENT MATERIAL	TEMP	EYELET	FRONT	REAR	SIZE	MATERIAL	FINISH DESCRIPTION	COUPLING TYPE	
	C*C*	Environmental Pressurized	Moisture-proof	Neoprene	125°C	•	-	_		Aluminum	500 hr Cad O.D		
	C*N*	Environmental Pressurized	Moisture-proof	Neoprene	125°C	_	-		16	Aluminum	Black Anodize		
MIL-DTL-22992 Class C,	J*C*	Environmental Pressurized, with Grommet	Moisture-proof	Neoprene	125°C	_	-		12	Aluminum	500 hr Cad O.D.		
J&R	J*N*	Environmental Pressurized, with Grommet	Moisture-proof	Neoprene	125°C	_	-		4	Aluminum	Black Anodize		
	R*C*	Environmental	Moisture-proof	Neoprene	125°C	_	-		1/0	Aluminum	500 hr Cad O.D.	Threaded Double	
	R*N*	Environmental	Moisture-proof	Neoprene	125°C	-	-			Aluminum	Black Anodize	Start	
MIL-DTL-22992 Class L	L (C)	Environmental, Gland Seal Backshell	Moisture-proof	Neoprene	125°C	•			6 4 2	Aluminum	500 hr Cad O.D.		
WILE-DTE-22592 Class E	L (N)	Environmental, Gland Seal Backshell	Moisture-proof	Neoprene	125°C	•			1/0 4/0	Aluminum	Black Anodize		
									16 12				
MIL-C-24217	ALL	High Pressure Bulkhead	Submersible	Silicone	75C	•	_	-	8 4	Stainless Steel	Passivated	Coupling	
									1/0				
MIL-DTL-25955	_	Environmental	Moisture-proof	Neoprene	125°C	-	•	-	20	Aluminum	Cadmium	Threaded Double	
	-	Hermetic	Moisture-proof	Neoprene	125°C	•	-	-		Carbon Steel	Tinned	Start	
	Е	Environmental with Grommet Nut	Moisture-proof	Neoprene	125°C	•	-	-		Aluminum	96 hr Cad O.D.		
AUL DTI 26402	F	Environmental with Strain Relief	Moisture-proof	Neoprene	125°C	•	-	-		Aluminum	96 hr Cad O.D.		
	H*A*	Hermetic	Moisture-proof		125°C	•			20	Stainless Steel	Passivate		
Series 1 Solder	H*B*	Hermetic	Moisture-proof		125°C	•			20	Stainless Steel	Passivate	Bayonet	
(IPT)	H*C*	Hermetic	Moisture-proof		125°C	•			12	Carbon Steel	Tinned		
	H*Y*	Hermetic	Moisture-proof		125°C	•				Carbon Steel	Tinned		
	J	Environmental Gland Seal	Moisture-proof	Neoprene	125°C	•				Aluminum	96 hr Cad O.D.		
	Р	Environmental Potting Seal	Moisture-proof	Neoprene	125°C	•				Aluminum	96 hr Cad O.D.		
MIL-DTL-26482	Е	Environmental with Grommet Nut	Moisture-proof	Neoprene	125°C	-	•	-	20	Aluminum	96 hr Cad O.D.		
Series 1 Crimp	F	Environmental with Strain Relief	Moisture-proof	Neoprene	125°C	-	•	-	16	Aluminum	96 hr Cad O.D.	Bayonet	
(IPT SE)	Р	Environmental Potting Seal	Moisture-proof	Neoprene	125°C	_	•	-	12	Aluminum	96 hr Cad O.D.		
	Α	Environmental	Submersible	Silicone	200°C	_	-	•		Aluminum	Black Anodize		
	Е	Environmental	Submersible	Silicone	175°C					Aluminum	Electroless Nickel		
	H*A*	Hermetic	Submersible	Silicone	200°C	•	-	_		Stainless Steel	Passivate		
	H*B*	Hermetic	Submersible	Silicone	200°C	•	-	-	20	Stainless Steel	Passivate		
MIL-DTL-26482	H*C*	Hermetic	Submersible	Silicone	175°C	•	-	-	16	Carbon Steel	Tinned	Bayonet	
	H*Y*	Hermetic	Submersible	Silicone	175°C	•	-	-	12	Carbon Steel	Tinned		
	L	Environmental	Submersible	Silicone	200°C	_	-	•		Aluminum	Electroless Nickel		
7	N	Hermetic	Submersible	Silicone	175°C	_	-	•		Carbon Steel	Tinned		
	W	Environmental	Submersible	Silicone	175°C	_	-	•		Aluminum	500 hr Cad O.D.		
	Е	Environmental, High Temperature	Splash-proof	Silicone	200°C	_	•	-		Stainless Steel	Passivate		
	F	Environmental, Fluid Resistant	Submersible	Silicone	175°C	_	•	-		Aluminum	Anodic Coating		
	G	Environmental, Grounding	Splash-proof	Silicone	200°C	_	•	-	20	Aluminum	Electroless Nickel		
MIL-DTL-26500	H*C	Hermetic	Splash-proof	Silicone	200°C	•	-	-	16	Carbon Steel	Tinned	Bayonet or Threaded	
	H*E	Hermetic	Splash-proof	Silicone	200°C	•	-	-	12	Carbon Steel	Tinned		
	K	Environmental, FIrewall	Splash-proof	Silicone	200°C	-	•	-		Stainless Steel	Passivate		
	R	Environmental	Splash-proof	Silicone	175°C	-	•	_		Aluminum	Black Anodize		

	ENVIRONMENTAL	PERFORMANCE				CONTACT 1	ГҮРЕ			SHELL		
MILITARY SPECIFICATION	AND MATERIAL	DESCRIPTION	WATER	RESILIENT MATERIAL	OPERATING	SOLDER or	CRIMP		SIZE	SHELL	FINISH DESCRIPTION	COUPLING TYPE
	CLASS		RESISTANCE		TEMP	EYELET	FRONT	REAR		MATERIAL		
	P*A	Potting Seal	_	None	150°C	•			22M	Aluminum	Bright/Gold Cad over Nickel	
MIL-DTL-27599	P*B	Potting Seal	_	None	150°C	•			22D	Aluminum	Bright/Gold Cad over Nickel	
Series I	T*A	Non-Environmental	_	None	175°C	•			20	Aluminum	500 hr Cad O.D.	Bayonet
	T*B	Non-Environmental	_	None	175°C	•			16 12	Aluminum	500 hr Cad O.D.	
	P*A	Potting Seal	-	None	150°C	•			22M	Aluminum	Bright/Gold Cad over Nickel	
MIL-DTL-27599	P*B	Potting Seal	_	None	150°C	•			22D	Aluminum	Bright/Gold Cad over Nickel	
Series II	T*A	Non-Environmental	_	None	175°C	•			20	Aluminum	500 hr Cad O.D.	Bayonet
	T*B	Non-Environmental	_	None	175°C	•			16 12	Aluminum	500 hr Cad O.D.	
	D	Environmental	Splash-proof	Fluorosilicone	175°C		•			Aluminum	500 hr Cad O.D. over Nickel	
MIL-DTL-28840	DS	Environmental	Splash-proof	Fluorosilicone	175°C		•		20	Stainless Steel	Stainless Steel, Cadmium- Black over Nickel	Threaded Double
	Т	Environmental	Splash-proof	Fluorosilicone	175°C		•			Aluminum	Nickel PTFE	Start
	Z	Environmental	Splash-proof	Fluorosilicone	175°C		•			Aluminum	Black Zinc Nickel	
MIL-PRF-28876	ALL	Environmental	Submersible	Fluorosilicone	65°C		Fiber Optic		-	Aluminum	500 hr Cad O.D.	Threaded
SAE AS29600	Е	Environmental	Submersible	Silicone	175°C	•			22D 22	Composite	None	
Series A	G	Environmental, Space Grade	Submersible	Silicone	175°C	•			20	Composite	Tin	Threaded Triple Start
MIL-DTL-38999 Insert	R	Environmental	Submersible	Silicone	175°C	•			16 12	Composite	Tin	
SAE AS29600	E	Environmental	Submersible	Silicone	175°C			•	23	Composite	None	
Series B	G	Environmental, Space Grade	Submersible	Silicone	175°C			•	20 16	Composite	Tin	Threaded Triple Start
SAE AS81511 Insert	R	Environmental	Submersible	Silicone	175°C			•	12	Composite	Tin	
	A	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +150°C			•		Aluminum	Cadmium - Gold/Clear Chromate	
	В	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +175°C			•		Aluminum	Cadmium - Olive-Drab Chromate	
	С	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +200°C			•		Aluminum	Hardcoat Anodize	
	F	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +200°C			•		Aluminum	Electroless Nickel	
	R	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +200°C			•	23	Aluminum	Electroless Nickel	
MIL-DTL-38999 Series I	Т	Environmental with Accessory Threads	Submersible	Silicone/Fluorosilicone	-65°C – +175°C			•	22D 22	Aluminum	Nickel-PTFE	
Scoop Proof and	U	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +150°C			•	20	Aluminum	Cadmium - Clear Chromate	
Series II Low Profile	Z	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +175°C			•	16	Aluminum	Zinc-Nickel - Black Chromate	Bayonet
(231 & 232)	D	Hermetic	Submersible	Silicone/Fluorosilicone	-65°C – +150°C	•			12 10	Stainless Steel	Fused Tin/3-10% Lead alloy (Carbon Steel)	
	Е	Environmental (Superseded by Class T)	Submersible	Silicone/Fluorosilicone	-65°C – +200°C			•	8	Stainless Steel	Passivated (Stainless Steel)	
	L	Environmental	Submersible	Silicone/Fluorosilicone	-65°C – +200°C			•		Stainless Steel	Electrodeposited Nickel (Stainless Steel)	
	N	Hermetic	Submersible	Silicone/Fluorosilicone	-65°C – +200°C	•				Stainless Steel	Electrodeposited Nickel (Stainless Steel)	

		PERFORMANCE				CONTACT TY	/DE			SHELL		
MILITARY	ENVIRONMENTAL	PERFORMANCE				CONTACT I				SHELL		
SPECIFICATION	AND MATERIAL	DESCRIPTION	WATER	RESILIENT MATERIAL		SOLDER or	CRIMP		SIZE	SHELL	FINISH DESCRIPTION	COUPLING TYPE
	CLASS		RESISTANCE		TEMP	EYELET	FRONT	REAR	31.2.2	MATERIAL		COOLEMACTILE
	С	Environmental Nonconductive	Submersible	Silicone or Fluorosilicone	200°C			•		Aluminum	Anodic (nonconductive)	
	F	Environmental Conductive	Submersible	Silicone or Fluorosilicone	200°C			•		Aluminum	Electroless Nickel	
	G	Environmental, Space Grade	Submersible	Silicone or Fluorosilicone	200°C			•		Aluminum	Electroless Nickel	
	Н	Hermetic, Space Grade	Submersible	Silicone or Fluorosilicone	200°C	•				Stainless Steel	Passivated	
	J	Environmental Composite	Submersible	Silicone or Fluorosilicone	175°C			•	23	Composite	Cadmium O.D. Chromate	
MIL-DTL-38999 Series III	K	Environmental, Firewall	Submersible	Silicone or Fluorosilicone	200°C			•	22D	Stainless Steel	Passivated	
Scoop Proof	L	Environmental, Stainless	Submersible	Silicone or Fluorosilicone	200°C			•	22	Stainless Steel	Electrodeposited Nickel	
and	M	Environmental, Composite	Submersible	Silicone or Fluorosilicone	200°C			•	20 16	Composite	Electroless or Electrodep. Nickel	Threaded Triple Start
Series IV Scoop Proof	N	Hermetic	Submersible	Silicone or Fluorosilicone	200°C	•			10	Stainless Steel	Electrodeposited Nickel	
(233 & 234)	R	Environmental Corrosion Resistant	Submersible	Silicone or Fluorosilicone	200°C			•	10	Aluminum	Electroless Nickel	
	S	Environmental Firewall	Submersible	Silicone or Fluorosilicone	200°C			•	8	Stainless Steel	Electrodeposited Nickel	
	Т	Environmental Nickel PTFE	Submersible	Silicone or Fluorosilicone	175°C			•		Aluminum	Nickel PTFE	
	W	Environmental	Submersible	Silicone or Fluorosilicone	175°C			•		Aluminum	500 hr Cad O.D.	
	Υ	Hermetic	Submersible	Silicone or Fluorosilicone	200°C	•				Stainless Steel	Passivated	
	Z	Environmental Zinc Nickel Plating	Submersible	Silicone or Fluorosilicone	175°C			•		Aluminum	Zinc Nickel - Black Chromate	
MIL-DTL-55116	_	Environmental, Cable Seal	Splash-proof	Neoprene	125°C	•			20	Stainless Steel	Passivated	Reverse Bayonet
MIL-DTL-55181	_	Environmental, Cable Seal	Splash-proof	Neoprene	125°C	•				Carbon Steel	96 hr Cad O.D.	Center Lock Screw
MIL-C-55243	_	Environmental, Cable Seal	Splash-proof	Neoprene	125°C	•				Aluminum	96 hr Cad O.D.	Reverse Bayonet
SAE AS81511 Series	A	Environmental	Submersible	Silicone	200°C			•	23	Aluminum	Electroless Nickel	,
1 Gang Release*	Е	Environmental	Splash-proof	Silicone	150°C			*	20	Aluminum	96 hr Cad O.D.	-
Superseded by	F	Environmental	Submersible	Silicone	175°C			•	16	Aluminum	Electroless Nickel	Bayonet
Series III	Н	Hermetic	Submersible	Silicone	150°C	*			12	Carbon Steel	Tinned	-
SAE AS81511 Series	Α	Environmental	Submersible	Silicone	200°C			*	23	Aluminum	Electroless Nickel	
2 Gang Release*	Е	Environmental	Splash-proof	Silicone	150°C			*	20	Aluminum	96 hr Cad O.D.	_
Superseded by	F	Environmental	Submersible	Silicone	175°C			*	16	Aluminum	Electroless Nickel	Bayonet
Series IV	Н	Hermetic	Submersible	Silicone	150°C	•			12	Carbon Steel	Tinned	
	Α	Environmental	Submersible	Silicone	200°C			•	23	Aluminum	Electroless Nickel	
SAE AS81511	D	Hermetic	Submersible	Silicone	175°C	•			20	Stainless	Passivated	_
Series III	F	Environmental	Submersible	Silicone	175°C			•	16	Aluminum	Electroless Nickel	Bayonet
	W	Environmental	Submersible	Silicone	175°C			•	12	Aluminum	500 hr Cad O.D.	-
	A	Environmental	Submersible	Silicone	200°C			•	23	Aluminum	Electroless Nickel	
SAE AS81511	D	Hermetic	Submersible	Silicone	175°C	•			20	Carbon Steel	Passivated	_
Series IV	F	Environmental	Submersible	Silicone	175°C				16	Aluminum	Electroless Nickel	Bayonet
	W	Environmental	Submersible	Silicone	175°C			•	12	Aluminum	500 hr Cad O.D.	-
	E	Environmental	Splash-proof	Neoprene	125°C	•				Aluminum	96 hr Cad O.D.	
SAE-AS81703	Н	Hermetic	Splash-proof	Neoprene	125°C	•			20	Carbon Steel	Tinned	
Series I	J	Gland Seal	Splash-proof	Neoprene	125°C				16	Aluminum	96 hr Cad O.D.	Push Pull
	Р	Environmental, Potting Seal	Splash-proof	Neoprene	125°C	•			12	Aluminum	96 hr Cad O.D.	
CAE AC01703	E	Environmental	Splash-proof	Neoprene	175°C		•		20	Aluminum	96 hr Cad O.D.	
SAE-AS81703 Series II	-			· ·					16			Push Pull
55.16511	J	Gland Seal	Splash-proof	Neoprene	175°C		•		12	Aluminum	96 hr Cad O.D.	


Right Brain / Left Brain Performance Matrix




Find the top view for each of the 3 structures




Find the three unduplicated stamps



For each front, find the corresponding back



Answers available at: www.glenair.com/qwikconnect





Find the top view for each teapot

		PERFORMANCE	PERFORMANCE							SHELL		
MILITARY	ENVIRONMENTAL AND MATERIAL		WATER		OPERATING	SOLDER or	CRIMP			SHELL		
SPECIFICATION	CLASS	DESCRIPTION	RESISTANCE	RESILIENT MATERIAL	TEMP	EYELET	FRONT	REAR	SIZE	MATERIAL	FINISH DESCRIPTION	COUPLING TYPE
	Е	Environmental	Submersible	Silicone	200°C			•	20	Aluminum	500 hr Cad O.D.	
SAE-AS81703	Н	Hermetic	Submersible	Silicone	200°C	•			20 16	Stainless Steel	Passivated	Push Pull
Series III	L	Environmental	Submersible	Silicone	175°C			•	12	Aluminum	500 hr Cad O.D.	Push Puli
	N	Hermetic	Submersible	Silicone	200°C			•	12	Stainless Steel	Passivated	
MIL-DTL-83526 Fiber Optic	ALL	Environmental	Submersible	Aluminum	65C		Fiber Optic		_	Aluminum	Grey Anodize	Threaded
	Α	Environmental	Submersible	Silicone	200°C			•		Aluminum	Black Anodized	
	G	Environmental	Submersible	Silicone	200°C			•		Stainless Steel	Passivated	
	Н	Hermetic	Splash-proof	Silicone	150°C	•				Carbon Steel	Tinned	
	J	Hermetic	Submersible	Silicone	150°C	•				Carbon Steel	Tinned	
	K	Environmental, Firewall	Submersible	Silicone	200°C			•		Stainless Steel	Passivated	
	L	Hermetic	Submersible	Silicone	200°C	•			16	Stainless Steel	Electrodeposited Nickel	
MIL-DTL-83723	M	Environmental	Submersible	Silicone	175°C			•	12	Aluminum	Electrodeposited Aluminum	
Series II (Inactive for new design) R S	N	Hermetic	Submersible	Silicone	200°C	•			8	Stainless Steel	Electrodeposited Nickel	Threaded
	Р	Hermetic	Submersible	Silicone	200°C	•			4	Stainless Steel	Passivated	
	R	Environmental	Submersible	Silicone	200°C			•	1/0	Aluminum	Electronless Nickel	
	S	Environmental, Firewall	Submersible	Silicone	200°C			•		Stainless Steel	Passivated	
	Т	Environmental	Submersible	Silicone	175°C			•		Aluminum	Nickel PTFE	
	W	Environmental	Submersible	Silicone	175°C			•		Aluminum	500 Hr. Conductive Cadmium	
	Υ	Hermetic	Submersible	Silicone	200°C	•				Stainless Steel	Passivated	
	Z	Environmental	Submersible	Silicone	175°C			•		Aluminum	Conductive Zinc Nickel	
	Α	Environmental	Submersible	Silicone	200°C			•		Aluminum	Black Anodized	
	G	Environmental	Submersible	Silicone	200°C			•		Stainless Steel	Passivated	
	Н	Hermetic	Splash-proof	Silicone	150°C	•				Carbon Steel	Tinned	
	J	Hermetic	Submersible	Silicone	150°C	•				Carbon Steel	Tinned	
	K	Environmental, Firewall	Submersible	Silicone	200°C			•		Stainless Steel	Passivated	
	L	Hermetic	Submersible	Silicone	200°C	•				Stainless Steel	Electrodeposited Nickel	
MIL-DTL-83723	M	Environmental	Submersible	Silicone	175°C			•	20	Aluminum	Electrodeposited Aluminum	
Series III	N	Hermetic	Submersible	Silicone	200°C	•			16	Stainless Steel	Electrodeposited Nickel	Bayonet or Threaded
Type B Bayonet or Type T Threaded	Р	Hermetic	Submersible	Silicone	200°C	•			12	Stainless Steel	Passivated	
Timedaed	R	Environmental	Submersible	Silicone	200°C			•		Aluminum	Electronless Nickel	
	S	Environmental, Firewall	Submersible	Silicone	200°C			•		Stainless Steel	Passivated	
	Т	Environmental	Submersible	Silicone	175°C			•		Aluminum	Nickel PTFE	
	W	Environmental	Submersible	Silicone	175°C			•		Aluminum	500 Hr. Conductive Cadmium	
	Υ	Hermetic	Submersible	Silicone	200°C	•				Stainless Steel	Passivated	
	Z	Environmental	Submersible	Silicone	175°C			•		Aluminum	Conductive Zinc Nickel	

AS39029 Crimp Contact Selection Guide

Military Part Number	Glenair Part Number	Contact Size	Wire Accommodation	Pin / Socket	BIN Color Striping		ng
M39029/56-348	850-001-22-348	22	22-28 AWG	Socket	Orange	Yellow	Grey
M39029/56-351	850-001-20-351	20	20-24 AWG	Socket	Orange	Green	Brown
M39029/56-352	850-001-16-352	16	16-20 AWG	Socket	Orange	Green	Red
M39029/56-353	850-001-12-353	12	12-14 AWG	Socket	Orange	Green	Orange
M39029/56-527	850-001-10-527	10	10 AWG	Socket	Green	Red	Violet
M39029/57-354	850-003-22-354	22	22-28 AWG	22-28 AWG Socket		Green	Yellow
M39029/57-357	850-003-20-357	20	20-24 AWG	Socket	Orange	Green	Violet
M39029/57-358	850-003-16-358	16	16-20 AWG	Socket	Orange	Green	Grey
M39029/57-359	850-003-12-359	12	12-14 AWG	Socket	Orange	Green	White
M39029/58-360	850-002-22-360	22	22-28 AWG	Pin	Orange	Blue	Black
M39029/58-363	850-002-20-363	20	20-24 AWG	Pin	Orange	Blue	Orange
M39029/58-364	850-002-16-364	16	16-20 AWG	Pin	Orange	Blue	Yellow
M39029/58-365	850-002-12-365	12	12-14 AWG	Pin	Orange	Blue	Green
M39029/58-528	850-002-10-528	10	10 AWG	Pin	Green	Red	Grey
M39029/63-368	850-021-20-368	20	20-24 AWG	Socket	Orange	Blue	Grey
M39029/64-369	850-022-20-369	20	20-24 AWG	Pin	Orange	Blue	White

3 ORANGE

AS39029 Crimp Contact Selection Guide

Military Part Number	Glenair Part Number	Contact Size	Wire Accommodation	Pin / Socket	Co	BIN Color Striping	
M39029/83-450	850-004-20-450	20	22-26 AWG	Pin	Yellow	Green	Black
M39029/83-451	850-004-20-451	20	28-32 AWG	Pin	Yellow	Green	Brown
M39029/83-508	850-004-20-508	20	20-24 AWG	Pin	Green	Black	Grey
M39029/84-452	850-005-20-452	20	22-26 AWG	Socket	Yellow	Green	Red
M39029/84-453	850-005-20-453	20	28-32 AWG	Socket	Yellow	Green	Orange
M39029/84-509	850-005-20-509	20	20-24 AWG	Socket	Green	Black	White
M39029/106-614	850-006-22-614	22	22-28 AWG	Socket	Blue	Brown	Yellow
M39029/106-615	850-006-20-615	20	20-24 AWG	Socket	Blue	Brown	Green
M39029/106-616	850-006-16-616	16	16-20 AWG	Socket	Blue	Brown	Blue
M39029/106-617	850-006-12-617	12	12-14 AWG	Socket	Blue	Brown	Violet
M39029/106-618	850-006-10-618	10	10 AWG	Socket	Blue	Brown	Grey
M39029/107-620	850-007-22-620	22	22-28 AWG	Pin	Blue	Red	Black
M39029/107-621	850-007-20-621	20	20-24 AWG	Pin	Blue	Black	Brown
M39029/107-622	850-007-16-622	16	16-20 AWG	Pin	Blue	Red	Red
M39029/107-623	850-007-12-623	12	12-14 AWG	Pin	Blue	Red	Orange
M39029/107-624	850-007-10-624	10	10 AWG	Pin	Blue	Red	Yellow

	BIN Color Coding									
A	0 BLACK	1 BROWN	2 RED	3 ORANGE	4 YELLOW	5 GREEN	6 BLUE	7 VIOLET	8 GREY	9 WHITE

 BIN Color Coding

 4
 5
 6
 7
 8
 9

 YELLOW
 GREEN
 BLUE
 VIOLET
 GREY
 WHITE

(19.92)

0 BLACK

AS39029 Shielded Contact Selection Guide

Military Part	Glenair Part	Contact	Pin /	Туре		BIN		
Number	Number	Size	Socket			olor Stripi		
M39029/27-210	852-001-12-210	12	Socket	Coaxial	Red	Brown	Black	
M39029/27-402	852-001-12-402	12	Socket	Coaxial	Yellow	Black	Red	
M39029/27-403	852-001-12-403	12	Socket	Coaxial	Yellow	Black	Orange	
M39029/27-404	852-001-12-404	12	Socket	Coaxial	Yellow	Black	Yellow	
M39029/27-405	852-001-12-405	12	Socket	Coaxial	Yellow	Black	Green	
M39029/27-406	852-001-12-406	12	Socket	Coaxial	Yellow	Black	Blue	
M39029/27-407	852-001-12-407	12	Socket	Coaxial	Yellow	Black	Violet	
M39029/27-408	852-001-12-408	12	Socket	Coaxial	Yellow	Black	Gray	
M39029/28-211	852-002-12-211	12	Pin	Coaxial	Red	Brown	Brown	
M39029/28-409	852-002-12-409	12	Pin	Coaxial	Yellow	Black	White	
M39029/28-410	852-002-12-410	12	Pin	Coaxial	Yellow	Brown	Black	
M39029/28-411	852-002-12-411	12	Pin	Coaxial	Yellow	Brown	Brown	¥
M39029/28-412	852-002-12-412	12	Pin	Coaxial	Yellow	Brown	Red	
M39029/28-413	852-002-12-413	12	Pin	Coaxial	Yellow	Brown	Orange	
M39029/28-414	852-002-12-414	12	Pin	Coaxial	Yellow	Brown	Yellow	
M39029/28-415	852-002-12-415	12	Pin	Coaxial	Yellow	Brown	Green	
M39029/59-366	852-006-08-366	08	Socket	Coaxial	Orange	Blue	Blue	
M39029/60-367	852-007-08-367	08	Pin	Coaxial	Orange	Blue	Violet	
M39029/75-416	852-003-12-416	12	Socket	Coaxial	Yellow	Brown	Blue	
M39029/75-417	852-003-12-417	12	Socket	Coaxial	Yellow	Brown	Violet	
M39029/75-418	852-003-12-418	12	Socket	Coaxial	Yellow	Brown	Gray	
M39029/75-419	852-003-12-419	12	Socket	Coaxial	Yellow	Brown	White	5
M39029/75-420	852-003-12-420	12	Socket	Coaxial	Yellow	Red	Black	0
M39029/75-421	852-003-12-421	12	Socket	Coaxial	Yellow	Red	Brown) (
M39029/75-422	852-003-12-422	12	Socket	Coaxial	Yellow	Red	Red	
M39029/75-423	852-003-12-423	12	Socket	Coaxial	Yellow	Red	Orange	
M39029/76-424	852-008-16-424	16	Pin	Coaxial	Yellow	Red	Yellow	
M39029/76-425	852-008-16-425	16	Pin	Coaxial	Yellow	Red	Green	
M39029/76-426	852-008-16-426	16	Pin	Coaxial	Yellow	Red	Blue	
M39029/76-427	852-008-16-427	16	Pin	Coaxial	Yellow	Red	Violet	
M39029/77-428	852-009-16-428	16	Socket	Coaxial	Yellow	Red	Gray	
M39029/77-429	852-009-16-429	16	Socket	Coaxial	Yellow	Red	White	
M39029/77-430	852-009-16-430	16	Socket	Coaxial	Yellow	Orange	Black	
M39029/77-431	852-009-16-431	16	Socket	Coaxial	Yellow	Orange	Brown	
M39029/78-432	852-010-16-432	16	Socket	Coaxial	Yellow	Orange	Red	
M39029/78-433	852-010-16-433	16	Socket	Coaxial	Yellow	Orange	Orange	
M39029/78-434	852-010-16-434	16	Socket	Coaxial	Yellow	Orange	Yellow	
M39029/78-435	852-010-16-435	16	Socket	Coaxial	Yellow	Orange	Green	
M39029/90-529	853-001-08-529	8	Pin	Concentric Twinax	Green	Red	White	Ŀ
M39029/91-530	853-002-08-530	8	Socket	Concentric Twinax	Green	Orange	Black	
M39029/102-558	852-004-12-558	12	Pin	Coaxial	Green	Green	Gray	
M39029/103-559	852-005-12-559	12	Socket	Coaxial	Green	Green	White	
M39029/113-625	853-003-08-625	8	Pin	Concentric Twinax	Blue	Red	Green	
M39029/113-626	853-003-08-626	8	Pin	Concentric Twinax	Blue	Red	Blue	
M39029/114-628	853-004-08-628	8	Socket	Concentric Twinax	Blue	Red	Gray	
M39029/114-629	853-004-08-629	8	Socket	Concentric Twinax	Blue	Red	White	4-
								_

El Ochito® Octaxial Contacts Selection Guide

				El Ochito	* Contacts: How	To Orde	er				
			Wire		Cable		El Ochit	o° Type I	El Ochito	005-03 858-006-03 6097-03 AI85097-03 005-04 858-006-04 6097-04 AI85097-04 -005-01 858-006-01 6097-01 AI85097-01 005-02 858-006-02	
	Data Protocol	Connector Type	Size	Cable Type	Glenair Part No. (Mfgr. P/N)	Cable Dia.	Pin Contact	Skt Contact	Pin Contact	Skt Contact	
					(g,		Assembly Instr.	Assembly Instr.	Assembly Instr.	Assembly Instr.	
				S/UTP	963-003-26 (PIC E6A3826)	.220 (5.56)	858-009-01 Al85074-01	858-010-01 Al85074-01			
		ARINC 600	26	- /	963-033-26	.220	858-009-02	858-010-02			
				S/FTP	(Gore RCN9047-26)	(5.56)	AI85084-01	AI85084-01			
			24	S/UTP	963-037-24 (PIC E6A3824)	.260 (6.60)			858-005-03 Al85097-03		
) (1000BASE-T 10GBASE-T	Series 23 SuperNine® Series 80		S/FTP	963-033-24 (Gore RCN9047-24)	.260 (6.60)			858-005-04 Al85097-04		
9	10GB/ISE 1	Mighty Mouse Series 28 HiPer-D [®]	26	S/UTP	963-003-26 (PIC E6A3826)	.220 (5.56)	858-003-01F Al85048-01	858-004-01F Al85048-01	858-005-01 Al85097-01		
	El Ochito®		20	S/FTP	963-033-26 (Gore RCN9047-26)	.220 (5.56)	858-003-02F Al85048-02	858-004-02F Al85048-02	858-005-02 Al85097-01		
	White	Series 79	26	S/UTP	963-003-26 (PIC E6A3826)	.220 (5.56)	858-003-01F Al85048-01	858-032-01F Al85112-01			
		Selies79	20	S/FTP	963-033-26 (Gore RCN9047-26)	.220 (5.56)	858-003-02F Al85048-02	858-032-02F Al85112-02		858-006-03 AI85097-03 858-006-04 AI85097-04 858-006-01 AI85097-01 858-006-02	
		EPXB	26	S/UTP	963-003-26 (PIC E6A3826)	.220 (5.56)	858-014-02F Al85099-01	858-015-02F Al85099-01			
		El Xe	20	S/FTP	963-033-26 (Gore RCN9047-26)	.220 (5.56)	858-014-01F Al85105-01	858-015-01F Al85105-01			
<u>(</u>		ARINC 600	26	Commercial Grade SuperSpeed USB	963-118	.217 (5.51)	858-038-01 Al852124-01	858-035-01 Al852124-01			
	SuperSpeed USB		ANINC 000 20	Aerospace Grade SuperSpeed USB	963-110	.236 (5.99)	858-038-02 Al85124-02	858-035-02 Al85124-02			
	:33	Series 79	26	Commercial Grade SuperSpeed USB	963-118	.217 (5.51)	858-028-01F Al85114-02	858-040-01F Al85125-01			
	El Ochito®		26	Aerospace Grade SuperSpeed USB	963-110	.236 (5.99)	858-028-02F Al85090-01	858-040-02F AI85125-02			
	Blue	Series 23 SuperNine® Series 80	26	Commercial Grade SuperSpeed USB	963-118	.217 (5.51)	858-028-01F Al85114-02	858-029-01F Al85114-02			
05 .1		Mighty Mouse Series 28 HiPer-D®	20	Aerospace Grade SuperSpeed USB	963-110	.236 (5.99)	858-028-02F Al85090-01	858-029-02F Al85090-01			
	HDMI, DisplayPort,	ARINC 600	26				858-039-01 Al85084-01	858-037-01 Al85084-01			
	SATA El Ochito® Red	Series 79	26	Cat 6a S/FTP	963-033-26 (Gore RCN9047-26)	.220 (5.56)	858-030-02F Al85048-02	858-041-01F Al85112-02			
		Series 23 SuperNine® Series 80 Mighty Mouse Series 28 HiPer-D®	26				858-030-02F Al85048-02	858-031-02F Al85048-02			

Fiber Optic Contact Selection Guide

Glenair Part Number	Part Description	Contact Size	Pin / Socket	Connector Series				
	MIL-DTL-38999 Fiber O	ptic Contacts						
181-001	M29504/5 Socket Terminus	16	Socket	D38999 Series III				
181-002	M29504/4 Pin Terminus	16	Pin	D38999 Series III				
181-035	Socket, Large Core Fiber	16	Socket	D38999 Series III				
181-036	Pin, Large Core Fiber	16	Pin	D38999 Series III				
181-052	Jewel Pin Terminus	16	Pin	D38999 Series III				
181-053	Jewel Socket Terminus	16	Socket	D38999 Series III				
181-048	Sealing Plug	16	Pin	D38999 Series III				
181-065	#20 Pin Terminus	20	Pin	D38999 Series III				
181-066	#20 Socket Terminus	20	Socket	D38999 Series III				
MIL-PRF-28876 Fiber Optic Contacts								
181-039	M29504/14 Pin Terminus	16	Pin	M28876				
181-040	M29504/15 Socket Terminus	16	Socket	M28876				
181-051	M29504/3 Dummy Terminus	16	Dummy	M28876				
Series 80 Mighty Mouse Fiber Optic Contacts								
181-057	Mighty Mouse Pin Terminus	16	Pin	Series 80 Mighty Mouse				
181-075	Mighty Mouse Socket Terminus	16	Socket	Series 80 Mighty Mouse				
181-084	Mighty Mouse Pin Terminus	20HD	Pin	Series 80 Mighty Mouse				
181-085	Mighty Mouse Socket Terminus	20HD	Socket	Series 80 Mighty Mouse				
	Special Fiber Optic COTS Contact	ts Size 16 Front	Release					
181-011	Front Release Socket with Pressure Sealing O-Ring(s)	16	Socket	COTS				
181-012	Front Release Pin	16	Pin	COTS				
181-051	Dummy Terminus	16	Dummy	COTS				
	ARINC Type Fiber Opt	tic Contacts						
181-076	ARINC 801 Terminus	16	Genderless Pin	ARINC 801				
187-079	M29504/6 Pin Terminus	16	Pin	ARINC 404, 600				
187-080	M29504/7 Socket Terminus	16	Socket	ARINC 404, 600				
	Glenair High Density (GHD) F	iber Optic Con	tacts					
181-056	GHD Terminus, Non-keyed	18	Genderless Pin	GHD				
181-047	GHD Terminus, Keyed	18	Genderless Pin	GHD				
181-058	Dummy Terminus	18	Dummy	GHD				
	Glenair GFOCA Fiber O	ptic Contacts						
181-050	GFOCA Terminus		Genderless Pin	GFOCA				
181-059	Dummy Terminus		Dummy	GFOCA				
	Next Generation Fiber Optic	(NGCON) Cont	acts					
181-043	M29504/18	16	Genderless Pin	M64266				

QwikConnect

High-Frequency RF / Microwave Contacts

AS39029 COAXIAL CONTACTS



Coaxial DC – 700 MHz



Size #12 AS39029 Coaxial DC – 3 GHz



Size #16 AS39029 Coaxial DC – 500 MHz

LOW-LOSS MATCHED IMPEDANCE COAXIAL CONTACTS



Size #8 50 Ohm Matched-Impedance Coaxial DC – 6 GHz



Size #12 50 Ohm Matched-Impedance Coaxial DC – 3 GHz



Size #8 75 Ohm Matched-Impedance Coaxial DC – 4 GHz



Size #12 75 Ohm Matched-Impedance Coaxial DC – 3 GHz

SPRING-LOADED MICROWAVE COAXIAL CONTACTS



Size #8 Spring-Loaded BMB Coaxial DC – 18 GHz



Size 12 Spring-Loaded SMPM Coaxial DC – 40 GHz

High-Speed Datalink Contacts



Size #8 77 Ohm Concentric Twinax DC – 10 MHz



Size #8 100 Ohm Concentric Twinax frequency: application-dependent



Size #12 77 Ohm **Concentric Twinax** DC - 20 MHz



Size #8 Differential Twinax frequency: application-dependent

Size #12 Differential Ultra-Twinax DC – 10 GHz

Size #8 Quadrax DC – 3 GHz

El Ochito® Size #8 Octaxial DC – 4GHz

48

.150 (3.81) MIN DEEP T

MIL-DTL-38999 Series III (SuperNine®) and Series 806 Mighty Mouse Mil-Aero Performance Specifications

Performance Specification								
TEST DESCRIPTION		REQ	UIREMENT		PROCEDURE			
Dielectric withstanding voltage at sea level	Contact Siz 20HD 22HD	Se	ltitude ea level ea level	Voltage 1800 1300	MIL-DTL-38999M para. 4.5.11.1 EIA-364-20 Method A 2 mA maximum leakage current Unmated pairs			
Dielectric withstanding voltage at altitude	Contact Siz 20HD	50,000 ft 70,000 ft 100,000 ft		Voltage 1000 1000 1000 800 800 800	MIL-DTL-38999M para. 4.5.11.2 EIA-364-20 Method A 2 mA maximum leakage current Mated pairs			
Insulation resistance at ambient temperature	5000 megohm	s minimum			MIL-DTL-38999M Para. 4.5.10.1 EIA-364-21			
Insulation resistance at elevated temperature	1000 megohm	s minimum			MIL-DTL-38999M Para. 4.5.10.2 EIA-364-21			
Contact resistance at 25°C, crimp contacts	Wire Size 20 22 24 26 28 30	Test Current Amperes 7.5 5 3 2 1.5 1	(m	Noltage Drop illivolts) After Conditioning 66 88 54 63 65 73	AS39029C Para. 4.7.5 EIA-364-06 Silver-plated wire			
Contact resistance at 200° C, crimp contacts		7.5 5 3 2 1.5	Maximum V Drop (milling) 94 125 77 89 92 103		AS39029C Para. 4.7.5 EIA-364-06 Silver-plated wire	Э		
Low level contact resistance, crimp contacts	Wire Size 20 22 24 26 28 30	Maximum Con Initial Value 9 15 20 31 50 75		ce (milliohms) r Conditioning 11 17 23 38 60 88	AS39029C Para. 4.7.4 EIA-364-23 Silver plated wire	6		
Contact resistance, glass-sealed hermetic connectors	Contact Size, Wire Size 20 22	Test Current Amperes 5 3	t Maxim Initial 60 85	um Millivolt Drop After Conditioning 75 95	MIL-DTL-38999M Para. 3.18.2 EIA-364-06			
Shell-to-shell conductivity	Finish Code NF MT ME ZR Z1 ZL	Shell Ma Al/OD 0 Al/Ni-P Al/El Al/Zn- SST/pa SST/pa	Cad TFE N -Ni ass.		MIL-DTL-38999M Para. 4.5.25 EIA-364-83	0		
Backshell shield braid to shell conductivity	Finish Code NF MT ME ZR Z1 ZL	Shell Ma Al/OD Al/Ni-I Al/E Al/Zr SST/p SST/p	Cad PTFE EN n-Ni pass.	Millivolt Drop (mV) 5.0 5.0 3.5 5.0 15.0 3.5 5.0 15.0	MIL-DTL-38999M Para. 4.5.25.1 EIA-364-83	0 0 0		
Indirect lightning strike		all meet shell		r proper functioning. Iuctivity, DWV and	. MIL-DTL-38999M Para. 4.5.47 EIA-364-75 10,000 Amps peak current	0		

QwikConnect

Porformanco Specification							
TEST DESCRIPTION	Performance Specification	PROCEDURE					
TEST DESCRIPTION	REQUIREMENT	PROCEDURE					
EMI shielding	Leakage Attenuation, (dB) minimum Freq. MHz Electroless Nickel Finish Cadmium, Nickel-PTFE, Zinc-Nickel Finish 100 90 90 200 88 88 300 88 88 400 87 87 800 85 85 1,000 85 85 1,500 76 69 2,000 70 65 3,000 69 61 4,000 68 58 6,000 66 55 10,000 65 50	MIL-DTL-38999M Para. 4.5.28					
Durability	No evidence of damage which could impair proper functioning following 500 cycles of mating and unmating.	MIL-DTL-38999M Para. 4.5.8 EIA-364-09					
Coupling and uncoupling torque	Shell size Maximum Engagement Ibs-inch. Minimum Disengagement Ibs-inch. 8 8 2 9 8 2 10 12 2 11 12 2 12 12 2 14 16 2 16 20 3 18 24 3 20 28 3 22 32 5 24 36 5	MIL-DTL-38999M Para. 4.5.7 EIA-364-114					
Insert retention	100 pounds per square inch, 25 pound minimum force	MIL-DTL-38999M Para. 4.5.12 EIA-364-35					
External bend moment	Shell size Pound inches 8 100 9 100 10 100 11 200 12 300 14 400 16 500 18 600 20 700 22 800 24 900	MIL-DTL-38999M Para. 4.5.16 EIA-364-43					
Contact retention	Contact size Pounds ± 10 percent 22HD 10 20HD 10	MIL-DTL-38999M Para. 4.5.20.1 EIA-364-29					
Magnetic permeability	2 μ maximum	MIL-DTL-38999M Para. 4.5.48 EIA-364-54					
Contact engaging /separation force	Contact forces shall meet AS39029 Table 9 requirements	AS39029C Para. 4.7.6 EIA-364-37					
Temperature cycling (thermal shock)	No evidence of damage detrimental to the function of the connector	MIL-DTL-38999M Para. 4.5.4 EIA-364-32 Mated connectors, -65° C to +200° C					
Random vibration, elevated temperature, 43g rms	No discontinuities of 1 microsecond or longer No resonance at frequencies less than 300 Hz	MIL-DTL-38999M Para. 4.5.23.2.3 with Figure 24 accessory load EIA-364-28 +200°C					
Random vibration, ambient temperature, 49g rms	No discontinuities of 1 microsecond or longer	MIL-DTL-38999M Para. 4.5.23.2.4 EIA-364-28 Test Condition V					
Sine vibration, 60g	No discontinuities of 1 microsecond or longer	MIL-DTL-38999M Para. 4.5.23.2.1 with Figure 24 accessory load 12 hours in each of 3 axes 4 hours at ambient, 4 hours at -55° C, 4 hours at +200° C					
Mechanical shock, 300g	No discontinuities of 1 microsecond or longer	MIL-DTL-38999M Para. 4.5.24.1 EIA-364-27					
High impact shock (901)	No discontinuities of 1 microsecond or longer No evidence of damage which could impair proper functioning.	MIL-DTL-38999M Para. 4.5.24.2 MIL-S-901 Grade A					


MIL-DTL-38999 Series III (SuperNine®) and Series 806 Mighty Mouse Mil-Aero Performance Specifications

	Performance Specification								
TEST DESCRIPTION	REQUIREMENT	Г	PROCEDURE						
Humidity, cyclic	Meet DWV and IR test		MIL-DTL-38999M Para. 4.5.26 EIA-364-31 Method 4 10 cycles, 10 days, 25 – 65°C 80 – 100% RH						
Ozone exposure	No evidence of damage detrimental to connector	the function of the	MIL-DTL-38999M Para. 4.5.29 EIA-364-14						
Fluid immersion	No damage to plastic, elastomeric and detrimental to the function of the con meet coupling torque and DWV requir within 3 hours of immersion.	nector. Connector shall	MIL-DTL-38999M Para. 4.5.30 EIA-364-10						
Altitude immersion	No evidence of moisture on connector At the end of the third cycle, while still tors shall meet dielectric withstanding megohms insulation resistance.	submersed, connec-	MIL-DTL-38999M Para. 4.5.9 EIA-364-03 75,000 feet						
Altitude- low temperature	Connectors shall meet insulation resist while at -65°C and 100,000 ft. Connect requirement when returned to ambier	ors shall meet DWV	MIL-DTL-38999M Para. 4.5.21 EIA-364-105 -65°C 100,000 ft.						
Thermal vacuum outgassing	All nonmetallic materials shall not excubors and 0.1% Total Volatile Condensible only to connectors that have been thermal vacuum outgassing.	ole Materials. Applica-	MIL-DTL-38999M Para. 4.5.42 ASTM E595						
Salt Spray (dynamic)	Finish Code Matl/Fin NF Al/OD Cad MT Al/Ni-PTFE ME Al/EN ZR Al/Zn-Ni Z1 SST/passivate ZL SST/Ni	Hours 500 500 96 500 1000	MIL-DTL-38999M Para. 4.5.13.2 EIA-364-26 500 mating cycles						

Standard Materials and Finishes								
DESCRIPTION	MATERIAL	FINISH						
Pin Contact	Copper alloy	50 microinches gold over nickel						
Socket Contact	Copper alloy, with stainless steel hood	50 microinches gold over nickel Contact hood: passivate						
Insulators	High grade rigid dielectric	None						
Seals	Fluorosilicone/silicone blend, blue	None						
EMI Spring	Beryllium copper	Nickel						
Shell, Coupling Nut, Jam Nut	Aluminum alloy or stainless steel	See sales drawing or catalog for finish options						
Contact Retention Clip	Beryllium copper	None						
Anti-Decoupling Ratchet Spring	Stainless steel	Passivate						

QwikConnect

Series 806 Mighty Mouse Mil-Aero Contact Arrangements




QwikConnect • January 2019

MIL-STD-1560 Standard Power and Signal Contact Arrangements for MIL-DTL-38999 Series III / SuperNine®



Environmental a	nd Her	metic (Contac	t Arrai	ngements
	Nu	mber of	f Contac	ts	Insert
Contact	#22D	#20	#16	#12	Arrangement
	6				9-35
	13				11-35
	22				13-35
C: #22D	37				15-35
Size #22D 5 Amp Max. Current	55				17-35
#22-#28 AWG	66				19-35
#22 #20 AVV	67				19-35
	79				21-35
	100				23-35
	128				25-35
		2			9-94
		3			9-98
		4			11-4
		5			11-5
		6			11-98
		7			11-99
		8			13-8
		10			13-98
		18			15-18
Size #20		19			15-19
7.5 Amp Max. Current		26			17-26
#20-#24 AWG		32			19-32
#20 #217WG		24			21-24
		25			21-25
		27			21-27
		41			21-41
		32			23-32
		34			23-34
		36			23-36
		53			23-53
		55			23-55
		61			25 61


Environmental and Hermetic Contact Arrangements						
	Nu	mber of	Insert			
Contact	#22D	#20	#16	#12	Arrangement	
			2		11-2	
			4		13-4	
			5		15-5	
			8		17-8	
Size #16 Contacts			11		19-11	
13 Amp Max. Current			16		21-16	
#16-#20 AWG			21		23-21	
			16		23-97	
			11		23-99	
			29		25-29	
			37		25-37	
Size #12 Contacts				6	17-6	
23 Amp Max. Current				11	21-11	
#12-14 AWG				19	25-19	



QwikConnect


Contact Legend		$\left(\begin{array}{cc} A \\ \bullet \end{array}\right)$	A A	Θ^{D} $^{A}\Theta$	$\begin{array}{c c} & & & \\ \hline & \Theta & & \Theta \end{array}$	9 11 0 1 0 3 1 0 4 1 0 4 1 0 4 1 0 4 1 0 4 1 0 4 1 0 4 1 0 4 1 0 1 0	$ \begin{array}{ccc} & & & & \\ & & & & \\ & & & & \\ & & & &$
#22D •		BO		Θ^{C} $^{B}\Theta$	$\begin{array}{c} \begin{array}{c} \\ \\ \\ \end{array} \begin{array}{c} \\ \\ \end{array} \begin{array}{$	8 • ¹³ • • ¹² • ⁴ 7 • • 6 • 5	рӨ Өс
Insert Arrangement		9-98	11-2	11-4	11-5	11-35	11-98
No. of Contacts	6	3	2	4	5	13	6
Contact Size Service Rating	#22D M	#20 I	#16 I	#20	#20	#22D M	#20 I
Service Rating				'			
						Θ	$\bigoplus_{i \in \mathcal{I}_i} \bigcup_{i \in \mathcal{I}_i} \bigcup_{i$
Contact Legend		\bigoplus^{A}	GO OA	/		0 0 0	A
#22D • #16 ⊕		$\begin{pmatrix} D & & \oplus B \end{pmatrix}$	$\left(\begin{smallmatrix} F \ominus & \ominus^H & \ominus^B \end{smallmatrix} \right)$	G K H	$\Theta_1 \Theta_C$		$\left(\begin{array}{ccc} \mathbb{E} & \bigoplus & \bigoplus^{\mathbb{B}} \end{array}\right)$
#20 ⊖ #12 -		⊕ c	$_{\rm E\Theta} \Theta_{\rm D} \Theta_{\rm C}$	P	₽ 8/		
Insert Arrangement	11-99	13-4	13-8		.98	13-35	15-5
No. of Contacts	7	4	8	1		22	5
Contact Size	#20	#16	#20	#2		#22D	#16
Service Rating	ı		l			М	II
Contact Legend	$\begin{bmatrix} L & & A & \\ \Theta & \Theta & & \Theta \\ & \Theta & & \Theta & & \Theta \end{bmatrix}$			0 0 0	E	△ ^A	\bigoplus^{A}
#22D ● #16 ⊕				0 0 0 0		E B	Gen B
#20 ⊖ #12 -			⊖ _E \				Φ 1
	Ge eF eE	\H⊖ ⊖ ₆ ⊖		0000			_F ⊕ ⊕ _C /
1						c	$\bigoplus_{E} \bigoplus_{D}$
Insert Arrangement	15-18	15-19		15-35	17-	-6	17-8
No. of Contacts	18	19		37	6		8
Contact Size	#20	#20		#22D	#1		#16
Service Rating			T T	M	Θ	_ 0 _ 6)
		Θ	725		Θ		Θ
Contact Legend	P O O D	40			\bigoplus^{J} \bigoplus^{A}	S	
#22D ● #16 ⊕		100	0 0 0 0 53	/ H	K ⊕ B \	$R \ominus P \ominus G$	-W - \
#20 ⊖ #12 🕣				G _G		NO CO	A A
	LO O X OW OF	/ 30				/ \ .e ^b	e e e e
	кө дө өн өд		60 240 31 039 046	F	\oplus $\bigoplus_{\mathbb{E}}$ $\bigoplus_{\mathbb{D}}$	/ _w ^r Θ	a ⊕ ⊖z ⊖ _G k⊖ ⊖ _J ⊖ _H
	47.26		47.05				
Insert Arrangement No. of Contacts	17-26 26		17-35 55		19-11 11		19-32 32
Contact Size	#20		#22D		#16		#20
Service Rating	I		M		II		I
Contact Legend	17 6 6 43	10	17 Q 35 44 52	/1			A
#22D • #16 ⊕		4 0	59		3 4 ^	\ / K	$\bigoplus_{M} \bigoplus_{M} \bigoplus_{M$
#20 ⊖ #12 🕣		65 1 0	0 0 0 0 0 65	H	к 🕳 🗡	₿	. ♥ N \
				G		() ()⊕ (
		3	67			H _⊕	
	16 24 33 42 50 57	9 1	24 Q ₃₄ Q ₁₃ 51	F		P₀ /	
					E D		Ψ_{F}
Insert Arrangement	19-35		19-45		21-11		21-16
No. of Contacts	66		67		11		16

MIL-STD-1560 Standard Power and Signal Contact Arrangements for MIL-DTL-38999 Series III / SuperNine®




Service Rating

QwikConnect



						Θ	$\Theta \mid \Theta \mid \Theta$	Θ Θ	\square	Θ Θ	$\Theta \cap \Theta$	
Θ	Θ		Θ	9			Tost Volta	ge AC RMS 60	NH- IAW MII -F	TI_28000		
					Sea	Level		00 Ft.		00 Ft.	100.0	000 Ft
•	Sai	rvice F	Rating		unmated	mated	unmated	mated	unmated	mated	unmated	mated
	Je.		tatilig									
		M			1300	1300	550	800	350	800	200	800
		N			1000	1000	400	600	260	600	200	600
		- 1			1800	1800	600	1000	400	1000	200	1000
		Ш			2300	2300	800	1000	500	1000	200	1000

Note: The provision of electrical safety factors in each particular application, including peak voltages, switching currents, transients, etc. is the responsibility of the electrical engineer.



#22D •


Insert Arrangement No. of Contacts Contact Size


Service Rating


#16 ⊕

MIL-STD-1560 High Density and Combo Contact Arrangements for MIL-DTL-38999 Series III / SuperNine®


Environmental and Hermetic Contact Arrangements				
Contact	Number of Size 23 Contacts	Inserrt Arrangement		
	9	9-23		
	19	11-23		
	32	13-23		
	55	15-23		
	73	17-23		
	88	19-23		
Size #23 High-Density (HD)	121	21-23		
5 Amp Max. Current	151	23-23		
#22-#26 AWG	187	25-23		








QwikConnect





No. of Contacts

Contact Size Service Rating

Insert Arrangement No. of Contacts

Contact Size Service Rating

MIL-DTL-38999 QPL-to-Glenair Finish Code Cross Reference

MIL-DTL-38999 Series I and II Class Code	Finish Description	Equivalent Glenair Material/Finish Code	Salt Spray Hours	Temperture Range	Conductive Yes/No	RoHS Yes/No	
		,	Aluminum Connectors			1	
А	Cadmium - Gold/Clear Chromate	J/LF	48	-65°C to +150°C	Yes	No	
В	Cadmium - Olive-Drab Chromate	NF	500	-65°C to +175°C	Yes	No	
С	Hardcoat Anodize	G	500	-65°C to +200°C	No	Yes	
F	Electroless Nickel	М	48	-65°C to +200°C	Yes	Yes	
R	Electroless Nickel	ME	96	-65°C to +200°C	Yes	Yes	
Т	Nickel-PTFE	MT	500	-65°C to +175°C	Yes	Yes	
U	Cadmium - Clear Chromate	LF	96	-65°C to +150°C	Yes	No	9 (
Z	Zinc-Nickel - Black Chromate	ZR	500	-65°C to +175°C	Yes	Yes	
		Carbon S	teel/Stainless Steel Cor	inectors			
D	Fused Tin/3-10% Lead alloy (Carbon Steel)	FT	24	-65°C to +150°C	Yes	No	
E	Passivated (Stainless Steel)	Z1	500	-65°C to +200°C	Yes	Yes	
L	Electrodeposited Nickel (Stainless Steel)	ZL	500	-65°C to +200°C	Yes	Yes	
N	Electrodeposited Nickel (Stainless Steel)	Р	48	-65°C to +200°C	Yes	Yes	
MIL-DTL-38999 Series III and IV Class Code	Finish Description	Equivalent Glenair Material/Finish Code	Salt Spray Hours	Temperature Range	Conductive Yes/No	RoHS Yes/No	
		ı	Aluminum Connectors				
С	Hardcoat Anodize	G	500	-65°C to +200°C	No	Yes	
F	Electroless Nickel	ME					
G	Electroless Nickel		48	-65°C to +200°C	Yes	Yes	
R	(Space Grade)	MA	48 48	-65°C to +200°C	Yes Yes	Yes	
		MA ME				Yes Yes	
Т	(Space Grade)		48	-65°C to +200°C	Yes	Yes	
T W	(Space Grade) Electroless Nickel	ME	48 96	-65°C to +200°C	Yes Yes	Yes Yes	
	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium -	ME MT	48 96 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C	Yes Yes Yes	Yes Yes Yes	
W	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black	ME MT NF ZR	48 96 500 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C	Yes Yes Yes Yes	Yes Yes Yes No	
W Z H	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black	ME MT NF ZR	48 96 500 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C	Yes Yes Yes Yes	Yes Yes Yes No	
W Z	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated	ME MT NF ZR	48 96 500 500 500 ainless Steel Connector	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C	Yes Yes Yes Yes Yes Yes	Yes Yes Yes No Yes	
W Z H	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated Electrodeposited Nickel	ME MT NF ZR St.	48 96 500 500 500 ainless Steel Connector 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C	Yes Yes Yes Yes Yes Yes	Yes Yes Yes No Yes	
W Z H K	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated Electrodeposited	ME MT NF ZR St Z1 Z1	48 96 500 500 500 ainless Steel Connector 500 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C s -65°C to +200°C -65°C to +200°C	Yes Yes Yes Yes Yes Yes Yes Yes	Yes Yes Yes No Yes Yes Yes Yes	
W Z H K	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated Electrodeposited Nickel Electrodeposited	ME MT NF ZR St Z1 Z1 ZL	48 96 500 500 500 ainless Steel Connector 500 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C s -65°C to +200°C -65°C to +200°C -65°C to +200°C	Yes	Yes Yes Yes No Yes Yes Yes Yes Yes Yes	
W Z H K L	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated Electrodeposited Nickel Electrodeposited Nickel Electrodeposited Sickel Electrodeposited	ME MT NF ZR St. Z1 Z1 ZL ZL	48 96 500 500 500 ainless Steel Connector 500 500 48	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C s -65°C to +200°C -65°C to +200°C -65°C to +200°C -65°C to +200°C	Yes	Yes Yes Yes No Yes Yes Yes Yes Yes Yes Yes	094:2.39
W Z H K L N S	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated Electrodeposited Nickel Electrodeposited Nickel Electrodeposited Nickel Passivated	ME MT NF ZR St Z1 Z1 ZL ZL ZL ZL Z1	48 96 500 500 500 ainless Steel Connector 500 500 48 48	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C s -65°C to +200°C -65°C to +200°C -65°C to +200°C -65°C to +200°C -65°C to +200°C	Yes	Yes Yes Yes No Yes Yes Yes Yes Yes Yes Yes Yes Yes	
W Z H K L N S	(Space Grade) Electroless Nickel Nickel-PTFE Cadmium - Olive-Drab Chromate Zinc-Nickel - Black Chromate Passivated Passivated Electrodeposited Nickel Electrodeposited Nickel Electrodeposited Nickel	ME MT NF ZR St Z1 Z1 ZL ZL ZL ZL Z1	48 96 500 500 500 ainless Steel Connector 500 500 48 48 48 500	-65°C to +200°C -65°C to +200°C -65°C to +175°C -65°C to +175°C -65°C to +175°C s -65°C to +200°C -65°C to +200°C -65°C to +200°C -65°C to +200°C -65°C to +200°C	Yes	Yes Yes Yes No Yes Yes Yes Yes Yes Yes Yes Yes Yes	

QwikConnect

AS85049 Material	Finish Description	Equivalent Glenair	Salt Spray Hours	Temperature Range	Conductive	RoHS
and Finish Code		Material/Finish Code		у	Yes/No	Yes/No
A (, , (0 (4 , 1 (5)			Aluminum Accessories	4506		.,
A (except /3, /4 and /5)	Anodize, Black	С	500	-65°C to +200°C	No	Yes
A (/3, /4 and /5)	Hardcoat Anodize	G	500	-65°C to +200°C	No	Yes
G	Electroless Nickel (Space Grade)	MA	96	-65°C to +200°C	Yes	Yes
N	Electroless Nickel	М	96	-65°C to +200°C	Yes	Yes
Р	Cadmium - Olive- Drab Chromate (Selectively Plated)	NFP	96	-65°C to +175°C	Yes	No
W	Cadmium - Olive-Drab Chromate	NF	1,000	-65°C to +175°C	Yes	No
X	Nickel-PTFE	MT	500	-65°C to +175°C	Yes	Yes
Y	Alumiplate™	AL	1,000	-65°C to +175°C	Yes	Yes
ΥP	Alumiplate™ (Selectively Plated)	ALP	96*	-65°C to +175°C	Yes	Yes
Z	Zinc-Nickel - Black Chromate	ZR	1,000	-65°C to +175°C	Yes	Yes
ZP	Zinc-Nickel - Black Chromate (Selectively Plated)	ZS	96*	-65°C to +175°C	Yes	Yes
		St	tainless Steel Accessories			
В	Cadmium - Black Chromate	ZU	1,000	-65°C to +175°C	Yes	No
S	Passivated	Z1	1,000	-65°C to +200°C	Yes	Yes
XS	Nickel-PTFE	ZMT	1,000	-65°C to +175°C	Yes	Yes
YS	Alumiplate™	ZAL	1,000	-65°C to +175°C	Yes	Yes
ZS	Zinc-Nickel - Black Chromate	ZZR	1,000	-65°C to +175°C	Yes	Yes
			Composite Accessories			
J	Cadmium - Olive-Drab Chromate	XW	2000	-65°C to +175°C	Yes	No
L	Cadmium - Olive-Drab Chromate (Selectively Plated)	XX	2000	-65°C to +175°C	Yes	No
М	Electroless Nickel	XM	2000	-65°C to +200°C	Yes	Yes
Т	No Plating	XO	N/A	-65°C to +175°C	No	Yes
XC	Nickel-PTFE	XMT	2000	-65°C to +175°C	Yes	Yes
YC	Alumiplate™	XAL	2000	-65°C to +175°C	Yes	Yes
YL	Alumiplate™ (Selectively Plated)	XAP	2000	-65°C to +175°C	Yes	Yes
ZC	Zinc-Nickel - Black Chromate	XZR	2000	-65°C to +175°C	Yes	Yes
ZL	Zinc-Nickel - Black Chromate (Selectively Plated)	XZS	2000	-65°C to +175°C	Yes	Yes

^{*} Spec Requirement of 500 hours is in error

Galvanic Corrosion and Anodic Index Reference Tables

	Galvanic Corrosion Table	
	Metal	(V)
dic	Gold, solid and plated, Gold-platinum alloy	0.00
tho	Rhodium plated on silver-plated copper	0.05
/Cat	Silver, solid or plated; monel metal. High nickel-copper alloys	0.15
Noble/Cathodic	Nickel, solid or plated, titanium and special alloys such as Monel	0.30
Most No	Copper, solid or plated; low brasses or bronzes; silver solder; German silvery high copper-nickel alloys; nickel-chromium alloys	0.35
ĕ	Brass and bronzes	0.40
	High brasses and bronzes	0.45
	18% chromium type corrosion-resistant steels	0.50
	Chromium plated; tin plated; 12% chromium type corrosion-resistant steels	0.60
	Tin-plate; tin-lead solder	0.65
	Lead, solid or plated; high lead alloys	0.70
	Aluminum, wrought alloys of the 2000 Series	0.75
	Iron, wrought, gray or malleable, plain carbon and low alloy steels	0.85
ي	Aluminum, wrought alloys other than 2000 Series aluminum, cast alloys of the silicon type	0.90
Noble/Anodic	Aluminum, cast alloys other than silicon type, cadmium, plated and chromate	0.95
ble/	Hot-dip-zinc plate; galvanized steel	1.20
8	Zinc, wrought; zinc-base die-casting alloys; zinc plated	1.25
Least	Magnesium & magnesium-base alloys, cast or wrought	1.75
Le	Beryllium	1.85

Galvanic corrosion occurs when dissimilar metals are in contact in the presence of an electrolyte. The corrosion of a metal, the anode, results from the positive current flowing from the anode to the less reactive (more noble) metal, the cathode, through the electrolyte. This form of corrosion has the potential to attack junctions of metals, or regions where one construction metal is changed to another. The critical point is the difference in potential of the two materials being considered as a joined pair.

The "anodic" or "less noble" metals such as magnesium, zinc and aluminium are more likely to be attacked than those at the "cathodic" or "noble" end of the series such as gold and silver.

Environment	Examples	Acceptable Anodic Index Difference
Harsh Environments	Outdoors, high humidity, and salt environments	Not more than 0.15 V difference
Uncontrolled Environments	Storage in warehouses or non-temperature and humidity controlled environments	Not more than 0.25 V difference
Controlled Environments	Temperature and humidity controlled	Not more than 0.50 V difference

QwikConnect

Ex Hazardous Zone and Category

Designations










ATEX EXPLOSIVE ZONES AND CATEGORIES



Explosion Triangle

Purpose of explosion zone connectors and glands

Glenair Series 927-072 ITS-Ex Hazardous Zone Connectors prevent explosions by eliminating the heat component in the explosion triangle. This is accomplished by preventing an ignition source, such as a flame or spark, from migrating through the cable or connector into a defined hazardous zone such as might be found in a petrochemical refinery or land/offshore drilling system. Hazardous zones are defined by frequency of presence of explosive gas or dust.

Hazardous Zone Fuel Types

- Gas, vapor and mists: methane, butane, ethylene, hydrogen, acetylene
- Dust: aluminum, sulfur, zinc grain, coal, sugar, epoxy resin


In the ATEx 1999/92/EC directive, hazardous areas are divided into three defined zones: 0, 1, and 2. These zones are designations used to describe the likelihood that explosive mixtures of fuel and oxygen exist during normal conditions of facility operation.

Zone 0 (20)	Zone 1 (21)	Zone 2 (22)
Area in which an explosive gas (dust) atmosphere is present continuously or for long periods or frequently.	Area in which an explosive gas (dust) atmosphere is likely to occur in normal operation occasionally.	Area in which an explosive gas (dust) atmosphere is likely to occur in normal operation but, if it does occur, will persist for a short period only.

Explosive area zone classifications are used by the operator to distinguish between explosive areas and their relative levels of risk. Operators use the triangular EX mark to indicate compliance with IECEX/ATEX requirements.

Manufacturers however use different classifications to describe where their products may be used.

The two systems generally conform in meaning but the words and symbols change.



Ex Hazardous Zone and Category

Designations









IEC AND ATEX

ATEx 94/9/EC directive classifies the equipment into categories 1,2,3 (Group II), based on protection level. Standard EN/ IEC 60079-0 introduces EPL (Equipment Protection Level).

ATEx	EPL according to IEC/EN 60079-0			
Group II	Gas	Dust		
Category 1	Ga	Da		
Category 2	Gb	Db		
Category 3	Gc	Dc		

The relation between the ATEx 1999/92/EC and the IEC is indicated below: in the Zone 0 you could mount an equipment Ga or 1G (according to 94/9/EC ATEx).

Atmosphere	Zone	EPL	ATEx Category
	0	Ga	1G
Gas	1	Gb or Ga	2G or 1G
	2	Gc or Gb or Ga	3G or 2G or 1G
	20	Da	1D
Dust	21	Db or Da	2D or 1D
	22	Dc or Db or Da	3D or 2D or 1D

Glenair Connectors 927-072 are qualified for Group IIA, IIB, IIC and for Group IIIA, IIIB, IIIC, Category 2 and Category 3.

Category 2	Category 3
Place where explosive atmosphere	Place where explosive atmosphere are
s likely to occur. Provides the	unlikely to occur, or if they do occur
protection level in case of failure of	not frequently and only for a short
he connector/equipment.	period of time.
	Provides the requisite level of
	protection during normal operation.

is for explosive	

Group II	Gases					
шл	Acetone, ethyl alcohol, ammonia, gasoline, butane, hexane,					
IIA	ethanol, natural gas, methanol, propane					
IIB	Acetaldehyde, propane, ethylene					
II.C	Hydrogen, gas mixture containing more than 25% hydrogen,					
IIC	acetylene, carbon disulphide					

GROUP III is for explosive DUST

Group III	Dust					
IIIA	Fibers					
IIIB	Non-conductive dust					
IIIC	Conductive dust					

TEMPERATURE CLASSES

Glenair Series 927-072 ITS-Ex Hazardous Zone Connectors are qualified IAW class T6 to class T1. The temperature class identifies the hottest temperature that the equipment can reach.

Temperature Class	Permissible surface temperatures of the electrical equipment	Ignition temperature of the combustible gases
T1	450 °C	> 450 °C
T2	300 °C	300 - 450 ℃
T3	200 °C	200 - 300 °C
T4	135 ℃	135 - 200 ℃
T5	100 °C	100 - 135 ℃
T6	85 °C	85 - 100 °C

TECHNICAL OVERVIEW

Certified Uses:

- With flammable gases and vapors with apparatus group **IIC and with temperature** classes T6 and T5 in zones 1 and 2
- With flammable dusts with apparatus group IIIC and with temperature classes T80°C and T95°C in zone 21 and 22
- The connectors are certified IP68 (tested at a depth of 10 meters for 30 minutes)

The Glenair ITS-Ex Hazardous Zone series of connectors is comprised of metallic bodies and shells (aluminium alloy standard, optional materials avalaible) with resilient silicone rubber inserts IAW MIL-DTL-5015. Pin or socket crimp contacts are available, and male and female inserts are reversible. Cable plugs and receptacles are available to form in-line cable connections. A fixed flange mount receptacle is available for Ex d boxes and Ex e bulkhead use. Connectors are coupled with a trapezoidal double-start threaded nut retained by grub (set) screws, and form a cylindrical flamepath when mated. When disconnected, plugs and receptacles are mated to an attached protective safety cap (or blanking cap). Absence of cap voids the Ex certification. Mate plug and receptacle caps together when not in use to prevent thread damage. Both plug and receptacle cable configurations are equipped with back-end accessory threads for the attachment of mechanical cable clamps and wire mesh Kellums grip-style attachments (potting required). A third style of rear-end accessory, an industry-standard Ex-certified explosion-proof cable gland, is also available and supplied by Glenair. The Ex certified cable gland does not require potting by the customer to achieve Ex d certified performance.

ATEX / IECEX LABELS

All Glenair ITS-Ex connectors are supplied with a non-removable label containing the following information per ATEx and **IECEx directives:**

ATEx Marking

C € 2460 ⟨Ex⟩

II 2 G Ex db IIC T6, T5 Gb II 2 D Ex tb IIIC T80°C, T95°C Db IP68 -40° C \leq Tamb \leq $+40^{\circ}$ C (T6, T80°C) or $+55^{\circ}$ C (T5, T95°C)

IECEx Marking

Ex db IIC T6, T5 Gb Ex tb IIIC T80°C, T95°C Db IP68 -40° C \leq Tamb \leq $+40^{\circ}$ C (T6, T80°C) or $+55^{\circ}$ C (T5, T95°C)

FOR PANEL MOUNT CONNECTORS ONLY:

ATEx Marking

C € 2460 ⟨Ex⟩



II 2 G Ex de IIC T6, T5 Gb II 2 D Ex tb IIIC T80°C, T95°C Db IP68 $-40oC \le Tamb \le +40°C (T6, T80°C) or +55°C (T5, T95°C)$

IECEx Marking


Ex de IIC T6, T5 Gb Ex tb IIIC T80°C, T95°C Db IP68 $-40oC \le Tamb \le +40°C (T6, T80°C) or +55°C (T5, T95°C)$

	Materials Materi					
ltem	Material					
Hardware Body	Standard Base Material: aluminium alloy EN AW 6082-T6 UNI EN 573-3 (0.7÷1.3% Si, 0.6÷1.2% Mg, <0.2% Ti). All aluminium parts finished with a hard, scratch-resistant coating per MIL-A-8625, type III, class 2.					
Insert	Silicone rubber					
Cable Seal Glands	Silicone rubber					
Grommet and Gasket	Silicone fire resistant rubber					
O-Ring	Silicone MVQ / VMQ					
Grub Screws (Set Screws)	UNI EN 10088-3, Alloy 316, stainless steel, passivated					
Crimp Socket and Pin Contacts	Copper alloy ISO CuZn37Pb2/CuZn35Pb2 (OT61B/OT62A) for size AWG 20, 18, 16, 12 and 8 and copper alloy ISO CuTe for size 4,0 4/0. Both of them are silver plated as standard and gold plated as option.					
Cement for potting	Bi-component epoxy resin (applied by the customer), flame retardant and thermally conductive, cure at room temperature for 24 hours.					


QwikConnect • January 2019 QwikConnect • January 2019

Circular Connector-to-Backshell Interface Standards / Designator Codes

	Circular Connector Front End Dimensional Details							
C	h - II C:						C Dia Mass	D. Eleste Def
	hell Size fo				A Thread Ref	B Dia Max	C Dia Max	D Flats Ref
Α	F/L	G	Н	U				
-	08 09	-	-	-	7/16-28 UNEF	.59 (15.0)	.86 (21.8)	.75 (19.1)
- 08	_	-	09 A -	-	M12 X 1 - 6H 1/2-20 UNF	.65 (16.5) .65 (16.5)		
-	_	_	_	08 9 A B	1/2-28 UNEF	.65 (16.5)	.98 (24.9)	.88 (22.2)
03	10 11	-	-	-	9/16-24 UNEF	.72 (18.3)	150 (2 115)	.00 (22.2)
-	-	-	11 B	-	M15 x 1 - 6H	.77 (19.6)		
10	-	-	-	-	5/8-24 UNEF	.77 (19.6)		
-	-	-	-	10 11 C D	5/8-28 UN	.77 (19.6)	1.16 (29.4)	1.00 (25.4)
-	12 13	-	-	-	11/16-24 UNEF	.84 (21.3)		
-	-	-	13 C	-	M18 x 1 - 6H	.89 (22.6)		
12 7	-	11 A	-	-	3/4-20 UNEF	.91 (23.1)		
-	-	-	-	12 13 F	3/4-28 UNS	91 (23.1)	1.28 (32.5)	1.13 (28.6)
-	14 15	-	-	-	13/16-20 UNEF	.97 (24.6)		
-	-	-	-	-	M22 x 1 - 6H	1.03 (26.2)		
14 12	-	13 B	13 B	-	7/8-20 UNEF	1.03 (26.2)		
-	-	-	-	14 15 G H	7/8-28 UN	1.03 (26.2)	1.41 (35.7)	1.25 (31.8)
-	16 17	-	-	-	15/16-20 UNEF	1.09 (27.7)		
-	-	-	17 E	-	M25 x 1 - 6H	1.15 (29.2)		
16 19	-	15 C	-	-	1-20 UNEF	1.15 (29.2)		
-	-	-	-	16 17 J K	1-28 UN	1.15 (29.2)	1.52 (38.5)	1.38 (35.1)
18 27	18 19	-	-	-	1-1/16-18 UNEF	1.22 (31.0)		
-	-	-	19 F	-	M28 x 1 - 6H	1.28 (32.5)		
-	-	17 D	-	-	1-1/8-18 UNEF	1.28 (32.5)		
-	-	-	-	18 19 M N	1-1/8-28 UN	1.28 (32.5)	1.64 (41.7)	1.50 (38.1)
20 37	20 21	-	-	-	1-3/16-18 UNEF	1.34 (34.0)		,
-	-	-	21 G	-	M31 x 1 - 6H	1.41 (35.8)		
-	-	19 E	-	-	1-1/4-18 UNEF	1.41 (35.8)		
-	-	-	-	20 21 P R	1-1/4-28 UN	1.41 (35.8)	1.77 (44.9)	1.63 (41.3)
22	22 23	-	-	-	1-5/16-18 UNEF	1.47 (37.3)		
-	-	-	23 H	-	M34 x 1 - 6H	1.53 (38.9)		
-	-	-	-	22 23 S T	1-3/8-28 UN	1.53 (38.9)	1.89 (48.0)	1.75 (44.5)
24	24 25	23 F	-	-	1-7/16-18 UNEF	1.59 (40.4)		
-	-	-	25 J	-	M37 x 1 - 6H	1.66 (42.2)		
61	-	-	-	-	1-1/2-18 UNEF	1.66 (42.2)		
-	-	-	-	24 25 U M	1-1/2-28 UN	1.66 (42.2)	2.02 (51.2)	1.88 (47.6)
-	-	25 G	-		1-9/16-18 UNEF	1.66 (42.2)		2.00 (50.8)
28	-	-	-	-	1-3/4-18 UNS	1.97 (50.0)	2.16 (54.8)	-



- 1. Connector shell size designations in blue are for reference only; do not use in part numbers.
- **2.** Metric dimensions (mm) are in parentheses and are for reference only. (1 inch = 25.4 mm)
- **3.** Consult factory for accessory interface data not listed.
- **4.** Use Glenair 600-091 or 600-157 tool to tighten coupling nut. Rubber jaw pliers or strap wrench may damage the parts.



QwikConnect

Anti-Decoupling

Coupling Nut

Flutes or Knurl

(Mfr. Option)

(Mfr. Option)

Connector

Designator

SPECIFICATION

MIL-DTL-5015 MIL-DTL-26482 MIL-C-81703 MIL-DTL-83723 40M39569 DEF 5326-3 LN 29504 NFC 93422 PAN 6432-1

SERIES

1 & 3

Environmental seal performed by interface geometry.

* Consult factory for direct coupling part numbers.

Direct Coupling

Note: Code A, rotatable coupling supplied without O-ring.

Follower

(Mfr. Option)

MS34XX

HE 302

PAN 6432-2 PATT 602 EN2997

Connector

Designator

SPECIFICATION


MIL-DTL-38999 40M38277 NFC 93422 NFC93422 PAN 6433-1 PATT 614

PATT 616

SERIES

1 & II NLS HE 309 HE 308

A Thread **Direct Coupling ***




Note: Direct coupling supplied with O-ring for moisture sealing. Add modifier code 101A to end of part number for O-ring to be supplied on rotatable coupling.

* Consult factory for direct coupling part numbers.

Connector Designator

SPECIFICATION

MIL-DTL-28840



Note: Code G, rotatable coupling is supplied without O-ring. Environmental seal performed by interface geometry.

* Consult factory for direct coupling part numbers.

Circular Connector-to-Backshell Interface Standards / Designator Codes

Circular Connector Common Interface Standards Anti-Decoupling (Mfr. Option) Rotatable Connector Coupling **Designator SPECIFICATION SERIES** MIL-DTL-38999 III & IV EN3645 **Direct Coupling** Flutes or Knurl (Mfr. Option)


Note: Direct coupling supplied with O-ring for moisture sealing. Add modifier code 101A to end of part number for O-ring to be supplied on rotatable coupling.

* Consult factory for direct coupling part numbers.

Connector **Designator**

SPECIFICATION

EN3372 JN1003 LN 29729 NFC93422 PAN 6433-2 PATT 615 VG 96912




Note: Direct coupling supplied with O-ring for moisture sealing. Add modifier code 101A to end of part number for O-ring to be supplied on rotatable coupling.

* Consult factory for direct coupling part numbers.

Connector Designator

SPECIFICATION

MIL-C-29600




Note: Direct coupling supplied with O-ring for moisture sealing. Add modifier code 101A to end of part number for O-ring to be supplied on rotatable coupling.

QwikConnect

Connector Manufacturers' Index for Backshell and Accessory Specifications

MFG SERILES GLANAIR CONNECTOR DESIGNATOR SPECIFICATION REFERENCE SERILES CLEMANR CONNECTOR DESIGNATOR SI Aero-Electric Connector Company MILDTL-38999 III								
AE22 H MIL-DTL-38999 III AE46 F MIL-DTL-38999 I AE47 F MIL-DTL-38999 II AE48 F MIL-DTL-38999 II AE49 F MIL-DTL-38999 I AE55 A SAE AS50151 MS3400 AE66 E MIL-DTL-26500 Aluminum AE77 A MIL-DTL-83723 III AE83 A MIL-DTL-38999 II ABB Electronics CT-R F MIL-DTL-38999 II CT-R F MIL-DTL-38999 II MK 8 S PATT 105 SM B S/A MK 12 S PATT 603 TV H M SC B S/A SJT L JN 1003 10-214 B S/A SJT L LN29729 TVS H TVS H TVS H M TVS H M TVS H M TVS H M <t< th=""><th>MFG SERIES</th><th>CONNECTOR</th><th></th><th>SERIES</th><th></th><th>MFG SERIES</th><th>CONNECTOR</th><th></th></t<>	MFG SERIES	CONNECTOR		SERIES		MFG SERIES	CONNECTOR	
AE46 F MIL-DTL-38999 II AE47 F MIL-DTL-38999 II AE48 F MIL-DTL-38999 II AE49 F MIL-DTL-38999 II AE55 A SAE AS50151 MS3400 AE66 E MIL-DTL-26482 II AE77 A MIL-DTL-83723 III ABB Electronics CT-R F MIL-DTL-38999 II MK 8 S S PATT 105 MK 12 S PATT 603 MK 12 S PATT 603 MK 12 S PATT 603 SJT L JN 1003 10-214 B SS SJT L JN 1003 10-214 B SS SJT L PAN 6433-1 TV H M M TVS H M TVS H M AE8 E M AE8 A LIN 29729 1II AB8 A LIN 29504 69 B SS AB8 J VG 95329 1II AB8 A PATT 616 15 AIR A MAIL-DTL-26482 H A PATT 616 615 AIR AB9 A PATT 616 15 AB8 A PATT 602 418-5 L NFC 93422 HE 306 APPHODUCTS BG D MIL-DTL-26482 I M AMPhenol Products BG D MIL-DTL-26482 I M AIL-DTL-26482 I M AIL-DTL-26482 I M AMPhenol/PyleNational AAPPhenolProducts BG D MIL-DTL-26482 I M AIL-DTL-26482 I M	Aero-Electric (Connector Company	1			Amphenol Pro	ducts (Continued)	
AE46 F MIL-DTL-38999 II AE47 F MIL-DTL-38999 II AE48 F MIL-DTL-38999 II AE49 F MIL-DTL-38999 II AE55 A SAE AS50151 MS3400 AE66 E MIL-DTL-26500 Aluminum AE77 A MIL-DTL-26500 Aluminum AE83 A MIL-DTL-38723 III AB8 Electronics CT-R F MIL-DTL-38723 III CWLD C MM AB8 S S PATT 105 SJT L S PATT 603 SJT L JN 1003 TV H M M M AB9 A LN 29504 BA8 J VG 95329 TIB A MM AE8 A MA LN 29504 THE AB9 B S M TO ATT 615 THE AB9 B S M THE AB A M M AE47 F MIL-DTL-38999 II AF1 C D M AF2 D M AF3 D M AF48 F M AF48 F M AF5 D M AF	AE22	Н	MIL-DTL-38999	III	_	JT-R	F	40
AE48 F MIL-DTL-38999 II MF-S D M M AE49 F MIL-DTL-38999 II MF-S D M M AE49 F MIL-DTL-38999 II M AE55 A SAE AS50151 MS3400 AE66 E MIL-DTL-26500 Aluminum AE77 A MIL-DTL-26482 II MAE49 F MIL-DTL-38723 III M MF-S D M M M M M M M M M M M M M M M M M M	AE46	F	MIL-DTL-38999	I		LJT	*	Μ
AE49 F MIL-DTL-38999 I	AE47	F	MIL-DTL-38999	II		LJT-R	F	М
AE55 A SAE AS50151 MS3400 AE66 E MIL-DTL-26500 Aluminum AE77 A MIL-DTL-26482 II AE83 A MIL-DTL-83723 III AB Electronics CT-R F MIL-DTL-38999 II MK 8 S S PATT 603 MK 12 S PATT 603 MK 12 S PATT 608 MK 18 S PATT 608 MK 18 S PATT 608 MK 19 PTS-DR A M M B S S PATT 603 MK 10 PTS-DR A M M B S S PATT 603 MK 10 PTS-DR A M M M P	AE48	F	MIL-DTL-38999	II		MF-S	D	Μ
AE66 E MIL-DTL-26500 Aluminum PTS-DR A M AE77 A MIL-DTL-26482 II PTS-DR A M AE83 A MIL-DTL-38723 III QWLD C M AB Electronics CT-R F MIL-DTL-38999 II SC B S/ CT-R F MIL-DTL-38999 II SC B S/ MK 12 S PATT 603 TV H M B S/ MK 18 S PATT 608 TVV H M TVVRB H M TVVS H M M M M M M M M M M M M M M M	AE49	F	MIL-DTL-38999	I		PT	D	М
AE77 A MIL-DTL-26482 II QWLD C M AE83 A MIL-DTL-38723 III QWLD C M SC B S SC B S S SC B S S S S PATT 105 S M B S S PATT 603 S S PATT 603 S S S S PATT 603 S S S PATT 604 S S S PATT 605 S S PATT 605 S S PATT 605 S S PATT 605 S S S PATT 605 S S PATT	AE55	Α	SAE AS50151	MS3400	2	PT-SE	D	М
AE83 A MIL-DTL-83723 III AB Electronics CT-R F MIL-DTL-38999 II MK 8 S S PATT 105 MK 12 S PATT 603 MK 12 S PATT 608 Amphenol Limited JT F PAN 6433-1 III INT F PAN 6433-1 III III III III III III III	AE66	E	MIL-DTL-26500	Aluminum		PTS-DR	A	М
SCC B SCC S SCC S SCC S SCC S S	AE77	A	MIL-DTL-26482	II		PTS-DR	Α	Μ
CT-R F MIL-DTL-38999 II SJT L	AE83	Α	MIL-DTL-83723	III		QWLD	С	М
MK 8 S PATT 105 SM B S MK 12 S PATT 603 TV H M MK 18 S PATT 608 TVRB H CI Amphenol Limited TVS H M M JT F PAN 6433-1 10-72 B 55 SJT L LN29729 10-214 B 55 SJT L PAN 6433-2 48 E M 118 A LN 29504 69 B S/A 162GB S PATT 603 97 B S/A 418-1 F PATT 616 9 B S/A 418-2 F PATT 614 246 * S/A 418-5 L NFC 93422 HE 306 348 J 348 J S/A 418-5 L PATT 615 418-1 F M 602GB A PAN 6	AB Electronics	3			(SC	В	SA
MK 12 S PATT 603 TV H M MK 18 S PATT 608 TVRB H CI Amphenol Limited TVS H M M JT F PAN 6433-1 10-72 B 55 SJT L LN29729 10-214 B 55 SJT L PAN 6433-2 69 B 55 118 A LN 29504 69 B 55 162GB S PATT 603 97 B 56 348 J VG 95329 118 A M 418-1 F PATT 616 97 B 56 418-5 L NFC 93422 HE 306 348 J	CT-R	F	MIL-DTL-38999	II		SJT	L	LI
MK 18 S PATT 608 TVRB H CI Amphenol Limited TVS H M JT F PAN 6433-1 10-72 B S/ SJT L LN29729 TO-214 B S/ SJT L PAN 6433-2 TO-214 B S/ SJT L PAN 6433-2 48 E M 118 A LN 29504 48 E M 162GB S PATT 603 97 B S/ 418-1 F PATT 616 97 B S/ 418-2 F PATT 616 118 A M 418-5 L NFC 93422 HE 306 348 J S/ 418-5 L PATT 615 418-1 F M 602GB A PATT 602 518 A M 652 A LN 29504 91-483	MK	8	S	PATT 105		SM	В	SA
Amphenol Limited JT F PAN 6433-1 10-72 B S/J SJT L LN29729 10-214 B S/J SJT L PAN 6433-2 10-214 B S/J 118 A LN 29504 48 E M 188 A LN 29504 969 B S/J 188 A LN 29504 97 B S/J 188 J VG 95329 118 A M 418-1 F PATT 616 97 B S/J 418-2 F PATT 616 97 B S/J 418-5 L NFC 93422 HE 306 91 348 J S/J 418-5 L PATT 615 418-1 F M 602GB A PAN 6432-1 418-2 F M 652 A LN 29504 91-483 A M	MK	12	S	PATT 603		TV	Н	М
JT F PAN 6433-1 10-72 B S/J SJT L JN 1003 10-214 B S/J SJT L LN29729 10-475 F 40 SJT L PAN 6433-2 48 E M 118 A LN 29504 69 B S/J 162GB S PATT 603 97 B S/J 418-1 F PATT 616 9 118 A M 418-2 F PATT 616 9 118 A M 418-5 L NFC 93422 HE 306 9 348 J S/J 418-5 L PATT 615 418-1 F M 602GB A PAN 6432-1 418-2 F M 652 A LN 29504 9 91-483 A M <tr< td=""><td>MK</td><td>18</td><td>S</td><td>PATT 608</td><td></td><td>TVRB</td><td>Н</td><td>CI</td></tr<>	MK	18	S	PATT 608		TVRB	Н	CI
SJT L JN 1003 SJT L LN29729 - 40 SJT L PAN 6433-2 48 E M 118 A LN 29504 69 B S/ 162GB S PATT 603 97 B S/ 348 J VG 95329 118 A M 418-1 F PATT 616 118 A M 418-2 F PATT 614 246 * 3/ 418-5 L NFC 93422 HE 306 348 J 3/ 3/ 3/ 418-1 F M 602GB A PATT 602 418-2 F M 602GB A PATT 602 518 A M 652 A LN 29504 418-2 F M 71 B 91-483 <t< td=""><td>Amphenol Lin</td><td>nited</td><td></td><td></td><td></td><td>TVS</td><td>Н</td><td>М</td></t<>	Amphenol Lin	nited				TVS	Н	М
SJT L LN29729 SJT L PAN 6433-2 118 A LN 29504 162GB S PATT 603 348 J VG 95329 418-1 F PATT 616 418-2 F PATT 614 418-5 L NFC 93422 HE 306 418-5 L PATT 615 602GB A PATT 602 602GB A PATT 602 62GB S PATT 105 652 A LN EN PATT 105 652 A MIL-DTL-26482 I JT * MIL-C-27599 10-475 F 40 48 E MM 69 B S 69 B S 97 B S 48 A E MM 69 B S 48 A E MM 69 B S 69	JT	F	PAN	6433-1		10-72	В	SA
SJT L PAN 6433-2 48 E M 118 A LN 29504 69 B S/A 162GB S PATT 603 97 B S/A 348 J VG 95329 118 A M 418-1 F PATT 616 97 B S/A 418-2 F PATT 616 97 B S/A 418-5 L NFC 93422 HE 306 94 118 A M 418-5 L PATT 615 418-1 F M 602GB A PAN 6432-1 418-2 F M 602GB A PATT 602 518 A M 652 A LN 29504 91-483 A M Amphenol Products B A M Amphenol/Pyle National B JT * MIL-C-27599 A M M Amphenol/Pyle National B <td>SJT</td> <td>L</td> <td>JN</td> <td>1003</td> <td></td> <td>10-214</td> <td>В</td> <td>SA</td>	SJT	L	JN	1003		10-214	В	SA
118 A LN 29504 69 B S/A 162GB S PATT 603 97 B S/A 348 J VG 95329 118 A M 418-1 F PATT 616 118 A M 418-2 F PATT 614 246 * S/A 418-5 L NFC 93422 HE 306 348 J 3/4 418-5 L PATT 615 418-1 F M 602GB A PAN 6432-1 418-2 F M 62GB S PATT 105 518 A M 652 A LN 29504 91-483 A M Amphenol Products B A M M JT * MIL-DTL-26482 I A Amphenol/Pyle National B	SJT	L	LN29729			10-475	F	40
162GB S PATT 603 97 B S/A 348 J VG 95329 118 A M 418-1 F PATT 616 118 A M 418-2 F PATT 614 246 * S/A 418-5 L NFC 93422 HE 306 9 348 J S/A 418-5 L PATT 615 418-1 F M 602GB A PAN 6432-1 418-2 F M 602GB S PATT 105 518 A M 652 A LN 29504 91-483 A M Amphenol Products B A M M JT * MIL-DTL-26482 I A Amphenol/Pyle National B A M	SJT	L	PAN	6433-2		48	E	М
348 J VG 95329 118 A M 418-1 F PATT 616 H 118 A M 418-2 F PATT 614 246 * 57 418-5 L NFC 93422 HE 306	118	Α	LN	29504		69	В	SA
348 J VG 95329 118 A M 418-1 F PATT 616 9 118 A M 418-2 F PATT 614 246 * SJ 418-5 L NFC 93422 HE 306 9 348 J SJ 418-5 L PATT 615 418-1 F M 602GB A PATT 602 91-483 A M 62GB S PATT 105 91-483 A M Amphenol Products B A M M MIL-DTL-26482 I Amphenol/Pyle National B A M	162GB	S	PATT	603		97	В	SA
418-2 F PATT 614 246 * SA 418-5 L NFC 93422 HE 306 348 J SA 418-5 L PATT 615 418-1 F M 602GB A PATT 602 418-2 F M 602GB S PATT 105 518 A M 652 A LN 29504 91-483 A M Amphenol Products I MIL-DTL-26482 I Amphenol/Pyle National B A Amphenol/Pyle National B A M M M Amphenol/Pyle National B A M	348	J	VG	95329	7	118	Α	М
418-5 L NFC 93422 HE 306 348 J SA 418-5 L PATT 615 418-1 F M 602GB A PATT 602 418-2 F M 602GB S PATT 105 518 A M 652 A LN 29504 91-483 A M Amphenol Products BG D MIL-DTL-26482 I I Amphenol/Pyle National B A M	418-1	F	PATT	616	Э	118	A	М
418-5 L PATT 615 418-1 F M 602GB A PAN 6432-1 418-2 F M 602GB A PATT 602 518 A M 652 A LN 29504 91-483 A M Amphenol Products B D MIL-DTL-26482 I I Amphenol/Pyle National JT * MIL-C-27599 B A M	418-2	F	PATT	614		246	*	SA
602GB A PAN 6432-1 418-2 F M 602GB A PATT 602 518 A M 652 A LN 29504 91-483 A M Amphenol Products I 91-483 A M JT * MIL-DTL-26482 I Amphenol/Pyle National JT * MIL-C-27599 B A M	418-5	L	NFC 93422	HE 306	Э	348	J	SA
602GB A PATT 602 518 A M 62GB S PATT 105 71 B SA 652 A LN 29504 91-483 A M Amphenol Products F Amphenol/Pyle National B Amphenol/Pyle National B A Amphenol/Pyle National JT * MIL-C-27599 B A M	418-5	L	PATT	615		418-1	F	Μ
62GB S PATT 105 652 A LN 29504 Amphenol Products BG D MIL-DTL-26482 I JT * MIL-C-27599 71 B S/ 91-483 A M Amphenol/Pyle National B A M	602GB	Α	PAN	6432-1		418-2	F	М
62GB S PATT 105 71 B S/A 652 A LN 29504 91-483 A M Amphenol Products I 91-483 A M JT * MIL-DTL-26482 I Amphenol/Pyle National B A M	602GB	Α	PATT	602	\ominus	518	Α	Μ
Amphenol Products BG D MIL-DTL-26482 I JT * MIL-C-27599 91-483 A M Amphenol/Pyle National B A M	62GB	S	PATT	105		71	В	SA
BG D MIL-DTL-26482 I Amphenol/Pyle National JT * MIL-C-27599 B A M	652	Α	LN	29504	Θ	91-483	Α	М
JT * MIL-C-27599 B A M	Amphenol Pro	oducts				91-483	Α	М
JI WILE-C-27599	BG	D	MIL-DTL-26482	I		Amphenol/Py	le National	
JT-R F MIL-DTL-38999 II T3 H M	JT	*	MIL-C-27599			В	Α	М
	JT-R	F	MIL-DTL-38999	II		T3	Н	М

	MFG SERIES	GLENAIR CONNECTOR DESIGNATOR	SPECIFICATION REFERENCE	SERIES
	Amphenol Pro	ducts (Continued)		
_	JT-R	F	40M38277	
	LJT	*	MIL-C-27599	
	LJT-R	F	MIL-DTL-38999	1
	MF-S	D	MIL-DTL-26482	1
	PT	D	MIL-DTL-26482	1
	PT-SE	D	MIL-DTL-26482	1
	PTS-DR	A	MIL-DTL-26482	II
	PTS-DR	Α	MIL-DTL-83723	1
	QWLD	С	MIL-DTL-22992	R
(SC	В	SAE AS50151	MS3100
	SJT	L	LN	29729
	SM	В	SAE AS50151	MS3100
	TV	Н	MIL-DTL-38999	III
ĺ	TVRB	Н	CECC 75201.002	III
	TVS	Н	MIL-DTL-38999	III
	10-72	В	SAE AS50151	MS3100
	10-214	В	SAE AS50151	MS3100
	10-475	F	40M38277	
	48	E	MIL-DTL-26500	Aluminum
	69	В	SAE AS50151	MS3100
	97	В	SAE AS50151	MS3100
	118	Α	MIL-DTL-26482	II
)	118	Α	MIL-DTL-83723	1
	246	*	SAE AS50151	
)	348	J	SAE AS81511	I-II
	418-1	F	MIL-DTL-38999	1
	418-2	F	MIL-DTL-38999	II
)	518	Α	MIL-DTL-83723	III
1	71	В	SAE AS50151	MS3100
)	91-483	A	MIL-DTL-26482	II
_	91-483	A	MIL-DTL-83723	1
	Amphenol/Py	le National		
	В	A	MIL-DTL-83723	III
	T3	Н	MIL-DTL-38999	III



QwikConnect • January 2019

Connector Manufacturers' Index for Backshell and Accessory Specifications

MFG SERIES	GLENAIR CONNECTOR DESIGNATOR	SPECIFICATION REFERENCE	SERIES	MFG SERIES	GLENAIR CONNECTOR DESIGNATOR	SPECIFICATION REFERENCE	SERIES
Amphenol/Pyl	e National (Contin	ued)		Deutsch Engir	neered Connecting	Devices (Continued)	
ZZW	Е	MIL-DTL-26500	Aluminum	837	Α	MIL-DTL-83723	III
ZZY	Е	MIL-DTL-26500	Aluminum	Deutsch Limit	ed		
	A	ESC 10, ESC 11		LL	J	SAE AS81511	III-IV
Amphenol/Tuo	hel Electronics Gn	nbH		DBAS	Α	PAN	6432-2
118	A	LN	29504	DTS	Н	MIL-DTL-38999	III
162GB	*	VG	95328	HDJ	L	JN	1003
348	J	VG	95329	RR	Α	PAN	6432-1
602GB	Α	DEF	5326-3	RR	Α	PATT	602
602GB	Α	PAN	6432-1	RR70	Α	QPL-81703	III
602GB	Α	PATT	602	SLPT	*	MIL-DTL-26482	T
62GB	*	DEF	5326-3	Glenair			
652	Α	LN	29504	90	G	MIL-DTL-28840	
Cie Deutsch &	Compagnie Deuts	ch GmbH		80	M	Mighty Mouse	800 Thru 805
AFD	Α	LN	29504	22	W	Geo-Marine®	
AFD	Α	MIL-DTL-26482	1	ITS, IT	R	SAE AS50151	
AFD	Α	PAN	6432-1	231	F	MIL-DTL-38999	I
DBAS	Α	QPL-81703	III	232	F	MIL-DTL-38999	II
DBAS	Α	PAN	6432-2	233	Н	MIL-DTL-38999	III
DFE	A	LN	29504	Souriau			
DVG	A	VG	95328	BT	D	MIL-DTL-26482	I
FDBA	A	LN	29504	G	D	MIL-DTL-26482	T
951	A	PRL	53125	L	D	MIL-DTL-26482	I
9.815	J	SAE AS81511	III & IV	L-T	D	MIL-DTL-26482	I .
991	A	PAN	6432-4	M-T	D	MIL-DTL-26482	I
999.1	F	MIL-DTL-38999	I	JVS	Н	CECC 75201.002	
	A	ESC 10		8LT	F	MIL-DTL-38999	1
	Α	ESC 11		8LT	F	NFC 93422	HE 308
Deutsch Engin	eered Connecting	Devices		8ST	L	JN 1003	8ST-034
AFD5	A	MIL-DTL-26482	II	8ST	L	LN 29729	
AFD	Α	MIL-DTL-83723	I	8ST	L	NFC 93422	HE 306
A815	J	SAE AS81511	III	8ST	L	PAN 6433-2	
B815	J	SAE AS81511	IV	8ST	L	PATT 615	
BMS	E	MIL-DTL-26500		8ST	L	VG 96912	
BTK	D	MIL-DTL-26482	ı	8T	F	MIL-DTL-38999	II
DBA	A	40M39569		8T	F	NFC 93422	HE 309
DBA7	Α	QPL-81703	III	85	D	MIL-DTL-26482	I
DTS	Н	MIL-DTL-38999	III	851	S	PATT 603	
DIV4	Н	MIL-DTL-38999	IV	851-50	*	NFL53125	
DL6	A	MIL-DTL-83723	III	851-50	*	VG 95328	
D817	Α	QPL-81703	III	8525	A	NFC 93422	HE 302
LPT	D	MIL-DTL-26482	I	8525.1	A	LN 29504	
381	Α	40M39569		8526	A	MIL-DTL-26482	II
450	D	MIL-DTL-26482	I	8526	A	PAN 6432-1	
460	D	MIL-DTL-26482		8526	Α	PATT 602	

			$\overline{\Box}$							Θ	\Box
		Θ	Θ		Θ	Θ			/∈		Θ
/	Θ	Θ		Θ	()	Θ		Θ	Θ	Θ
	Θ		0		e e	Θ	Θ		\ominus	Θ	Θ.
	Θ	θ					6/	\	Θ	Θ	(
			Θ	Θ	Θ				\ e	, ∈) (
		0	Θ		Α	θ				Θ	Θ
											_

QwikConnect

	MFG SERIES	GLENAIR CONNECTOR DESIGNATOR	SPECIFICATION REFERENCE	SERIES
	Souriau (conti	nued)		
	8533	Α	EN 2992	
	8533	Α	ESC 10	
/-	8534	Α	ESC 11	8534
	Flight Connec	tor Corporation		
	FC	*	SAE AS50151	
	FF	A	SAE AS50151	MS3400
	FH	*	SAE AS50151	
\setminus	FHA	K	MIL-DTL-83723	II
\downarrow	PL	Н	MIL-DTL-38999	IV
	G & H Technolo	ogies		
	BL	Н	MIL-DTL-38999	IV
	NC	G	MIL-DTL-28840	
	ITT Cannon			
	CA3106B	*	VG95234	
	CA-E / R	В	SAE AS50151	MS3100
	CA-RX	В	SAE AS50151	MS3100
	CVA	K	MIL-DTL-83723	II
	CV340	Α	SAE AS50151	MS3400
1	CV345	A	SAE AS50151	MS3450
/_	KFS	G	MIL-DTL-28840	
$' \in$	KJ	F	MIL-DTL-38999	II
	KJ	F	40M38277	
Θ	KJA	Н	MIL-DTL-38999	III
Д	KJL	F	MIL-DTL-38999	1
igwedge	KPSE	D	MIL-DTL-26482	1
	KPT	D	MIL-DTL-26482	1
+	MF	Α	MIL-DTL-83723	III
	PV-G	A	40M39569	
	PVA	A	MIL-DTL-83723	1
	PV7	Α	MIL-DTL-26482	II
	Α	ESC 10	KE, SE	
		ectric France SA		
	KJ	F	MIL-DTL-38999	II
	KJ	F	PAN	6433-1
	KJL	F	MIL-DTL-38999	1
	251	*	MIL-DTL-26482	I
	ITT Cannon Uk			
	KJ	F	PATT	614
1	KPSE	D .	MIL-DTL-26482	
1	PV-S	A	MIL-DTL-83723	I
	PVW	A	LN29504	
	PVX	A	PAN	6432-1
	PVX	A FSC 10	PATT KE SE	602
	Δ	FSC 10	K E S E	

	MFG SERIES	GLENAIR CONNECTOR DESIGNATOR	SPECIFICATION REFERENCE	SERIES
\uparrow	ITT Cannon Ele	ctric GmbH		
	CA3106B	*	VG 95234	
	CGK	L	LN 29729	
	CWLD	С	MIL-DTL-22992	R
,	KJ	F	PAN 6433-1	
	KPSE	*	VG 95328	
	KPT	*	VG 95328	
	PVW	Α	LN 29504	
10	PVX	A	PAN 6432-1	
Ť	J-Tech			
	JT 3400	Α	SAE AS50151	MS3400
	JT 3450	Α	SAE AS50151	MS3450
	JTVG95234	Α	VG95234	
	Labinal/Cinch			
	CNO930	Α	MIL-DTL-83723	III
	48	Е	MIL-DTL-26500	Aluminum
	RMS			
\setminus	RO	MIL-DTL-26500	Aluminum	
$+\epsilon$	Schaltbau Gml	ьн		
	650	J	VG 95329	
)	674	*	VG 95328	
)	675	*	VG 95328	
	679	J	VG 95329	
)	SICEM			
+	SCB	*	VG 95234	
	Sunbank			
)	JSC	MIL-DTL-28840		
	ITT Cannon			
>	TT	F	PAN 6433-1	
	PT	S	PATT 105	
	PT-SE	S	PATT 603	
	STT	L	LN 29729	
	STT	L	PAN 6433-2	
	STT	L	PATT 615	
	STT	L	VG 96912	
	ITT VEAM			
	CIR	*	VG 95234	
	VPT	D	MIL-DTL-26482	1
	VPT-SE	*	MIL-DTL-26482	I
	VPT-SE	*	VG 95328	
	K			

AS85049 Qualified Backshells and Connector Accessories

Part No.	Description				
AS85049/1	Straight Strain Relief				
AS85049/2	Straight Environmental Strain Relief				
AS85049/3	Straight Environmental Backshell				
AS85049/4	Straight Step-Up Environmental Backshell				
AS85049/5	Straight Step-Down Environmental Backshell				
AS85049/6	45° RFI/EMI Environmental Backshell				
AS85049/7	45° Environmental Backshell				
AS85049/8	90° RFI/EMI Environmental Backshell				
AS85049/9	90° Environmental Backshell				
AS85049/10	Straight RFI/EMI Environmental Backshell				
AS85049/11	Straight Environmental Backshell				
AS85049/14	E Nuts				
AS85049/15	45° Qwik-Ty® Strain Reliefs				
AS85049/16	90° Qwik-Ty® Strain Reliefs				
AS85049/17	Straight RFI/EMI Environmental Backshell				
AS85049/18	Straight RFI/EMI Environmental Backshell				
AS85049/19	Straight Environmental Backshell				
AS85049/20	Straight Crimp Ring Backshell and Crimp Ring				
AS85049/21	Straight Non-Environmental Strain Relief				
AS85049/23	45° RFI-EMI Non-Environmental Backshell				
AS85049/24	90° RFI-EMI Non-Environmental Backshell				
AS85049/25	Straight RFI-EMI Non-Environmental Backshell				
AS85049/26	Adapter / Crimp Ring				
AS85049/27	E Nuts				
AS85049/28	Strt. Rectangular Non-Environmental Backshell				
AS85049/29	Straight Non-Environmental Strain Relief				
AS85049/30	Straight RFI-EMI Shield Termination Backshell				
AS85049/31	E Nuts				
AS85049/33	Straight Crimp Ring Non-Env. Backshell				
AS85049/34	Straight Adapter and Extender				
AS85049/36	Straight RFI-EMI Non-Environmental Backshell				
AS85049/37	90° RFI-EMI Non-Environmental Backshell				
AS85049/38	Straight Strain Reliefs				
AS85049/39	90° Strain Reliefs				
AS85049/41	Straight Strain Relief				
AS85049/42	Straight Strain Relief				
AS85049/43	45° Strain Relief				
AS85049/44	Straight Rectangular Strain Relief Backshell				
AS85049/45	Straight Strain Relief				
AS85049/46	90° Non-Self-Locking Composite Strain Relief				
AS85049/47	90° Strain Reliefs				
AS85049/48	Rectangular Strain Relief Backshell				
AS85049/49	Straight Strain Relief				
AS85049/50	Rectangular Strain Relief Backshell				
AS85049/51	90° Strain Reliefs				
AS85049/52	Straight Strain Reliefs				

Part No.	Description			
AS85049/53 /54 /55	Qwik-Ty® Strain Reliefs			
AS85049/56 /57	Qwik-Ty® Strain Reliefs			
AS85049/58	Potting Boot Ring			
AS85049/59	Straight Shrink Boot Adapter			
AS85049/60	Straight Shrink Boot Adapters			
AS85049/61	Potting Boot Ring			
AS85049/62	Straight Shrink Boot Adapter			
AS85049/63	90° Qwik-Ty® Strain Relief			
AS85049/69	Straight Shrink Boot Adapter			
AS85049/74	Potting Boot			
AS85049/75	Potting Boot			
AS85049/76	90° EMI/RFI Environmental Backshell			
AS85049/77	45° EMI/RFI Environmental Backshell			
AS85049/78	45° EMI/RFI Environmental Backshell			
AS85049/79	90° EMI/RFI Environmental Backshell			
AS85049/80	Sealing Plug, Sizes 8, 12 and 16			
AS85049/81	Sealing Plug			
AS85049/82 /83 /84	Banding Backshells			
AS85049/85 /86 /87	Banding Backshells			
AS85049/88 /89 /90	Banding Backshells			
AS85049/91/92	Strain Reliefs			
AS85049/93	Banding Split Ring			
AS85049/94	Full Perimeter Mounting Flange			
AS85049/95	3/4 Perimeter Mounting Flange			
AS85049/96	1/4 Perimeter Mounting Flange			
AS85049/103	Straight Shield Sock Composite Adapter			
AS85049/104	45° Shield Sock Composite Adapter			
AS85049/105	90° Shield Sock Composite Adapter			
AS85049/109 AS85049/111	Straight Shield Sock Shrink Boot Adapter 90° Shield Sock Sock Shrink Boot Adapter			
AS85049/111	Straight Shield Sock Sock Shrink Boot Adapter			
AS85049/114	90° Shield Sock Shrink Boot Adapter			
AS85049/115	Straight Shield Sock Shrink Boot Adapter			
AS85049/118	Straight Strain Relief			
AS85049/120	90° Strain Relief			
AS85049/121	Straight Strain Relief			
AS85049/123	90° Strain Relief			
AS85049/124	Sraight Strain Relief			
AS85049/126	90° Strain Relief			
AS85049/127	Bushing Strip			
AS85049/128-3, -4	Clamping Bands			
AS85049/130	Gasket			
AS85049/139	Telescoping Bushing, C or L			
AS85049/140	Straight Lipped Heat Shrink Boots			
AS85049/141	90° Lipped Heat Shrink Boots			
AS85049/142	Wide Body Heat Shrink Boot Transitions			

QwikConnect

Recommended Backshell-to-Connector Torque Values

INSTALLATION TOROUTE VALUES FOR CIRCUL AR FLECTRICAL CONNECTOR ACCESSORIES							
Shell Sizes	Column 1 Light and Medium Duty AS50151 (AS31001 Series) MIL-DTL-26482 Series I MIL-DTL-26500, MIL-DTL-27599 MIL-DTL-38999 Series I and II SAE AS81511 Series I, II, III and IV AS81703 Series I	Light and Medium Duty AS50151 (AS31001 Series) MIL-DTL-26482 Series I L-DTL-26500, MIL-DTL-27599 MIL-DTL-38999 Series I and II E AS81511 Series I, II, III and IV Heavy Duty AS50151 (AS34001 Series) MIL-DTL-22992, MIL-DTL-28840 MIL-DTL-26482 Series II MIL-DTL-38999 Series II and IV MIL-DTL-38723 Series I, II and III,					
	In-Lbs, Min/Max In-Lbs, Min/Max		In-Lbs, Min/Max				
8, 9, A	30/40	51/61	20/25				
3, 10, 10SL, 11, B	30/40	71/81	20/30				
7, 12, 12S, 13, C	35/45	103/113	25/35				
14, 14S, 15, D	35/45	111/121	25/35				
16, 16S, 17, E	35/45	111/121	30/40				
18, 19, 27, F	35/45	111/121	30/40				
20, 21, 37, G	75/85	131/141	35/45				
22, 23, H	75/85	131/141	35/45				
24, 25, 61, J	75/85	131/141	35/45				
28, 29	115/125	143/153	115/125				
32, 33	115/125	143/153	115/125				
36	115/125	142/153	112/125				
40	155/165	159/169	N/A				
44	155/165	159/169	N/A				
48	155/165	159/169	N/A				

RECOMMENDED TORQUE VALUES for

512 56555						
Series II		Series I, III, IV				
Shell Size	In-Lbs Min/Max	Shell Size	In-Lbs Min/Max			
8	46/50	9	30/36			
10	10 55/60		40/46			
12	70/75	13	55/60			
14	80/85	15	70/75			
16	90/95	17	80/85			
18	100/110	19	90/95			
20	110/120	21	100/110			
22	120/130	23	110/120			
24	140/150	25	120/130			

TORQUE VALUES FOR CABLE CLAMP SCREWS 5,6

	Θ	CABLE CLAMP SCREWS 5,6				
			In-Lbs			
s		Screw Size	Min/Max			
ax	`	2-56	1.5/2.5			
5		4-40	3.5/4.5			
5		6-32	5.0/7.0			
)		8-32	7.0/9.0			
;		10-32	9.0/11.0			
5		.250-20	11.0/13.0			
5						
0						

1) Use Glenair 600-091/157 and 600-007 torque tools when tightening hexagonal composite

- 2) Metal and composite torque values per SAE AIR 6151. All values provided in Inch-Pounds.
- 3) For additional guidance or values/conditions not listed, refer to SAE AIR6151.
- 4) Values are based on lubricated grommets and clamp threads.
- 5) For stainless-steel or plated steel screws into aluminum or stainless-steel.
- 6) Not applicable for light-duty saddles unless bottomed on clamp nut.

CABLE CLAMP TORQUE VALUES


	With Grommet ⁴	Without Grommet	
Clamp Size	In-Lbs Min/Max	In-Lbs Min/Max	
3	8/12	30/40	
4	10/15	30/40	
6	10/15	35/55	
8	12/20	35/55	
10	12/20	35/55	
12	15/30	40/60	
16	20/40	40/60	
20	20/40	40/60	
24	25/45	80/100	
28	30/50	80/100	
32	30/50	80/100	
40	40/60	80/100	

EMI/RFI shielding terminated with conical metal ferrule(s) should employ a minimum recommended torque of 35 in-lb.

Band-Master ATS®

Performance Matrix and Sizing Information

Criteria	Standard	Slim Standard	Micro	Nano			
Material	304 SS	304 SS	304 SS	304 SS			
Part Numbers (Flat)	601-005 (9"), 601-040 (14"), 601-049 (18")	601-570 (9"), 601-572 (14")	601-024 (5"), 601-060 (8"), 601-064 (14")	601-500 (6"), 601-504 (9"), 601-508 (14")			
Part Numbers (precoiled)	601-006 (9"), 601-041 (14"), 601-050 (18")	601-571 (9"), 601-573 (14")	601-025 (5"), 601-061 (8"), 601-065 (14")	601-501 (6"), 601-505 (9"), 601-509 (14")			
Lengths (inch)	18", 14" and 9"	14" and 9"	14", 8" and 5"	14", 9" and 6"			
Fits Diameters (inch)	.30" to 2.5"	.30" to 1.8"	.15" to 1.8"	.08" to 1.8"			
Width (inch)	.24"	.24″	.12″	.075″			
Thickness (Inch)	.02"	.01″	.015″	.01″			
Weight before installation (grams)	14" is 9.06g	14" is 4.46g	8" is 1.76g	9″ is .84g			
	T	ooling Information					
Hand Tool Part Number	601-100	601-109	601-101	601-108			
Pneumatic Tool Part Number	601-106	601-110	601-107	601-118			
Recommended Tool Setting	150 ±5 lbs.	100 ± 3 lbs.	80 ±5 lbs.	50 ±3 lbs.			
Performace Data							
Termination Resistance (mΩ)	0.082	0.083	0.087	0.155			
Termination Construction	Ni/Al backshell Size 25, Tin Copper Braid	Ni/Al backshell Size 25, Tin Copper Braid	Ni/Al backshell Size 15, Tin Copper Braid	Ni/Al backshell Size 16, Tin Copper Braid			
Avg. Resistance Across Band (m Ω)	0.84	0.99	0.763	1.227			
Avg. Single Junction Resistance $(m\Omega)$	0.42	0.532	0.382	0.613			
Cable Pull Out (pounds)	160 lbs	150 lbs	80 lbs	100 lbs			
Clamping Tension (pounds)	100 to 180 lbs	50 to 100 lbs	50 to 85 lbs	20 to 50 lbs			
Random Vibration	46grms at +175°C 8 hrs each axis, EIA-364-28E cond. V, letter K	46grms at +175°C 8 hrs each axis, EIA-364-28E cond. V, letter K	46grms at +175°C 8 hrs each axis, EIA-364-28E cond. V, letter K	46grms at +175°C 8 hrs each axis, EIA-364-28E cond. V, letter K			
Thermal Shock	-65°C to +200°C 5 cycles						
Temperature Life	1,000 hrs at +200°C						
Associated Test Report (Available Upon Request)			Test Report NTS 978-7382	Test Report NTS PR021798			
Mil-Spec (85049) Yes		No	Yes	No			



QwikConnect

Band-Master ATS® Manual Tool Selection

STANDARD

601-100 Hand Tool for Standard Bands

The 601-100 Standard Band-Master ATS $^{\circ}$ Tool weighs 1.18 lbs., and is designed for standard .24" width clamping bands in a tension range from 100 to 180 lbs. Calibrate at 150 lbs. \pm 5 lbs. for most shield terminations. Tool and band should never be lubricated.



601-109 Hand Tool for Slim Standard Bands

The 601-109 Slim Standard Band-Master ATS $^{\circ}$ Tool weighs 1.2 lbs., and is designed for slim standard .24" width clamping bands in a tension range from 50 to 100 lbs. Calibrate at 100 lbs. \pm 5 lbs. for most shield terminations. Tool and band should never be lubricated.



601-101 Hand Tool for Micro Bands

The 601-101 Micro Band-Master ATS $^{\circ}$ Tool weighs 1.18 lbs., and is designed for micro .120" width clamping bands in a tension range from 50 to 85 lbs. Calibrate at 80 lbs \pm 5 lbs. for most shield terminations. Tool and band should never be lubricated.



601-108 Hand Tool for Nano Bands

The 601-108 Nano Band-Master ATS $^{\circ}$ Tool weighs 1.18 lbs., and is designed for nano .075" width clamping bands in a tension range from 20 to 50 lbs. Calibrate at 50 lbs. \pm 3 lbs. for most shield terminations. Tool and band should never be lubricated.



3 lengths and 3 widths of EMI braid termination bands plus new Slim Standard bands for size and weight savings—50% lighter and lower-profile than standard bands. Terminated "Slim" style bands have a tighter, smoother buckle with no sharp edge to injure assembly technicians. Plus, say goodbye to protective tape wrapping!

	Band-Master ATS' Band Selection					
	Length		Part Number		Fits Diameter	
Bands	in.	mm.	Flat	Pre-Coiled	in.	mm.
Short Standard Band	9.0	228.6	601-005	601-006	1.0	25.4
Medium Standard Band	14.0	355.6	601-040	601-041	1.8	47.8
Long Standard Band	18.0	457.2	601-049	601-050	2.5	63.5
Short Micro Band	5.0	127.0	601-024	601-025	0.5	12.7
Medium Micro Band	8.0	203.2	601-060	601-061	.88	22.4
Long Micro Band	14.0	355.6	601-064	601-065	1.8	47.8
Short Nano Band	6.0	152.4	601-500	601-501	.60	15.2
Medium Nano Band	9.0	228.6	601-504	601-505	.94	23.9
Long Nano Band	14.0	355.6	601-508	601-509	1.8	47.8
Short Slim Standard Band	9.0	228.6	601-570	601-571	1.0	25.4
Medium Slim Standard Band	14.25	362.0	601-572	601-573	1.8	47.8
		\				

Glossary of Connector Terms and Definitions

QwikConnect

Back-Mounted: A connector design used in panel or box applications in which the mounting flange is located inside the equipment enclosure.

Bayonet Coupling: A mating design utilizing pins on the receptacle and slots on the plug for quick-connect and disconnect coupling. "Reverse" bayonet puts the pins on the plug and slots on the receptacle.

Circular Connector: Any of a thousand flavors of multipin interconnects with cylindrical contact housings and circular contact interface geometries. Circular connectors are selected for ease of engagement and disengagement, their ability to conveniently house different types of contacts, their wide range of allowable contact voltages and currents, their ease of environmental sealing and their rugged mechanical performance. In military and other high-rel applications, the MIL-DTL-5015 and MIL-DTL-38999 are commonly specified examples. Note: A disadvantage of the circular design is loss of panel space when used in arrays.

Closed Entry: A contact cavity design in which the entry diameter of the socket insulator is smaller than the outside dimension of the socket contact. Closed entry limits the size or position of the mating contact to a maximum dimension.

Connector Body: The metal or plastic housing of a connector plug. Its main purpose is to house the contacts, maintain their position and shield them from dust, dirt, moisture, and electrical interference.

Coaxial Contacts (and Cable): A contact with inner and outer conductive elements separated by a center dielectric element. Coaxial contacts terminate coaxial cable, and are employed in high bandwidth, high-frequency RF applications such as video and audio. The cable offers a closed, controlled impedance medium for the transmission of RF energy. It also provides high-frequency performance and RFI shielding.

Contact: The conductive element in a connector.
Contacts mate mechanically and electrically to transmit signals and/or power across a connector interface.
Crimp style contacts are the most common type found in high-reliability cylindrical connectors. Male contacts are sometimes referred to as leads, posts or pins.
Female contacts are universally known as sockets.

Contact Arrangement or Pattern: The gauge, number, spacing and arrangement of contacts in a connector. Contact arrangement selections are based on the current and voltage requirements of the application, and the space available for the connector package.

Contact Engaging and Separating Force: Tensile force required to engage or separate mating contacts. Measured in ounces, the force increases with contact size

Contact (or Circuit) Identifier: Wiring schematics identify and label each and every circuit with numbers, letters or special codes. On the connector, this process is maintained by marking small numbers or letters next to each contact cavity.

Contact Resistance: The measure of electrical resistance across a pair of fully mated contacts. Measured in ohms or millivolt drop at a specified current, contact resistance is affected by normal force (the static force on the contact interface), plating quality and the physical geometry of the contact.

Contact Retainer: A locking clip or tang used to secure a crimp contact in place within the connector insert. Contact retention specifications define the force required to remove a properly seated contact for each class of connector.

Contact Retention: The pressure a contact can withstand, in either direction, without being dislodged from the retaining clip which holds it within the connector insert.

Contact Size: An assigned number denoting the outside diameter of the engaging end of the pin contact. The larger the number, the smaller the size.

Contact Spacing: Also referred to as pitch, the distance, center-to-center, between adjacent contacts.

Coupling Ring: An accessory feature of the connector plug which aids in mating and unmating plugs and receptacles and prevents decoupling of the connector. Self-locking coupling rings are used for high-vibration applications.

Crimp: The physical compression (deformation) of .7 a contact barrel around a wire conductor in order to make an electrical connection.

Crimp Contact: A contact pin or socket, shipped loose with the connector body, and designed to be crimped onto the end of the wire conductor with a special tool. Often referred to as "crimp and poke" contacts, the terminated contact is poked into the connector body either by hand, or in the case of small gauge wires, with the aid of a hand-held tool. The ease of assembly and maintenance afforded by crimp contacts is preferred for aerospace and other high-reliability applications not requiring a hermetic seal.

Dielectric: A material having electrical insulating properties, such as the contact insulator in a connector or the jacketing on a wire.

Electrical Connector: A separable device which provides mechanical and electrical contact between two elements of an interconnect system without unacceptable signal distortion or power loss.

radiated or magnetically induced voltage that degrades, obstructs, or repeatedly interrupts performance of electronic equipment.

designed to prevent fluids, moisture, air or dust from degrading the performance of electrical contacts and conductors. "Environmental" components typically use gaskets, grommets, potting materials or interfacial and O-ring seals to prevent the penetration of foreign substances into the inner-workings of the part.

which provides EMI suppression in addition to its normal function of transmitting electrical energy. Filtered connectors are typically specified for high-speed signal paths. Filtering is accomplished through the integration of capacitors into the contact to separate high-frequency noise from low-frequency signals.

Firewall Connector: A class of high-reliability, feedthrough connectors designed to prevent fire or sparks from penetrating through a sealed bulkhead. Firewall connectors must continue to function for a specific period of time when exposed to fire, and are typically specified in military applications such as fighter jets and Navy ships.

Flange: The integral mounting plate on some bulkhead and feed-through receptacles used to attach the connector to the chassis or panel. The connector flange is typically square, and is mounted to the panel with threaded screws.

Front Mounted: A receptacle connector design used in panel or box applications in which the connector mounting flange is located on the outside of the equipment enclosure.

be removed from the connector for maintenance using a special hand-held tool. The proper insertion and removal tool must be used at all times. In front release designs, the tool is inserted into the mating face of the connector to disengage the contact from its retaining clip. The disengaged contact is then removed from the back (cable-side) of the connector by lightly pulling on the attached wire.

Grommet: An elastomeric seal used on the back side of a connector to seal out fluids, moisture, air and dust.

Grounding (or EMI) Fingers: A set of spring fingers in certain connectors, used to facilitate shell to shell grounding and enhance EMI performance. The grounding fingers engage before contact mating and remain engaged until after contact separation.

Guide Pins: Metal posts with a rounded or pointed tip which projects beyond the contact interface, used to assist in the correct alignment and mating of connector shells and contacts. The post mates with a corresponding cavity on the mating connector before contacts are allowed to engage. Guide pins are typically used in rack and panel packaging and in other "blindmate" applications. Guide pins can also be used to ensure correct polarization.

Hermetic Connector: A class of connectors equipped with a pressure seal for use in maintaining pressurized application environments. The hermetic element of the connector is typically fabricated from vitreous glass.

Insert: A molded piece of dielectric material that fits inside the connector shell to house the connector contacts. Inserts are tooled for each shell size, and contact arrangement. Inserts made from resilient materials also contribute to environmental properties.

Glossary of Connector Terms and Definitions

QwikConnect

Insulation Displacement: Forcing an insulated wire into a terminal slot smaller than the conductor diameter, displacing the insulation to make electrical contact.

Interfacial Seal: An elastomeric seal providing overall sealing of the mated connectors and their individual contacts. "Cork & bottle" style seals feature a raised shoulder around each pin contact that compresses into a corresponding hole on the socket contact insulator.

Key: A raised shoulder (referred to as a "dog" by crusty old machinists) which slides into a corresponding slot or keyway to guide the plug and receptacle together during mating. The principal function of the key is to insure polarization of the mating contacts.

Levels of Interconnection: A classification system defining connector types in terms of interconnect system function. Environmental levels include Level 4 (sub-assembly to sub-assembly), Level 5 (sub-assembly to I/O) and Level 6 (system to system). The lower levels (1, 2 and 3) cover printed circuit board interconnections inside equipment housings.

Mating and Unmating Force: The force required to join and separate two halves of a connector. This is the sum of contact engaging forces plus any additional force necessary to overcome minor misalignment of connector halves and any dimensional variations in the connector shells.

Normal Force: A measure of the spring pressure applied perpendicularly to contacts in mated connectors. The force of this spring pressure creates the gas-tight interface between contact surfaces which prevents corrosive contaminants from penetrating or forming between the contacts. High normal force reduces resistance across the contacts, but contributes to contact wear and may overstress the connector housing and even damage the spring properties of contact sockets. However, maintaining a constant normal force is an essential requirement for electrical integrity in the connector.

Package Size: The length, width and height of the connector; or alternatively the dimensions of the entire interconnect system. Package size is an issue in many applications where system miniaturization, faster operating speeds, higher operating temperatures and

other application requirements place demands on the envelope of space the connector and its accessories may occupy.

Plug: The half of a connector pair which is designed to attach to a wire or cable; as opposed to the receptacle half which is typically mounted to a bulkhead, panel or box. Even though we usually picture plugs as having male (pin) contacts, they can in fact house any type of contact—pins, sockets or even both. Thus it is the design and location of the connector which makes it a plug, not the gender of its contacts.

Polarize: Design features on mating connectors—such as keyways or keystone shell geometries—that insure connectors can be mated in only one possible orientation. The shape of a D-Sub connector shell, for example, assures that the two halves of the connector can be mated in only one way.

Potting: The permanent sealing of the cable end of a connector with a compound or material to exclude moisture or to provide a strain relief. Glenair typically uses epoxy compounds for this purpose because of their dimensional stability and high-temperature resistance.

Radio frequency interference (RFI) is a type of EMI that occurs between the audio and infrared frequencies in the electromagnetic spectrum. Many natural RF signals exist in nature, but typically RFI is a man-made electromagnetic wave such as might originate in unfiltered electronic circuitry.

Rear Mounted: A square-flanged receptacle connector in which the mounting flange is located on the inside of the equipment enclosure.

Rear Release: "Crimp and poke" style contacts (see Crimp Contacts above) may be removed from the connector for maintenance using a special hand-held tool. The proper insertion and removal tool must be used to install and remove wires from such crimp and poke connectors. In rear release designs, the tool is inserted into the rear (cable side) of the connector to disengage the contact from its retaining clip.

The disengaged contact is then removed from the connector by lightly pulling on the attached wire.

Receptacle: The other half of the connector pair, designed to be mounted—with jam nut fittings or other fastener hardware—to a bulkhead, panel or box. Inline receptacles are also available for cable-to-cable connections. As with the plug, it is the design and location of the receptacle in the system, not the gender of its contacts, which makes it a receptacle.

Rectangular Connector: Any of the many of multipin interconnects with rectangular shell housings and rectangular insert interface geometries. Some rectangular connectors are mounted in rack and panel configurations in which large arrays of fixed receptacle connectors are mated with plugs attached to a movable rack for efficient utilization of space. D-Subminiatures are the world's most common rectangular connectors.

Scoop-proof: Scoop-proof connectors feature a nice, long shell on the receptacle which prevents damage to the exposed contact pins during mating. No matter how hard that swabbie tries, it is impossible to cock the mating plug so as to damage the pins or electrically short the contacts.

Service Rating: Also called Current Rating, the maximum voltage or current load a connector is designed to carry during continuous, long-term use. Good engineering practice usually entails preliminary testing of connectors which will be operated with most or all contacts at the maximum rated load. Designers will often maximize contact and wire size in such situations.

Solder Cup: A connector design that typically uses potting material to permanently affix the contacts inside the connector shell. Termination of contact to wire is then accomplished by soldering the wire into the cup-like barrel on the back of the contact. In the United Kingdom it is important to pronounce the "I" in solder. Brits also prefer to say "bucket" rather than "cup" when specifying solder contacts.

Standoff Part of a connector shell, a standoff provides additional working room between the connector shell, and, for example, a printed circuit board

Surface Mount: A termination method in which solder "tails" or leads on the connector are soldered directly to a printed circuit board. In high-reliability commercial and military applications, surface mount receptacle connectors are typically limited to rectangular designs

such as D-Subminiatures and Micro-D's. But some surface-mount applications do use a cylindrical connector mounted to the box with ribbon cable or flying leads soldered directly to the PCB. The reason here is to provide a low-resistance pathway to ground of the shielded cable. In severe EMI applications, it is less satisfactory to bring the shielded cable directly to the printed circuit board because of the difficulty in shielding out interference conducted along the cable.

Termination: Termination is the physical act of attaching a wire conductor to a contact. Effective termination contributes to electrical performance and to the durability and reliability of the interconnect system. Common termination methods include crimp, insulation displacement, surface mount, and soldering. Termination can also refer to the mechanical attachment of EMI shielding to the connector backshell.

Threaded Coupling: An interconnect mating design which utilizes a threaded nut on the plug, and a corresponding set of threads on the receptacle, to mate the pair of components. The coupling nut is usually equipped with flats or knurling for easy assembly. Different thread types, profiles and geometries provide different functionality. "Buttress" threads, for example, are often specified on plastic connectors due to their enhanced tensile strength. The MIL-DTL-38999 Series III connector incorporates a triple-start threaded coupling mechanism for greater vibration protection and faster mating and unmating.

Wiping Effectiveness: Maintaining a clean, metallic path is essential if contacts are to perform with low and stable contact resistance. Surface films and contaminants are removed from the surface of plated contacts each time mating occurs. This displacement of surface contaminants during mating is called contact wiping. Wiping effectiveness depends on the contact geometry, engagement length and normal force. Interestingly, oxide film does not form on gold plated contacts, so wiping pressure can be lighter to displace the occasional surface contaminant.

Wire Pull-Out Force: This defines the force required to separate a wire from a contact. In properly terminated crimp contacts, the wire will generally break before it pulls away from the contact.

Outlook

Take Action

Most of you know that I cut my teeth in the interconnect industry as a field sales rep, a role I look back on fondly for the solid foundation it provided me for my longer-term work at Glenair. There is of course no better way to understand your customers than substantive, daily interaction. And let me tell you, the field sales rep is the tip of the spear when it comes to Glenair's outreach and interaction with the folks who buy and use our products.

Working directly with customers is all about getting stuff done; and job one is doing your utmost to understand exactly what the customer needs, and getting to work on it right away. We have a guiding principle that



speaks directly to this idea, which is, simply, *Take Action*—a kind of a wrap-up to the other principles on the Glenair list as well as an exhortation to get out there and solve problems and drive solutions. I have a colleague who likes to say that, "a good idea by itself is worthless. But a good idea put into action can be worth a fortune." Another way to say this is "knowledge of an effective approach only has value when that knowledge is put to good use."

And that's exactly why we illustrate this guiding principle with Rosie the Riveter. What a perfect image to remind us all how big an impact we can each have by stepping up to the big jobs and hammering away at them until they are done.

I'd like to repeat something to the team here at Glenair that I believe I have stated before in this column. And that is that the doors to upper management are always open at Glenair if you are ever in doubt as to what action to take in any particular situation. Unlike many organizations, there is no "Chief of Staff" guarding access to our most senior people (and potentially keeping that "worthless" good idea from becoming a "fortune"). We are sincere about this. Our goal is a nice flat organization in which we all work together as a team, and truly feel empowered to take action to solve problems on behalf of our customers.

By the way, isn't this issue of *QwikConnect* a keeper? What a fabulous compendium of useful reference information for all of us that call the interconnect industry our home. Thanks to everyone who contributed.

Ohris Torney

QwikConnect

ILENAIR • Volume 23 • Number 1

Publisher

Christopher J. Toomey

Managing Editor
Marcus Kaufman

Editor/Art Director
Mike Borgsdorf

Graphic Designer
George Ramirez

Technical Consultant
Jim Donaldson

Issue Contributors

Brian Brown Greg Brown Tony Birks Greg Cameron Michael Connal Ty Geverink Mike Ghara Pat Oakes

Distribution

Terry White

To subscribe or unsubscribe, please contact Terry White: twhite@qlenair.com

QwikConnect is published quarterly by Glenair, Inc. and printed in the U.S.A. All rights reserved. © Copyright 2019 Glenair, Inc. A complete archive of past issues of QwikConnect is available on the Internet at www.glenair.com/qwikconnect

GLENAIR, INC.

1211 AIR WAY
GLENDALE, CA 91201-2497
TEL: 818-247-6000
FAX: 818-500-9912
E-MAIL: sales@glenair.com
www.glenair.com

